





	ITEM ①	ITEM ②
PART NUMBER	BODY	CONTACT
108-XXXX-801	NYLON	BRASS TIN PL .0001 MIN OVER NICKEL PL .00005 MIN
108-XXXX-802	NYLON	BRASS GOLD PL .00001 MIN OVER NICKEL PL .00003 MIN



MOUNTING HOLE DETAIL

- NOTES:
1. SPECIFICATIONS:
- MECHANICAL:
- TORQUE: 12 OZ IN MIN REQUIRED TO TURN CONTACT IN BODY
- TORQUE: 12 OZ IN MIN REQUIRED TO TURN BODY IN PANEL
- PUSHOUT FORCE: 30 LBS MIN REQUIRED TO REMOVE CONTACT FROM BODY
- PUSHOUT FORCE: 50 LBS MIN REQUIRED TO REMOVE BODY FROM PANEL
- ELECTRICAL:
- DIELECTRIC WITHSTANDING VOLTAGE: 8500 VRMS MIN
- CURRENT RATING: 10 AMPS MIN
- CONTACT RESISTANCE: 10 MILLIOHMS MAX
- CAPACITANCE: 2.6 pF NOMINAL
- INSULATION RESISTANCE: 5000 MEGOHMS MIN
- ENVIRONMENTAL:
- LIFE EXPECTANCY: 5000 CYCLES MIN
- TEMPERATURE RANGE: -55° TO +85° C
- VIBRATION: 10 TO 55 Hz MIN
- SHOCK: 100 g's MIN

CATALOG DESIGNATION FOR VARIOUS COLORED BODIES	
PART NUMBER	COLOR
108-2301-XXX	WHITE
108-2302-XXX	RED
108-2303-XXX	BLACK
108-2304-XXX	GREEN
108-2305-XXX	LIGHT BLUE
108-2306-XXX	ORANGE
108-2307-XXX	YELLOW
108-2308-XXX	BROWN
108-2309-XXX	LIGHT GREEN
108-2310-XXX	BLUE
108-2311-XXX	IVORY
108-2312-XXX	VIOLET
108-2313-XXX	GRAY

DRAWING NO. - 2301-801									
C - 108-2320-820									
0		REVISIONS							
ENGINEERING RELEASE									
14	08-22-89	EJ	RFR	CS	SM	H			ECO 24322

THIS DRAWING TO BE INTERPRETED
PER ASME Y 14.5M - 1994

"μSTATION"



Cinch Connectivity Solutions
P.O. Box 1732
Waseca, MN 56093
1-800-247-8256

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY <i>EJ</i>	DATE 9-25-89
DECIMALS	mm	CHECKED BY RRE	DATE 1-12-90
.XX	_____	APPROVED BY GSQ	DATE 1-12-90
.XXX	_____		DATE 1-12-90
MATL	_____	RELEASE DATE 1-12-90	
FINISH	_____	U/M INCH	SCALE 4:1

TITLE BANANA JACK RIB-LOC FOR .175 BANANA PLUG	
SHEET 2 OF 2	DRAWING NO. - 2301-801 C - 108-2320-820