






PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL


PC BOARD VERSIONS			
PRODUCT NR:	PCB THICKNESS	DIM A	LOADING INFO.
85865-X02/X02LF	1.6	2.90	FULL LOADED
85865-X12/X12LF	2.4	3.53	FULL LOADED



- NOTES:
- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
 - 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
 - 3 INDICATED HOLES ARE UNPLATED.
 - 4 For PLATING SPEC, REFER TO DRAWING 10097866.
 - 5 PRODUCT MARKING: PART NUMBER & BATCH ID.
 - 6 SET BACK FOR TAIL BLOCK
 - 7 DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.
 - 8 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD.
 - 9 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008 .
 - 10 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.



RECOMMENDED HOLE PATTERN, COMPONENT SIDE.



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI ELECTRONICS	
SEE NOTES									
ltr	ecm	no	dr	date	linear	projection	title		
H	0004-0043	Clu	040623				5 ROW R.A. S.T.B. SIGNAL		
J	0004-0104	Clu	041223				RECEPT. 48mm MOD. P.P.		
K	0007-0189	Cent	05/15/07	angles			product family		
L	0008-0171	TER	8/26/08	dr	R. VISSCHERS	941005	size		
M	0009-0088	Cent	03/03/08	engr	E. FEIJEN	941005	dwg no		
					chr	E. FEIJEN	scale		
G	0004-0036	Clu	040603	app	E. FEIJEN	941003	5:1		
sheet	revision								
index	sheet								