

FLEX STACK

(2.54 mm) .100"

TLW-118-06-T-D

MTLW-130-05-G-S-110


TLW, MTLW SERIES

LOW-PROFILE .025" SQ POST HEADERS

Board Mates:
BSW, CES, SLW, HLE

FEATURES

These headers provide the ultimate low-profile (0.64 mm) .025" square post board stacking system. The high quality Phosphor Bronze terminals are available with a standard short post height (TLW Series) for mating with low-profile sockets, or the post height can be Modified (MTLW Series) to accommodate IDC assemblies and other applications.



TLW	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OTHER OPTION											
01 thru 40 = Single Row 			Specify LEAD STYLE from chart 			-F = Gold flash on post, Matte Tin on tail	-S = Single Row -D = Double Row										
01 thru 36 = Double Row 			<table border="1"> <thead> <tr> <th>LEAD STYLE</th> <th>A</th> <th>C</th> </tr> </thead> <tbody> <tr> <td>-01</td> <td>N/A</td> <td>(5.84) .230</td> </tr> <tr> <td>-05</td> <td>(4.32) .170</td> <td>(2.67) .105</td> </tr> <tr> <td>-06</td> <td>(3.43) .135</td> <td>(2.67) .105</td> </tr> </tbody> </table>	LEAD STYLE	A	C	-01	N/A	(5.84) .230	-05	(4.32) .170	(2.67) .105	-06	(3.43) .135	(2.67) .105	-G = 10 μ" (0.25 μm) Gold on post, Gold flash on tail -T = Matte Tin	-RA = Right-angle (-01 Lead Style only) -“XX” = Polarized Position Specify position for omitted pin.
LEAD STYLE	A	C															
-01	N/A	(5.84) .230															
-05	(4.32) .170	(2.67) .105															
-06	(3.43) .135	(2.67) .105															

ALSO AVAILABLE
(MOQ Required)

• Other platings

SPECIFICATIONS

For complete specifications see www.samtec.com?TLW or www.samtec.com?MTLW

Insulator Material: Black Liquid Crystal Polymer
Terminal Material: Phosphor Bronze
Plating: Au or Sn over 50 μ" (1.27 μm) Ni
Current Rating (TLW/SLW): 5.2 A per pin (2 pins powered)
Operating Temp Range: -55 °C to +105 °C with Tin
 -55 °C to +125 °C with Gold
RoHS Compliant: Yes
Lead-Free Solderable: Yes

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Note:
Some lengths, styles and options are non-standard, non-returnable. MTLW Series is non-standard, non-returnable.

MTLW	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	POST HEIGHT																			
01 thru 40 = Single Row 			Specify LEAD STYLE from chart 			-S = Single Row -D = Double Row	-“XXX” = Post Height Dimension (In inches)																		
01 thru 36 = Double Row 			<table border="1"> <thead> <tr> <th>LEAD STYLE</th> <th>OAL</th> </tr> </thead> <tbody> <tr> <td>-05</td> <td>(8.51) .335</td> </tr> <tr> <td>-06</td> <td>(7.62) .300</td> </tr> <tr> <td>-07</td> <td>(10.92) .430</td> </tr> <tr> <td>-08</td> <td>(13.46) .530</td> </tr> <tr> <td>-09</td> <td>(18.54) .730</td> </tr> <tr> <td>-10</td> <td>(21.08) .830</td> </tr> <tr> <td>-22</td> <td>(16.00) .630</td> </tr> <tr> <td>-23</td> <td>(11.30) .445</td> </tr> <tr> <td>-24</td> <td>(12.19) .480</td> </tr> </tbody> </table>	LEAD STYLE	OAL	-05	(8.51) .335	-06	(7.62) .300	-07	(10.92) .430	-08	(13.46) .530	-09	(18.54) .730	-10	(21.08) .830	-22	(16.00) .630	-23	(11.30) .445	-24	(12.19) .480	-F = Gold flash on post, Matte Tin on tail -L = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail -G = 10 μ" (0.25 μm) Gold on post, Gold flash on tail -T = Matte Tin	
LEAD STYLE	OAL																								
-05	(8.51) .335																								
-06	(7.62) .300																								
-07	(10.92) .430																								
-08	(13.46) .530																								
-09	(18.54) .730																								
-10	(21.08) .830																								
-22	(16.00) .630																								
-23	(11.30) .445																								
-24	(12.19) .480																								

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.