






- THIS RECEPTACLE WILL MATE WITH ANY PLUG WITH THE SAME INSERT ARRANGEMENT AS DEFINED BY MS18273-1.
- MAXIMUM WIRE INSULATION USED WITH THIS RECEPTACLE IS .072 DIA MAX.
- Be Cu RETENTION CLIPS ARE INCLUDED IN INSERT.
- CUSTOMER PART NUMBER MAY BE SPLIT BETWEEN FRONT AND REAR SHELLS, SAME SIDE. FAR SIDE REFERS TO WIDE SIDE OF KEYSTONE, NEAR SIDE REFERS TO NARROW SIDE OF KEYSTONE.
- THESE CONNECTORS ARE QUALIFIED TO GODDARD SPACE FLIGHT CENTER SPECIFICATION S-311-P-4.
- CUSTOMER PART NUMBER MAY BE SPLIT BETWEEN FRONT AND REAR SHELLS.
- RESTRICTED TO CAE ELECTRONICS ONLY.
- CONNECTOR SUPPLIED WITH CONTACTS, TE PART NUMBER 206793-1; (NOT INSTALLED).

SUPERSEDED BY 1996077-1				
	.120	8333648P2	207253-8	207253-8
	.120	570513-1	207253-7	207253-7
9	.120	LMSC 1621480-001	207253-6	207253-6
	.120	LMSC 1621480-001	207253-5	207253-5
8 6	.120	311P409-1S-B-12	207253-2	207253-4
	-	-	207253-3	207253-3
6	.120	311P409-1S-B-12	207253-2	207253-2
6	.154	311P409-1S-B-15	207253-1	207253-1
REMARKS	DIA A	INK STAMPED CUSTOMER P/N	INK STAMPED TE P/N	AMP P/N
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. THOMPSON CHK D. MANTIONE APVD D. MANTIONE	TE Connectivity	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME	AMPLIMITE RECEPTACLE ASSEMBLY SERIES 109, SIZE 1	
	0 PLC ± -	PRODUCT SPEC	-	
	1 PLC ± -	APPLICATION SPEC	-	
	2 PLC ± -	WEIGHT	-	
MATERIAL SEE CALLOUTS	FINISH SEE CALLOUTS	SCALE	SHEET 1 OF 1	
CUSTOMER DRAWING		SCALE 4:1	REV U	