






REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD
C1		REVISED PER ECO-19-015526	11OCT2019	AL HL



RECOMMENDED PCB DESIGN

1. STUD : CAP : 46
2. Ni PLATING AFTER PLATING 35
3. FR-4, t=1.0REF

- NOTE
1. MATERIAL : STUD : BRASS
CAP : 46 NYLON
2. FINISH : MATTE TIN PLATING AFTER Ni PLATING.
3. NO BURR IS ALLOWED AT UNSPECIFIED CORNERS.
FR-4, t=1.0REF

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.TAKASU 16SEP03		 TE Connectivity Ltd.						
DIMENSIONS: 単位: 純 MM		CHK K.KODAIRA 16SEP03								
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD K.KODAIRA 16SEP03								
		NAME 名称								
		EMBOSS PACKAGE, MDC-STUD								
		SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO					
MATERIAL 材料		FINISH 仕上		A300779C-1717786		—				
SEE TABLE		WEIGHT		CUSTOMER DRAWING			SCALE 尺度	NTS	SHEET 1 of 2	REV C1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP ,01 .

© COPYRIGHT 2003 By -

ALL RIGHTS RESERVED.

REVISIONS

變更

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

DIRECTION OFF TOP OF REEL →

WEEDING THE COVER TAPE :
300MIN
(NOT INCLUDE
EMPTY POCKETS)

?????????
300??
??????????

PEELING ANGLE :
??? 165°~180°

VIEW C

ø380±1

16.4REF

23.5F

400 MIN.

WITHOUT CHARGE

WITH PRODUCT CHARGE

ea PACKAGE

??

WITHOUT CHARGE

25 HOLES MIN.

OBSELETE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN H.TAKASU 16SEP2003

CHK K.KODAIRA 16SEP2003

APVD K.KODAIRA 16SEP2003

PRODUCT SPEC
製品規格APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING



TE Connectivity Ltd.

NAME
名称EMBOSS PACKAGE,
MDC-STUD

SIZE

CAGE CODE

DRAWING NO
番号

C=1717786

RESTRICTED TO


—

SCALE
尺度 NTS

SHEET

2 OF 2

REV C1

DIMENSIONS:
単位: 寸
MMTOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0	PLC	± 0.3
1	PLC	± 0.3
2	PLC	± 0.1
3	PLC	±
4	PLC	±
ANGLES		± 1

FINISH
仕上MATERIAL
材料

SEE TABLE