

This information is given as an indication. In the continual goal to improve our products, we reserve the right to make any modifications judged necessary

2 W

DC- 18 GHz


SMA

COAXIAL ATTENUATOR

issue
04.aug.93

Page
1 / 1

DRAWING



General tolerances: +/- 0.5 mm

R F CHARACTERISTICS

FREQUENCY RANGE : DC - 18 GHz
IMPEDANCE : 50 Ohms
ATTENUATION - NOMINAL : 20 dB

FREQUENCY	DC- 2 GHz	2 - 4 GHz	4 - 8 GHz	8 -12.4GHz	12.4- 18 GHz
V.S.W.R	<= 1.10	<= 1.15	<= 1.20	<= 1.25	<= 1.35
DEVIATION (dB)	+0.6 / -0.6	+0.6 / -0.6	+0.6 / -0.6	+0.6 / -0.6	+0.6 / -0.6

TEMPERATURE SENSITIVITY : 4×10^{-4} dB
dB * °C

PEAK POWER at 25°C (1µs,1%.) : 100 W


AVERAGE POWER at 25°C : 2 W

MECHANICAL CHARACTERISTICS

CONNECTORS : SMA male/female per MIL-C 39012
WEIGHT : < 5 g

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE RANGE (°C) : -55 , +125
STORAGE TEMPERATURE RANGE (°C) : -55 , +125



QUALITY
Dpt app. _____

CREATION
PEN : CAT
EP : -----
Nom : KL
Date:14.dec.87

04.aug.93

New format

25.apr.89

New format

ISSUE

REVISIONS

NAME

RADIALL®

101. Philibert Hoffmann | Phone:33.1.49353535
- Z.I Ouest - | Fax :33.1.48546363
93116 ROSNY/BOIS Cedex-FRANCE | Twx RADIA 235220F