PART NUMBER CODING

G _ C _ _ SFBN - M30

NUMBER OF POSITIONS PER ROW

PLATING

ALL PLATINGS HAVE .000050" NICKEL UNDERPLATE

	CONTACT	TERMINATION
B =	.000010" GOLD	.000100" PURE TIN, MATTE
C =	.000030" GOLD	.000100" PURE TIN, MATTE
E =	.000100" PURE TIN, MATTE OVERALL	





REVISIONS				
REV.	ECO. NO	DESCRIPTION	DATE	BY
A	474	ORIGINAL RELEASE	10-20-05	MNH
B	841	REVERSE BENDS	11/28/2005	HT
C	1694	ADDING TOLERANCE	5/16/2008	IA
D	1902	UPDATE PCB LAYOUT, REMOVE BOM	1/22/2009	JH

PART NUMBER	A
G_C01SFBN-M30	0.100 [2.54]
G_C02SFBN-M30	0.200 [5.08]
G_C03SFBN-M30	0.300 [7.62]
G_C04SFBN-M30	0.400 [10.16]
G_C05SFBN-M30	0.500 [12.70]
G_C06SFBN-M30	0.600 [15.24]
G_C07SFBN-M30	0.700 [17.78]
G_C08SFBN-M30	0.800 [20.32]
G_C09SFBN-M30	0.900 [22.86]
G_C10SFBN-M30	1.000 [25.40]
G_C11SFBN-M30	1.100 [27.94]
G_C12SFBN-M30	1.200 [30.48]
G_C13SFBN-M30	1.300 [33.02]
G_C14SFBN-M30	1.400 [35.56]
G_C15SFBN-M30	1.500 [38.10]
G_C16SFBN-M30	1.600 [40.64]
G_C17SFBN-M30	1.700 [43.18]
G_C18SFBN-M30	1.800 [45.72]
G_C19SFBN-M30	1.900 [48.26]
G_C20SFBN-M30	2.000 [50.80]
G_C21SFBN-M30	2.100 [53.34]
G_C22SFBN-M30	2.200 [55.88]
G_C23SFBN-M30	2.300 [58.42]
G_C24SFBN-M30	2.400 [60.96]
G_C25SFBN-M30	2.500 [63.50]
G_C26SFBN-M30	2.600 [66.04]
G_C27SFBN-M30	2.700 [68.58]
G_C28SFBN-M30	2.800 [71.12]
G_C29SFBN-M30	2.900 [73.66]
G_C30SFBN-M30	3.000 [76.20]
G_C31SFBN-M30	3.100 [78.74]
G_C32SFBN-M30	3.200 [81.28]
G_C33SFBN-M30	3.300 [83.82]
G_C34SFBN-M30	3.400 [86.36]
G_C35SFBN-M30	3.500 [88.90]
G_C36SFBN-M30	3.600 [91.44]

NOTES:

1. INSULATOR MATERIAL: PA9T.
2. CONTACT MATERIAL: PHOSPHOR BRONZE
3. PLATING: SEE TABLE
4. OPERATING TEMPERATURE: -65°C TO +125°C
5. PROCESSING TEMPERATURE: 260°C MAX FOR 120 SECS MAX.
6. UL FLAMMABILITY: 94V-0
7. VOLTAGE RATING: 600 VDC MINIMUM AT SEA LEVEL.
8. CURRENT RATING: 3 AMP
9. INSULATION RESISTANCE: 5000 MEGA OHMS.
10. MODIFICATION: SURFACE MOUNT.

CUSTOMER COPY

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES[MM]
TOLERANCES:
ANGULAR: ± 30'
.XX=± .02 [.508]
.XXX=± .005 [.1270]
.XXXX=± .0005 [.0127]
SURFACE FINISH: 63 Ra
REMOVE ALL BURRS AND SHARP EDGES .010 MAX

INTERPRET DIMENSIONS AND GEOMETRIC TOLERANCING
PER: ANSI Y14.5M-1994

	DATE	NAME
DRAWN		Aria

THE INFORMATION HEREIN CONTAINS PROPIETARY INFORMATION OF SULLINS ELECTRONICS AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED TO OTHERS FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY AN OFFICER OF SULLINS ELECTRONICS.

SULLINS CONNECTOR SOLUTIONS

DESCRIPTION: HEADER, .100 CC

PART NUMBER: G_C_ _SFBN-M30

SIZE	DWG. NO.	REV
C	C10584	D

SCALE: 4:1 | SHEET 1 OF 1

FILE NAME: Z:\ECO PENDING\1902\C10584, G_C_ _SFBN-M30 HEADERS PRINT: 2/9/2009