




D

C


B

A



RECOMMENDED P. C. BOARD LAYOUT

1. POLARIZING KEYS ARE INTENDED TO PREVENT 180° MISMATCH OF LIKE SIZES; KEYS ARE NOT INTENDED TO PREVENT MATING OF DIFFERENT SIZES.
2. TAILS SOLDER DIPPED $.025$ MIN LENGTH, WITH SN63 SOLDER PER QQ-S-571.
3. MARK AMP, PART NUMBER AND DATE CODE. MARKING MAY BE ON 2 SIDES OF THE PART. SMALLER ASSEMBLIES MAY CONTAIN NO MARKING OR PARTIAL MARKING.
4. HOUSING MATERIAL: FLAME RETARDANT GLASS REINFORCED POLYESTER. COLOR: BLACK.
5. SOCKET CONTACT MATERIAL: BERYLLIUM COPPER PER QQ-C-533. ALTERNATE MATERIAL: PHOSPHOR BRONZE PER QQ-B-750. CONTACT FINISH: PLATED GOLD $.000050$ THICK ON MATING AREA PLATED GOLD FLASH ON CONTACT TAIL, ALL OVER NICKEL $.000050$ THICK.



SECTION A-A

OBSOLETE	.700	.775	30	213143-8
	.550	.625	24	213143-7
OBSOLETE	1.200	1.275	50	213143-6
	1.150	1.225	48	213143-5
OBSOLETE	.950	1.025	40	213143-4
	.600	.675	26	213143-3
	.100	.175	6	213143-2
	.050	.125	4	213143-1
	B	A	NO OF POSITIONS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

T. SHUEY

12-7-88

CHK

—

—

APVD

—

—

PRODUCT SPEC

—

—

APPLICATION SPEC

—

—

WEIGHT

—

—

CUSTOMER DRAWING

—

—

DIMENSIONS:

INCHES

0 PLC

±

—

1 PLC

±

—

2 PLC

±

—

3 PLC

±

.010

4 PLC

±

—

ANGLES

±

—

FINISH

—

—

MATERIAL

SEE CALLOUTS

SEE CALLOUTS

TE Connectivity

SOCKET CONNECTOR ASSEMBLY,
CHEVRON, PLANE SURFACE MOUNT
WITH KEYING

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=213143

RESTRICTED TO

—

SCALE

10:1

SHEET

1 of 1

REV

M