



Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFFiber Optic ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'F6LZ3-12M2'

Your search criteria matched only one product, shown below

F6LZ3-12M2



- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- SC Duplex Patch Cords include SC Duplex Clips to maintain polarity
- Highest quality flame retardant fiber optic cable with tight -buffered coating on each optical fiber

Part Number	F6LZ3-12M2
RoHS Compliancy Status	Intended for use in fixed installations which are outside the scope of RoHS
Part Description	SC to female MTRJ multimode duplex LSZH patch cord, 1.8mm jacketed cable (one duplex SC connector on one end and one female MTRJ connector on the other end)– 62.5/125μ m.
Product Type	Hybrid Patch Cords
Length (m)	2
Fiber Compatibility	62.5/125μm
Fiber Cable Size	1.8mm
Fiber Cable Type	Jacketed
Fiber Type	Multimode
Connector 1 Type	SC Connector
Connector 2 Type	MT-RJ Connector
End Configurations	SC to MTRJ
Fiber Count	2
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.