




1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 9.14±0.08 [.360±.003] CENTERS

2 FOR OPTIMUM RETENTION IN POKE-IN TYPE MAG-MATE TERMINALS, THE SERRATION AS SHOWN MUST BE ENGAGED WITH THE EDGE OF THE LEAF

DETAIL D
SCALE 15:1

OBSOLETE	REVERSE	#18-#14 AWG	2.29-3.56 [.090-.140] DIA	63458-2
	STANDARD	#18-#14 AWG	2.29-3.56 [.090-.140] DIA	63458-1
	REELING	WIRE RANGE	INSULATION RANGE	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 22DEC97 MICHAEL S. FEHER CHK 20JAN98 RICHARD GRZYBOWSKI APVD 21JAN98 NELSON E. NEFF	TE Connectivity	
DIMENSIONS: INCHES		PRODUCT SPEC 108-22045	NAME TAB, POKE-IN, MAG-MATE™ -	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-2050		
MATERIAL BRASS		WEIGHT -	SIZE A2	CAGE CODE 00779
FINISH PRE-TIN PLATED		CUSTOMER DRAWING	DRAWING NO C=63458	RESTRICTED TO -
		SCALE 8:1	SHEET 1 of 1	REV J2