


## P-Channel 2.5-V (G-S) MOSFET

PRODUCT SUMMARY		
$V_{DS}$ (V)	$r_{DS(on)}$ ( $\Omega$ )	$I_D$ (A)
- 25	0.180 at $V_{GS} = - 4.5$ V	$\pm 1.5$
	0.200 at $V_{GS} = - 3.6$ V	$\pm 1.4$
	0.265 at $V_{GS} = - 2.5$ V	$\pm 1.2$

### FEATURES

- TrenchFET® Power MOSFET


**RoHS\***  
COMPLIANT


Ordering Information: Si1403DL-T1  
Si1403DL-T1-E3 (Lead (Pb)-free)

### ABSOLUTE MAXIMUM RATINGS $T_A = 25$ °C, unless otherwise noted

Parameter	Symbol	5 Sec	Steady State	Unit
Drain-Source Voltage	$V_{DS}$	- 20	$\pm 12$	V
Gate-Source Voltage	$V_{GS}$			
Continuous Drain Current ( $T_J = 150$ °C)	$I_D$	$\pm 1.5$	$\pm 1.4$	A
		$\pm 1.2$	$\pm 1.0$	
Pulsed Drain Current	$I_{DM}$	$\pm 5$		A
Continuous Diode Current (Diode Conduction) <sup>a</sup>	$I_S$	- 0.8	- 0.8	
Maximum Power Dissipation <sup>a</sup>	$P_D$	0.625	0.568	W
		0.400	0.295	
Operating Junction and Storage Temperature Range	$T_J, T_{stg}$	- 55 to 150		°C

### THERMAL RESISTANCE RATINGS

Parameter	Symbol	Typical	Maximum	Unit
Maximum Junction-to-Ambient <sup>a</sup>	$R_{thJA}$	165	200	°C/W
Steady State		180	220	
Maximum Junction-to-Foot (Drain)	$R_{thJF}$	105	130	

Notes:

a. Surface mounted on 1" x 1" FR4 board.

\* Pb containing terminations are not RoHS compliant, exemptions may apply.

**SPECIFICATIONS**  $T_J = 25^\circ\text{C}$ , unless otherwise noted



Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
<b>Static</b>						
Gate Threshold Voltage	$V_{GS(\text{th})}$	$V_{DS} = V_{GS}, I_D = -250 \mu\text{A}$	-0.6		-1.5	V
Gate-Body Leakage	$I_{GSS}$	$V_{DS} = 0 \text{ V}, V_{GS} = \pm 12 \text{ V}$			$\pm 100$	nA
Zero Gate Voltage Drain Current	$I_{DSS}$	$V_{DS} = -20 \text{ V}, V_{GS} = 0 \text{ V}$			-1	
		$V_{DS} = -20 \text{ V}, V_{GS} = 0 \text{ V}, T_J = 85^\circ\text{C}$			-5	$\mu\text{A}$
On-State Drain Current <sup>a</sup>	$I_{D(\text{on})}$	$V_{DS} = -5 \text{ V}, V_{GS} = -4.5 \text{ V}$	-2			A
Drain-Source On-State Resistance <sup>a</sup>	$r_{DS(\text{on})}$	$V_{GS} = -4.5 \text{ V}, I_D = -1.5 \text{ A}$		0.145	0.180	$\Omega$
		$V_{GS} = -3.6 \text{ V}, I_D = -1.4 \text{ A}$		0.165	0.200	
		$V_{GS} = -2.5 \text{ V}, I_D = -0.8 \text{ A}$		0.220	0.265	
Forward Transconductance <sup>a</sup>	$g_{fs}$	$V_{GS} = -10 \text{ V}, I_D = -1.5 \text{ A}$		3.8		S
Diode Forward Voltage <sup>a</sup>	$V_{SD}$	$I_S = -0.8, V_{GS} = 0 \text{ V}$		-0.78	-1.1	V
<b>Dynamic<sup>b</sup></b>						
Total Gate Charge	$Q_g$	$V_{DS} = -10 \text{ V}, V_{GS} = -4.5 \text{ V}, I_D = -1.5 \text{ A}$		3.7	4.5	nC
Gate-Source Charge	$Q_{gs}$			0.9		
Gate-Drain Charge	$Q_{gd}$			0.9		
Turn-On Delay Time	$t_{d(\text{on})}$	$V_{DD} = -10 \text{ V}, R_L = 10 \Omega$ $I_D \equiv -1 \text{ A}, V_{GEN} = -4.5 \text{ V}, R_G = 6 \Omega$		8	12	ns
Rise Time	$t_r$			25	40	
Turn-Off Delay Time	$t_{d(\text{off})}$			21	32	
Fall Time	$t_f$			20	30	
Source-Drain Reverse Recovery Time	$t_{rr}$	$I_F = -0.8 \text{ A}, dI/dt = 100 \text{ A}/\mu\text{s}$		20	40	







## Notes:

a. Pulse test; pulse width  $\leq 300 \mu\text{s}$ , duty cycle  $\leq 2\%$ .





b. Guaranteed by design, not subject to production testing.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

**TYPICAL CHARACTERISTICS**  $T_A = 25^\circ\text{C}$ , unless noted

**TYPICAL CHARACTERISTICS**  $T_A = 25^\circ\text{C}$ , unless noted

**On-Resistance vs. Drain Current**

**Capacitance**

**Gate Charge**

**On-Resistance vs. Junction Temperature**

**Capacitance**

**On-Resistance vs. Gate-to-Source Voltage**

**TYPICAL CHARACTERISTICS**  $T_A = 25^\circ\text{C}$ , unless noted



## Normalized Thermal Transient Impedance, Junction-to-Foot

## Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay](#):

[SI1403DL-T1-E3](#) [SI1403DL-T1](#) [SI1403DL-E3](#)