


# HiPerFET™ Power MOSFETs Q-Class

N-Channel Enhancement Mode  
Avalanche Rated, High dv/dt, Low  $Q_g$

IXFH 80N20Q  
IXFK 80N20Q  
IXFT 80N20Q


$$\begin{aligned} V_{DSS} &= 200 \text{ V} \\ I_{D25} &= 80 \text{ A} \\ R_{DS(on)} &= 28 \text{ m}\Omega \\ t_{rr} &\leq 200 \text{ ns} \end{aligned}$$

Preliminary data sheet




| Symbol    | Test Conditions                                                                                                                         | Maximum Ratings            |                                      |
|-----------|-----------------------------------------------------------------------------------------------------------------------------------------|----------------------------|--------------------------------------|
| $V_{DSS}$ | $T_J = 25^\circ\text{C to } 150^\circ\text{C}$                                                                                          | 200                        | V                                    |
| $V_{DGR}$ | $T_J = 25^\circ\text{C to } 150^\circ\text{C}; R_{GS} = 1 \text{ M}\Omega$                                                              | 200                        | V                                    |
| $V_{GS}$  | Continuous                                                                                                                              | $\pm 20$                   | V                                    |
| $V_{GSM}$ | Transient                                                                                                                               | $\pm 30$                   | V                                    |
| $I_{D25}$ | $T_C = 25^\circ\text{C}$                                                                                                                | 80                         | A                                    |
| $I_{DM}$  | $T_C = 25^\circ\text{C}$ , pulse width limited by $T_{JM}$                                                                              | 320                        | A                                    |
| $I_{AR}$  | $T_C = 25^\circ\text{C}$                                                                                                                | 80                         | A                                    |
| $E_{AR}$  | $T_C = 25^\circ\text{C}$                                                                                                                | 45                         | mJ                                   |
| $E_{AS}$  | $T_C = 25^\circ\text{C}$                                                                                                                | 1.5                        | J                                    |
| dv/dt     | $I_S \leq I_{DM}$ , $di/dt \leq 100 \text{ A}/\mu\text{s}$ , $V_{DD} \leq V_{DSS}$ ,<br>$T_J \leq 150^\circ\text{C}$ , $R_G = 2 \Omega$ | 5                          | V/ns                                 |
| $P_D$     | $T_C = 25^\circ\text{C}$                                                                                                                | 360                        | W                                    |
| $T_J$     |                                                                                                                                         | -55 ... +150               | $^\circ\text{C}$                     |
| $T_{JM}$  |                                                                                                                                         | 150                        | $^\circ\text{C}$                     |
| $T_{stg}$ |                                                                                                                                         | -55 ... +150               | $^\circ\text{C}$                     |
| $T_L$     | 1.6 mm (0.063 in) from case for 10 s                                                                                                    | 300                        | $^\circ\text{C}$                     |
| $M_d$     | Mounting torque                                                                                                                         | TO-247<br>TO-264           | 1.13/10 Nm/lb.in.<br>0.9/6 Nm/lb.in. |
| Weight    |                                                                                                                                         | TO-247<br>TO-264<br>TO-268 | 6 g<br>10 g<br>4 g                   |


TO-247 AD (IXFH)



TO-268 (D3) (IXFT)



TO-264 AA (IXFK)



G = Gate  
S = Source

TAB = Drain

| Symbol       | Test Conditions                                                                                                        | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |                          |
|--------------|------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|--------------------------|
|              |                                                                                                                        | min.                                                                              | typ. | max.                     |
| $V_{DSS}$    | $V_{GS} = 0 \text{ V}$ , $I_D = 250 \mu\text{A}$                                                                       | 200                                                                               |      | V                        |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 4 \text{ mA}$                                                                               | 2.0                                                                               |      | 4.0 V                    |
| $I_{GSS}$    | $V_{GS} = \pm 20 \text{ V}_{DC}$ , $V_{DS} = 0$                                                                        |                                                                                   |      | $\pm 100 \text{ nA}$     |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$ , $V_{GS} = 0 \text{ V}$<br>$T_J = 25^\circ\text{C}$<br>$T_J = 125^\circ\text{C}$                   |                                                                                   |      | 25 $\mu\text{A}$<br>1 mA |
| $R_{DS(on)}$ | $V_{GS} = 10 \text{ V}$ , $I_D = 0.5 \cdot I_{D25}$<br>Pulse test, $t \leq 300 \mu\text{s}$ , duty cycle $d \leq 2 \%$ |                                                                                   |      | 28 m $\Omega$            |

## Features

- Low gate charge
- International standard packages
- Epoxy meet UL 94V-0, flammability classification
- Low  $R_{DS(on)}$  HDMOS™ process
- Rugged polysilicon gate cell structure
- Avalanche energy and current rated
- Fast intrinsic Rectifier

## Advantages

- Easy to mount
- Space savings
- High power density

| Symbol                                                                                                | Test Conditions                                                                                                                                    | Characteristic Values<br>(T <sub>J</sub> = 25°C, unless otherwise specified) |              |            |    |
|-------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------|--------------|------------|----|
|                                                                                                       |                                                                                                                                                    | min.                                                                         | typ.         | max.       |    |
| <b>g<sub>fs</sub></b>                                                                                 | V <sub>DS</sub> = 10 V; I <sub>D</sub> = 0.5 • I <sub>D25</sub> , pulse test                                                                       | 35                                                                           | 45           | S          |    |
| <b>C<sub>iss</sub></b><br><b>C<sub>oss</sub></b><br><b>C<sub>rss</sub></b>                            | } V <sub>GS</sub> = 0 V, V <sub>DS</sub> = 25 V, f = 1 MHz                                                                                         |                                                                              | 4600         | pF         |    |
|                                                                                                       |                                                                                                                                                    |                                                                              |              | 1100       | pF |
|                                                                                                       |                                                                                                                                                    |                                                                              |              | 500        | pF |
| <b>t<sub>d(on)</sub></b><br><b>t<sub>r</sub></b><br><b>t<sub>d(off)</sub></b><br><b>t<sub>f</sub></b> | } V <sub>GS</sub> = 10 V, V <sub>DS</sub> = 0.5 • V <sub>DSS</sub> , I <sub>D</sub> = 0.5 • I <sub>D25</sub><br>R <sub>G</sub> = 2.0 Ω (External), |                                                                              | 26           | ns         |    |
|                                                                                                       |                                                                                                                                                    |                                                                              |              | 50         | ns |
|                                                                                                       |                                                                                                                                                    |                                                                              |              | 75         | ns |
|                                                                                                       |                                                                                                                                                    |                                                                              |              | 20         | ns |
| <b>Q<sub>g(on)</sub></b><br><b>Q<sub>gs</sub></b><br><b>Q<sub>gd</sub></b>                            | } V <sub>GS</sub> = 10 V, V <sub>DS</sub> = 0.5 • V <sub>DSS</sub> , I <sub>D</sub> = 0.5 • I <sub>D25</sub>                                       |                                                                              | 180          | nC         |    |
|                                                                                                       |                                                                                                                                                    |                                                                              |              | 39         | nC |
|                                                                                                       |                                                                                                                                                    |                                                                              |              | 100        | nC |
| <b>R<sub>thJC</sub></b>                                                                               |                                                                                                                                                    |                                                                              |              | 0.35 K/W   |    |
| <b>R<sub>thCK</sub></b>                                                                               | TO-247<br>TO-264                                                                                                                                   |                                                                              | 0.25<br>0.15 | K/W<br>K/W |    |


### Source-Drain Diode

### Characteristic Values

( $T_1 = 25^\circ\text{C}$ , unless otherwise specified)


| Symbol                           | Test Conditions                                                                                                | min. | typ.      | max.                            |
|----------------------------------|----------------------------------------------------------------------------------------------------------------|------|-----------|---------------------------------|
| $I_S$                            | $V_{GS} = 0\text{ V}$                                                                                          |      |           | 80                              |
| $I_{SM}$                         | Repetitive; pulse width limited by $T_{JM}$                                                                    |      |           | 320                             |
| $V_{SD}$                         | $I_F = I_S$ , $V_{GS} = 0\text{ V}$ ,<br>Pulse test, $t \leq 300\text{ }\mu\text{s}$ , duty cycle $d \leq 2\%$ |      |           | 1.5                             |
| $t_{rr}$<br>$Q_{RM}$<br>$I_{RM}$ | $I_F = I_S$ -di/dt = $100\text{ A}/\mu\text{s}$ , $V_R = 100\text{ V}$                                         |      | 1.2<br>10 | 200<br>ns<br>$\mu\text{C}$<br>A |

**TO-268AA (D<sup>3</sup> PAK)**




| Dim.           | Millimeter |       | Inches   |      |
|----------------|------------|-------|----------|------|
|                | Min.       | Max.  | Min.     | Max. |
| A              | 4.9        | 5.1   | .193     | .201 |
| A <sub>1</sub> | 2.7        | 2.9   | .106     | .114 |
| A <sub>2</sub> | .02        | .25   | .001     | .010 |
| b              | 1.15       | 1.45  | .045     | .057 |
| b <sub>2</sub> | 1.9        | 2.1   | .75      | .83  |
| C              | .4         | .65   | .016     | .026 |
| D              | 13.80      | 14.00 | .543     | .551 |
| E              | 15.85      | 16.05 | .624     | .632 |
| E <sub>1</sub> | 13.3       | 13.6  | .524     | .535 |
| e              | 5.45 BSC   |       | .215 BSC |      |
| H              | 18.70      | 19.10 | .736     | .752 |
| L              | 2.40       | 2.70  | .094     | .106 |
| L1             | 1.20       | 1.40  | .047     | .055 |
| L2             | 1.00       | 1.15  | .039     | .045 |
| L3             | 0.25 BSC   |       | .010 BSC |      |
| L4             | 3.80       | 4.10  | .150     | .161 |

## TO-247 AD (IXFH) Outline



| Dim. | Millimeter |       | Inches |       |
|------|------------|-------|--------|-------|
|      | Min.       | Max.  | Min.   | Max.  |
| A    | 19.81      | 20.32 | 0.780  | 0.800 |
| B    | 20.80      | 21.46 | 0.819  | 0.845 |
| C    | 15.75      | 16.26 | 0.610  | 0.640 |
| D    | 3.55       | 3.65  | 0.140  | 0.144 |
| E    | 4.32       | 5.49  | 0.170  | 0.216 |
| F    | 5.4        | 6.2   | 0.212  | 0.244 |
| G    | 1.65       | 2.13  | 0.065  | 0.084 |
| H    | -          | 4.5   | -      | 0.177 |
| J    | 1.0        | 1.4   | 0.040  | 0.055 |
| K    | 10.8       | 11.0  | 0.426  | 0.433 |
| L    | 4.7        | 5.3   | 0.185  | 0.209 |
| M    | 0.4        | 0.8   | 0.016  | 0.031 |
| N    | 1.5        | 2.49  | 0.087  | 0.102 |

## TO-264 AA (IXFK) Outline



| Dim. | Millimeter |       | Inches |       |
|------|------------|-------|--------|-------|
|      | Min.       | Max.  | Min.   | Max.  |
| A    | 4.82       | 5.13  | .190   | .202  |
| A1   | 2.54       | 2.89  | .100   | .114  |
| A2   | 2.00       | 2.10  | .079   | .083  |
| b    | 1.12       | 1.42  | .044   | .056  |
| b1   | 2.39       | 2.69  | .094   | .106  |
| b2   | 2.90       | 3.09  | .114   | .122  |
| c    | 0.53       | 0.83  | .021   | .033  |
| D    | 25.91      | 26.16 | 1.020  | 1.030 |
| E    | 19.81      | 19.96 | .780   | .786  |
| e    | 5.46       | BS C  | .215   | BS C  |
| J    | 0.00       | 0.25  | .000   | .010  |
| K    | 0.00       | 0.25  | .000   | .010  |
| L    | 20.32      | 20.83 | .800   | .820  |
| L1   | 2.29       | 2.59  | .090   | .102  |
| P    | 3.17       | 3.66  | .125   | .144  |
| Q    | 6.07       | 6.27  | .239   | .247  |
| Q1   | 8.38       | 8.69  | .330   | .342  |
| R    | 3.81       | 4.32  | .150   | .170  |
| R1   | 1.78       | 2.29  | .070   | .090  |
| S    | 6.04       | 6.30  | .238   | .248  |
| T    | 1.57       | 1.83  | .062   | .072  |

## Min. Recommended Footprint

