

4

3

2

1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

.19


© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00		O	NEW RELEASE	1SEPT99	MM SG



- 1 HOUSING: PBT, UL 94V-0 RATED, COLOR (SEE TABLE)
CONTACTS: PHOSPHOR BRONZE.
SHELL: STEEL.
BOARDLOCKS: BRASS.
THREADED INSERTS: BRASS.
- 2 CONTACTS: GOLD PLATED (SEE TABLE) ON MATING END, 2.54µm[.000100in]
MIN TIN-LEAD ON SOLDER TAILS ALL OVER 1.27µm[.000050in] MIN NICKEL
ON ENTIRE CONTACT.
SHELL: NICKEL PLATED.
BOARDLOCK: TIN OR TIN-LEAD PLATED 2.54µm[.000100in]
THREADED INSERT: NICKEL PLATED 0.76µm[.000030in].
- 3 SPECIFICATIONS:
CURRENT RATING: 2 AMPS. (SIGNAL APPLICATION ONLY)
VOLTAGE RATING: 250 VAC.
DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC(RMS).
INSULATION RESISTANCE: 1000 MEGOHMS MIN.
CONTACT RESISTANCE: 20 MILLIOHMS MAX.
OPERATING TEMPERATURE: -55° TO 105°C.
- 4 DIMENSION IS NON-CUMULATIVE.
5. SPECIFICATIONS SUBJECT TO CHANGES WITHOUT NOTICE.
CONTACT AMP FOR THE LATEST SPECIFICATIONS.



P.C.B. LAYOUT

{1.57 (.062) PC Board Thickness}

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.MORRIS 01SEP99	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: MM		CHK S.GOOD 01SEP99	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S.GOOD 01SEP99	RECEPTACLE ASSEMBLY, 9 POSN, RIGHT ANGLE, 8.08mm[0.318in] SERIES, AMPLIMITE	
0 PLC ± - 1 PLC ± 0.3 2 PLC ± 0.2 3 PLC ± 0.1 4 PLC ANGLES ± -		PRODUCT SPEC SEE NOTES 3	SIZE A3	
MATERIAL SEE NOTES 1		APPLICATION SPEC -	CAGE CODE 00779	
FINISH SEE NOTES 2		WEIGHT -	DRAWING NO C=788750	
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 1	
			REV O	