


1A THREE TERMINAL NEGATIVE VOLTAGE REGULATORS
-5V, -6V, -8V, -9V, -10V, -12V, -15V, -18V, -20V, -24V.

FEATURES

- Suitable for C-MOS, TTL, and the other digital IC power supply.
- Internal thermal overload protecting.
- Internal short circuit current limiting.
- Output current in excess of 1.0A.


MAXIMUM RATINGS (Ta=25 °C)

CHARACTERISTIC		SYMBOL	RATING	UNIT
Input Voltage	KIA7905F ~ KIA7915F	V_{IN}	-35	V
	KIA7918F ~ KIA7924F		-40	
Power Dissipation (Tc=25 °C)		P_D	12	W
Power Dissipation (Without Heatsink)		P_D	1.3	W
Operating Junction Temperature		T_j	-30 ~ 150	°C
Operating Temperature		T_{opr}	-30 ~ 75	°C
Storage Temperature		T_{stg}	-55 ~ 150	°C



KIA7905F~KIA7924F

EQUIVALENT CIRCUIT



KIA7905F~KIA7924F

ELECTRICAL CHARACTERISTICS

KIA7905F

(Unless otherwise specified, $V_{IN}=-10V$, $I_{OUT}=500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN}=2.2\mu F$, $C_{OUT}=1\mu F$)

CHARACTERISTIC	SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage	V _{OUT}	1	T _j =25℃		-5.2	-5.0	-4.8	V
Input Regulation	Reg line	1	T _j =25℃	-12V ≤ V _{IN} ≤ -8V	-	5	50	mV
				-25V ≤ V _{IN} ≤ -7V	-	10	100	
Load Regulation	Reg load	1	T _j =25℃	5mA ≤ I _{OUT} ≤ 1.5A	-	10	100	mV
				250mA ≤ I _{OUT} ≤ 750mA	-	3	50	
Output Voltage	V _{OUT}	1	-20V ≤ V _{IN} ≤ -7V 5mA ≤ I _{OUT} ≤ 1.0A		-5.25	-5.0	-4.75	V
Quiescent Current	I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	ΔI _{BI}	1	-25V ≤ V _{IN} ≤ -8V		-	0.1	1.3	mA
	ΔI _{BO}		5mA ≤ I _{OUT} ≤ 1.0A		-	0.05	0.5	
Output Noise Voltage	V _{NO}	2	Ta=25℃, 10Hz ≤ f ≤ 100kHz		-	100	-	μV _{rms}
Ripple Rejection Ratio	RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit	I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage	T _{CVO}	1	I _{OUT} =5.0mA		-	-0.4	-	mV/℃
Dropout Voltage	V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905F~KIA7924F

ELECTRICAL CHARACTERISTICS

KIA7906F

(Unless otherwise specified, $V_{IN}=-11V$, $I_{OUT}=500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN}=2.2\mu F$, $C_{OUT}=1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-6.25	-6.0	-5.75	V
Input Regulation		Reg line	1	T _j =25℃	-13V ≤ V _{IN} ≤ -9V	-	5	60	mV
					-25V ≤ V _{IN} ≤ -8V	-	10	120	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤ I _{OUT} ≤ 1.5A	-	10	120	mV
					250mA ≤ I _{OUT} ≤ 750mA	-	3	60	
Output Voltage		V _{OUT}	1	-21V ≤ V _{IN} ≤ -9V 5mA ≤ I _{OUT} ≤ 1.0A		-6.3	-6.0	-5.7	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-25V ≤ V _{IN} ≤ -9V		-	-	1.3	mA
	Load	ΔI _{BO}		5mA ≤ I _{OUT} ≤ 1.0A		-	-	0.5	
Output Noise Voltage		V _{NO}	2	Ta=25℃, 10Hz ≤ f ≤ 100kHz		-	130	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-0.5	-	mV/℃
Dropout Voltage		V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905F~KIA7924F

ELECTRICAL CHARACTERISTICS

KIA7908F

(Unless otherwise specified, $V_{IN}=-14V$, $I_{OUT}=500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN}=2.2\mu F$, $C_{OUT}=1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-8.3	-8.0	-7.7	V
Input Regulation		Reg line	1	T _j =25℃	-17V ≤V _{IN} ≤-11V	-	5	80	mV
					-25V ≤V _{IN} ≤-10.5V	-	10	100	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤I _{OUT} ≤1.5A	-	12	160	mV
					250mA ≤I _{OUT} ≤750mA	-	4	80	
Output Voltage		V _{OUT}	1	-23V ≤V _{IN} ≤-11.5V 5mA ≤I _{OUT} ≤1.0A		-8.4	-8.0	-7.6	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-25V ≤V _{IN} ≤-11.5V		-	0.1	1.0	mA
	Load	ΔI _{BO}		5mA ≤I _{OUT} ≤1.0A		-	0.05	0.5	
Output Noise Voltage		V _{NO}	2	Ta=25℃, 10Hz ≤f ≤100kHz		-	175	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-0.6	-	mV/℃
Dropout Voltage		V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905F~KIA7924F

ELECTRICAL CHARACTERISTICS

KIA7909F

(Unless otherwise specified, $V_{IN}=-15V$, $I_{OUT}=500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN}=2.2\mu F$, $C_{OUT}=1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-9.3	-9.0	-8.7	V
Input Regulation		Reg line	1	T _j =25℃	-19V ≤ V _{IN} ≤ -13V	-	5	90	mV
					-26V ≤ V _{IN} ≤ -11.5V	-	10	100	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤ I _{OUT} ≤ 1.5A	-	10	150	mV
					250mA ≤ I _{OUT} ≤ 750mA	-	5	120	
Output Voltage		V _{OUT}	1	-24V ≤ V _{IN} ≤ -11.5V 5mA ≤ I _{OUT} ≤ 1.0A		-9.4	-9.0	-8.6	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-26.5V ≤ V _{IN} ≤ -13V		-	0.1	1.0	mA
	Load	ΔI _{BO}		5mA ≤ I _{OUT} ≤ 1.0A		-	0.05	0.5	
Output Noise Voltage		V _{NO}	2	Ta=25℃, 10Hz ≤ f ≤ 100kHz		-	180	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-0.7	-	mV/℃
Dropout Voltage		V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905F~KIA7924F

ELECTRICAL CHARACTERISTICS

KIA7910F

(Unless otherwise specified, $V_{IN}=-16V$, $I_{OUT}=500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN}=2.2\mu F$, $C_{OUT}=1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-10.4	-10	-9.6	V
Input Regulation		Reg line	1	T _j =25℃	-20V ≤V _{IN} ≤-14V	-	5	100	mV
					-27V ≤V _{IN} ≤-12.5V	-	10	110	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤I _{OUT} ≤1.5A	-	10	180	mV
					250mA ≤I _{OUT} ≤750mA	-	6	120	
Output Voltage		V _{OUT}	1	-25V ≤V _{IN} ≤-12.5V 5mA ≤I _{OUT} ≤1.0A		-10.5	-10	-9.5	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-27.5V ≤V _{IN} ≤-14V		-	0.1	1.0	mA
	Load	ΔI _{BO}		5mA ≤I _{OUT} ≤1.0A		-	0.05	0.5	
Output Noise Voltage		V _{NO}	2	Ta=25℃, 10Hz≤f≤100kHz		-	190	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-0.7	-	mV/℃
Dropout Voltage		V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905F~KIA7924F

ELECTRICAL CHARACTERISTICS

KIA7912F

(Unless otherwise specified, $V_{IN}=-18V$, $I_{OUT}=500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN}=2.2\mu F$, $C_{OUT}=1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-12.5	-12	-11.5	V
Input Regulation		Reg line	1	T _j =25℃	-22V ≤ V _{IN} ≤ -16V	-	6	120	mV
					-30V ≤ V _{IN} ≤ -14.5V	-	12	240	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤ I _{OUT} ≤ 1.5A	-	12	240	mV
					250mA ≤ I _{OUT} ≤ 750mA	-	4	120	
Output Voltage		V _{OUT}	1	-27V ≤ V _{IN} ≤ -15.5V 5mA ≤ I _{OUT} ≤ 1.0A		-12.6	-12	-11.4	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-30V ≤ V _{IN} ≤ -15V		-	0.1	1.0	mA
	Load	ΔI _{BO}		5mA ≤ I _{OUT} ≤ 1.0A		-	0.05	0.5	
Output Noise Voltage		V _{NO}	2	Ta=25℃, 10Hz ≤ f ≤ 100kHz		-	200	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-0.8	-	mV/℃
Dropout Voltage		V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905F~KIA7924F

ELECTRICAL CHARACTERISTICS

KIA7915F

(Unless otherwise specified, $V_{IN}=-23V$, $I_{OUT}=500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN}=2.2\mu F$, $C_{OUT}=1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-15.6	-15	-14.4	V
Input Regulation		Reg line	1	T _j =25℃	-26V ≤V _{IN} ≤-20V	-	6	150	mV
					-30V ≤V _{IN} ≤-17.5V	-	12	300	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤I _{OUT} ≤1.5A	-	12	300	mV
					250mA ≤I _{OUT} ≤750mA	-	4	150	
Output Voltage		V _{OUT}	1	-30V ≤V _{IN} ≤-18V 5mA ≤I _{OUT} ≤1.0A		-15.75	-15	-14.25	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-30V ≤V _{IN} ≤-17.5V		-	0.1	1.0	mA
	Load	ΔI _{BO}		5mA ≤I _{OUT} ≤1.0A		-	0.05	0.5	
Output Noise Voltage		V _{NO}	2	Ta=25℃, 10Hz ≤f ≤100kHz		-	250	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-0.9	-	mV/℃
Dropout Voltage		V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905F~KIA7924F

ELECTRICAL CHARACTERISTICS

KIA7918F

(Unless otherwise specified, $V_{IN}=-27V$, $I_{OUT}=500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN}=2.2\mu F$, $C_{OUT}=1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-18.7	-18	-17.3	V
Input Regulation		Reg line	1	T _j =25℃	-30V ≤ V _{IN} ≤ -24V	-	8	180	mV
					-33V ≤ V _{IN} ≤ -21V	-	15	360	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤ I _{OUT} ≤ 1.5A	-	15	360	mV
					250mA ≤ I _{OUT} ≤ 750mA	-	5	180	
Output Voltage		V _{OUT}	1	-33V ≤ V _{IN} ≤ -22.5V 5mA ≤ I _{OUT} ≤ 1.0A		-18.85	-18	-17.15	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-33V ≤ V _{IN} ≤ -22V		-	-	1.0	mA
	Load	ΔI _{BO}		5mA ≤ I _{OUT} ≤ 1.0A		-	-	0.5	
Output Noise Voltage		V _{NO}	2	Ta=25℃, 10Hz ≤ f ≤ 100kHz		-	300	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-1.0	-	mV/℃
Dropout Voltage		V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905F~KIA7924F

ELECTRICAL CHARACTERISTICS

KIA7920F

(Unless otherwise specified, $V_{IN}=-30V$, $I_{OUT}=500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN}=2.2\mu F$, $C_{OUT}=1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25 °C		-20.8	-20	-19.2	V
Input Regulation		Reg line	1	T _j =25 °C	-32V ≤V _{IN} ≤-26V	-	10	180	mV
					-35V ≤V _{IN} ≤-24V	-	18	360	
Load Regulation		Reg load	1	T _j =25 °C	5mA ≤I _{OUT} ≤1.5A	-	18	360	mV
					250mA ≤I _{OUT} ≤750mA	-	10	180	
Output Voltage		V _{OUT}	1	-35V ≤V _{IN} ≤-24 5mA ≤I _{OUT} ≤1.0A		-21.0	-20	-19.0	V
Quiescent Current		I _B	1	T _j =25 °C		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-36.5V ≤V _{IN} ≤-25V		-	-	1.0	mA
	Load	ΔI _{BO}		5mA ≤I _{OUT} ≤1.0A		-	-	0.5	
Output Noise Voltage		V _{NO}	2	Ta=25 °C, 10Hz ≤f ≤100kHz		-	350	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25 °C		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-1.0	-	mV/ °C
Dropout Voltage		V _D	1	T _j =25 °C, I _{OUT} =1A		-	2.0	-	V

KIA7905F~KIA7924F

ELECTRICAL CHARACTERISTICS

KIA7924F


(Unless otherwise specified, $V_{IN}=-33V$, $I_{OUT}=500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN}=0.33\mu F$, $C_{OUT}=0.1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-25	-24	-23	V
Input Regulation		Reg line	1	T _j =25℃	-36V ≤ V _{IN} ≤ -30V	-	8	240	mV
					-38V ≤ V _{IN} ≤ -27V	-	15	480	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤ I _{OUT} ≤ 1.5A	-	15	480	mV
					250mA ≤ I _{OUT} ≤ 750mA	-	5	240	
Output Voltage		V _{OUT}	1	-38V ≤ V _{IN} ≤ -27V 5mA ≤ I _{OUT} ≤ 1.0A		-25.2	-24	-22.5	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-38V ≤ V _{IN} ≤ -27V		-	-	1.0	mA
	Load	ΔI _{BO}		5mA ≤ I _{OUT} ≤ 1.0A		-	-	0.5	
Output Noise Voltage		V _{NO}	2	Ta=25℃, 10Hz ≤ f ≤ 100kHz		-	400	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-1.0	-	mV/℃
Dropout Voltage		V _D	1	T _a =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905F~KIA7924F

TEST CIRCUIT

V_{OUT} , Reg · Line, Reg · Load, I_B , ΔI_B , V_D , T_{CVO}




Notes : (1) To specify an output voltage, substitute voltage value for "XX"


(2) Required for stability. For value given, capacitor must be solid tantalum. If aluminum electrolytics are used, at least ten times value shown should be selected. C_1 is required if regulator is located an appreciable distance from power supply filter.

(3) To improve transient response. If large capacitors are used, a high current diode from input to output (1N4001 or similar) should be introduced to protect the device from momentary input short circuit.

2. V_{NO}




3. R · R




KIA7905F~KIA7924F


$I_B - T_j$




$V_{OUT} - T_j$




$RR - I_{OUT}$



$I_{SC} - V_{IN}$



$V_D - T_j$



$P_D - T_a$

