

Product Facts

- Small, lightweight, fan-cooled unit
- Small profile for installation where space is restricted
- Handheld operation
- Focused heat
- Quiet, efficient IR operation
- CE approved

Applications

Used for installing SolderSleeve devices and SolderTacts contacts.

IR-1759 MiniRay Infrared Heating Tool



* Control box not shown

Specifications and Dimensions

Lamp	Tungsten-halogen
Fan	Nominal power 250 W, 24 Vac, 50–60 Hz
Weight	12 Vac (supplied through control unit)
Cable length	.73 kg [1.6 lb]
Electronic Control Unit	
Main supply	2 m [6.5 ft]
Weight	110/230 Vac, 50/60 Hz, 11 A/5.5A universal
Dimensions	3.4 kg [7.6 lb]
	16.3 x 12.2 x 12.2 cm [6.4 x 4.8 x 4.8 in]

Ordering Information

Description	Part No.
Complete kit consisting of: Handtool/Reflector/Control Box (Manual control, Dual voltage)	IR1759-MK4-AT3130-EDCont CF0024-000

Accessories and Replacement Parts

Handtool, standard aperture	IR-1759-MK4/A	CF0025-000
Handtool, large aperture	IR-3104-MK4/A	CF5497-000
Control box with time control-230 V	ED-7-001-MK4-230V-50HZ	CF0199-000
Control box with time control-110 V	ED-7-002-MK4-110V-60HZ	CF0201-000
Control box with manual control-110/230V	ED-7-CONT-230/110V-MK4	CF0026-000
Battery powered control box	ED-7-Battbox-MK4-230/110V	CF0200-000
Conversion kit (AE-897) for adapting standard-aperture MiniRay heating tool to wide-aperture MiniRay tool (includes reflector)	AT-313/AE-897	934630-000
Inner reflector (standard aperture)	AE-424	547918-000
Inner reflector (wide aperture)	AE-153	988285-000
Lamp (250 W, 24 V)	NAE-143-3	988208-000
Filter (standard aperture)	AES-IR1759-100-FILTER-DUL	431468-000
Filter (large aperture)	AES-IR1759-300-FLTR-LRG	F52511-000

*IR tools are not recommended for use with black wire or cable insulations.

Available in:	Americas	Europe	Asia Pacific
	■	■	■