




Copyright FCI.



D

CATALOGUE NUMBER
7434L0825S01
7434L0825S01LF *

* - LEAD FREE version



Crimping part to use with a thickness PCB of 1.6
holes $\varnothing = 3.2^{+0.1}_0$





LEAD FREE VERSION:

"This product meets European Union Directives and other country regulations as described in GS-22-008"


The housing will withstand exposure to 260°C peak temperature for 10 seconds in a wave solder application with a 1.6mm minimum thick circuit board

REV F - 2006-04-17


2



IMPLANTATION C.1 PCB FOOTPRINT



Tol Gen: 0mm to 10mm ± 0.1 mm
10mm to 30mm ± 0.15 mm
30mm to 60mm ± 0.2 mm
60mm and above ± 0.3 mm

www.fciconnect.com			surface - 		tolerance std ISO:1302 ISO:406 ISO:1101		projection 		MM 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	D.LEGRAND	2002/04/29	ANGULAR	LINEAR	0.X	±	size A3	Scale 3:2		
Eng	F.TISSERAND	2002/04/29			0.XX	±				
Chr	S.S.CHERIAN	2008/06/28			0.XXX	±				
Appr	S.S.CHERIAN	2008/06/28	0°	±°	Product family SMARTCARD		ECN 108-0080		Spec ref -	
			title SMARTCARD ASSEMBLY			dwg no VJWI2132			Rev. D	
			L08-16 CONTACTS - 8 CONTACTS							
			catalog no SEE TABLE			CUSTOMER			sheet 1 of 1	