


PRODUCT NUMBER
SEE TABLE

1 | 2

3 |

4



NOTES:

- ① THIS LENGTH OF PIN TO BE FREE OF NICKS, TOOL MARKS, AND PLASTIC SLIVERS.
- ② PIN RETENTION TO BE 3.00 Lbs/1.36 Kgs MIN PER PIN IN EITHER DIRECTION.
- ③ TERMINAL PLATING: SEE PRODUCT TABLE
- ④ MOLDING MAT'L: MIN 20% GLASS FILLED POLYESTER PER UL-94-VO, COLOR: BLACK.
- ⑤ DIM D =:
(NO. OF COLUMNS -1) TIMES .100 [ENGLISH].
(NO. OF COLUMNS -1) TIMES 2.54 [METRIC].
- ⑥ TERMINAL MATERIAL - 3/4 HARD PHOS BRONZE PER UL-94-VO, COLOR : BLACK.

7. 1 THRU 4 POSITIONS ARE NOT AVAILABLE
5 THRU 100 POSITIONS ARE AVAILABLE

mat'l. code NOTE 4 & 6				tolerances unless otherwise specified		CUSTOMER COPY	title	www.fciconnect.com
ltr	ecn no	dr	date	linear	angles			
P				.XX±.01/.X ±.3 .XXX±.005/.XX ±.10 .XXXX±.0020/.XXX ±.050	σ ±Z	projection	RIGHT ANGLE 2 ROW GUIDE PIN HEADER, POL	
				dr J.W.BAIR 9/7/90	dr J.W.BAIR 9/7/90	INCH/MM	product family HEADERS	code 213
				engr S.AURAND 9/7/90	engr S.AURAND 9/7/90	size	dwg no	sheet 2 of
				chr S.AURAND 9/7/90	chr S.AURAND 9/7/90	scale		
				appd S.AURAND 9/7/90	appd S.AURAND 9/7/90	2/1	A4	68535
sheet	revision							
index	sheet							

1 | 2

ACAD

PDM: Rev:P

3 |

STATUS: Released

cage code 22526
Printed Aug 02, 2002

4

All rights strictly reserved. Reproduction or issue to third parties in any format whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

Tous droits réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de CFCI. Droits de reproduction FCII.

1 | 2

3

4

PRODUCT NUMBER	SIZE	DIM D	DIM F	DIM E	OVERALL LENGTH DIM L	PLATING	PIN OMITTED	
68535-130	2 x 30	NOTE 5	.37/9.4 + DIM D	.40/10.2 + DIM D	.48/12.2 + DIM D	DUPLEX 15u"/.38u Au & 100u"/2.54u MIN 60/40 SnPb OVER 50u"/1.27 Ni	A3	
68535-230	2 x 30	NOTE 5	.37/9.4 + DIM D	.40/10.2 + DIM D	.48/12.2 + DIM D	DUPLEX 15u"/.38u Au & 100u"/2.54u MIN 60/40 SnPb OVER 50u"/1.27 Ni	B3	
68535-330	2 x 30	NOTE 5	.37/9.4 + DIM D	.40/10.2 + DIM D	.48/12.2 + DIM D	DUPLEX 15u"/.38u Au & 100u"/2.54u MIN 60/40 SnPb OVER 50u"/1.27 Ni	A30	

4
ECL

mat'l. code NOTE 4 & 6				tolerances unless otherwise specified		CUSTOMER COPY	 FCI www.fciconnect.com		
ltr	ecn no	dr	date	.xx±.01 / x ±.3	.xxx±.005 / .xx ±.10				
P				linear	.xxxx±.0020 / .xxx ±.050	projection	title  RIGHT ANGLE 2 ROW GUIDE PIN HEADER, POL		
				angles	o' ±2°				
		dr	J.W.BAIR	9/7/90		product family	HEADERS	code 213	
		engr	S.AURAND	9/7/90		size	dwg no		
		chr	S.AURAND	9/7/90	scale	2/1	A4 	68535	sheet 3 of
		oppd	S.AURAND	9/7/90					
sheet index	revision sheet								

1 2

ACAD

PDM: Rev:P

3 STATUS: Released

cage code
Printed: Apr 02, 2002

4