






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AA	00		E	REV PER 0S15-0134-05	29SEP2005	RG JW
			F	ECO-08-000390	10JAN2008	LAM JW



1. MATERIAL:
HOUSING - HIGH TEMPERATURE THERMOPLASTIC, PER UL94V-0, COLOR: BLACK
TERMINALS - .014 THICK PHOSPHOR BRONZE.
PLATING - 50 MICRO INCHES GOLD IN CONTACT AREA 150 MICRO INCHES TIN-LEAD ON SOLDER TAILS, ALL OVER 50 MICRO INCHES OF NICKEL.
SHIELD - .0077 THICK COPPER-ZINC ALLOY, PREPLATED WITH 50 MICRO INCHES MINIMUM SATIN NICKEL WITH 80 MICRO INCHES MINIMUM TIN POST DIPPED ON PCB GROUND TABS.
2. JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68, SUBPART F.
3. RJ45 MOD PLUG SELECTIVE - THIS CONNECTOR UTILIZES 2 STAINLESS STEEL SPRING MEMBERS WHICH PREVENT THE INSERTION OF A RJ11 (6 POSITION) PLUG INTO THE JACK PORT, WHILE ALLOWING A RJ45 (8 POSITION) PLUG TO MATE FREELY.
- WARNING: THIS FEATURE WAS DEVELOPED FOR TYPICAL PLUG INSERTION FORCES. EXCESSIVE INSERTION FORCE MAY OVERCOME THE SELECTIVE FEATURES AND DAMAGE THE CONNECTOR.



AMP 1471-9 REV 31MAR2000

Pro/ENGINEER DRAWING

1364288-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN A. HASIRCIOGLU 07FEB00	tyco Electronics		Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK D. DIXON 25MAY00	NAME INVERTED MODULAR JACK ASSEMBLY, 1X1, SHIELDED, PANEL GROUNDS, RJ45 MOD PLUG SELECTIVE CAPABILITY			
		APVD D. SUMMERS 25MAY00	PRODUCT SPEC 108-1163-4			
		APPLICATION SPEC 114-2154				
MATERIAL SEE NOTE 1	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±.01 3 PLC ±.005 4 PLC ± ANGLES ±1° FINISH	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO 1364288	RESTRICTED TO -
SEE NOTE 1		CUSTOMER DRAWING		SCALE 3:1	SHEET 1	OF 1
				REV F		