



Dimensions: mm

Specifications :

- Input impedance: 1M Ω
- Width of minimum pulse: 30 nsec
- Maximum input frequency: 17 MHz
- Measurable logic gate: TTL and CMOS
 - Logic 1 (red LED lights) and then buzz.
 - 2.3 V \pm 0.2 V 70% Vcc
 - Logic 0 (green LED lights) and then buzz.
 - 0.8 V \pm 0.2 V 30% Vcc
- Input overvoltage protection: \pm 220 VDC/VAC 15 sec
- Pulse (yellow LED) flashing time 500 msec
- Power supply protection: \pm 20 V

383-LP2817

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

PSP:

[383-LP2817](#)