




APPLICATOR No. 69037-1196
PRODUCT No. 43030/31 20-24 AWG



ITEM	PART NUMBER	DESCRIPTION
1	69037-0163	SHEAR PUNCH
2	69037-0031	SHEAR DIE
3	69039-1577	CONDUCTOR PUNCH
4	69039-3129	CONDUCTOR ANVIL
5	69039-2571	INSULATION PUNCH
6	69039-4560	INSULATION ANVIL
7	69037-2196	TOOL KIT (ITEMS 3 - 6)

CRIMP SPECIFICATION: (SEE ALSO PRODUCT SPEC. CS.43030/31)

WIRE mm2 (AWG)	CRIMP HEIGHT (COND)	PULL FORCE (MIN)
0.50 (20)	0.91/0.99mm (.036"/.039")	SEE PRODUCT SPEC.
0.35 (22)	0.84/0.91mm (.033"/.036")	SEE PRODUCT SPEC.
0.22 (24)	0.79/0.84mm (.031"/.033")	SEE PRODUCT SPEC.

WIRE STRIP LENGTH: - 2.5 / 2.9 mm (.100" / 0.115")