





MICRO SWITCH
a Honeywell Division

FED.MFG.CODE 91929

MINIATURE PRECISION LIMIT SWITCH

CATALOG LISTING

914CE2-6K




NOTES

1 - ZINC HOUSING FINISHED WITH GRAY PAINT

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CHARACTERISTICS

OPERATING FORCE — — — — 5 LB MAX
DIFFERENTIAL TRAVEL — — — — .004 MAX
OVERTRAVEL — — — — .118 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

5A 1/10HP 125 OR 250 VAC



SCALE FULL

DO NOT
SCALE PRINT

**UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE**

ONE PLACE (.0) ± .030

TWO PLACE (.00) ± .015

THREE PLACE (.000) ± .005

ANGLES ±

WEIGHT

914CE2-6K

M

DRAWING
NUMBER

2

ISSUE

REVISIONS

A CO-69061
S A V
31 AUG 91

CHECK

CHECK

14 NOV 91

DAW

CHECK

91

SAV 13 SEPT 91

DDM/CAD
DRAWN