



Features

- Multiple applications: parallel, series, dual-inductor and transformer
- Magnetically shielded, low radiation
- Inductance range: 0.47 to 4000 μ H
- Rated current up to 17.6 A
- RoHS compliant*

Applications

- SEPIC topology
- Power supplies for:
 - Communication equipment
 - Notebooks, desktop computers, servers
 - LCDs, flat panels, backlights
 - Camcorders, HDTVs, car audio systems

SRF1260 Series - Dual-Winding Shielded Power Inductors

Electrical Specifications @ 25 °C

Bourns Part No.	Parallel Rating					Series Rating				
	Inductance @ 100 KHz L (μ H)	Tol. (%)	DCR (Ω) Max.	Irms (A)	Isat (A)	Inductance @ 100 KHz L (μ H)	Tol. (%)	DCR (Ω) Max.	Irms (A)	Isat (A)
SRF1260-R47Y	0.47	± 30	0.0053	17.6	33	1.88	± 30	0.0212	8.8	16.5
SRF1260-1R0Y	1.0	± 30	0.0062	15	23.6	4	± 30	0.026	7.51	11.8
SRF1260-1R5Y	1.5	± 30	0.0073	13.8	18.3	6	± 30	0.0302	6.89	9.15
SRF1260-2R2Y	2.2	± 30	0.0085	10.9	15	8.8	± 30	0.0333	5.46	7.5
SRF1260-3R3Y	3.3	± 30	0.0101	9.26	12.7	13.2	± 30	0.0372	4.63	6.35
SRF1260-4R7Y	4.7	± 30	0.0137	7.18	9.71	18.8	± 30	0.0479	3.59	4.86
SRF1260-6R8Y	6.8	± 30	0.0186	6.64	8.68	27.2	± 30	0.0672	3.32	4.34
SRF1260-8R2Y	8.2	± 30	0.0194	5.54	7.86	32.8	± 30	0.0737	2.77	3.93
SRF1260-100M	10	± 20	0.0246	5.35	7.17	40	± 20	0.0934	2.67	3.59
SRF1260-150M	15	± 20	0.0329	4.27	5.69	60	± 20	0.125	2.13	2.85
SRF1260-220M	22	± 20	0.0451	3.7	4.71	88	± 20	0.172	1.84	2.36
SRF1260-330M	33	± 20	0.0618	3.28	3.84	132	± 20	0.256	1.64	1.92
SRF1260-470M	47	± 20	0.086	2.71	3.24	188	± 20	0.34	1.35	1.62
SRF1260-680M	68	± 20	0.117	2.22	2.7	272	± 20	0.444	1.11	1.35
SRF1260-820M	82	± 20	0.15	2.05	2.39	328	± 20	0.568	1.03	1.2
SRF1260-101M	100	± 20	0.171	1.78	2.2	400	± 20	0.656	0.892	1.1
SRF1260-151M	150	± 20	0.254	1.48	1.81	600	± 20	0.972	0.739	0.905
SRF1260-221M	220	± 20	0.354	1.19	1.51	880	± 20	1.416	0.594	0.755
SRF1260-331M	330	± 20	0.574	1.06	1.22	1320	± 20	2.29	0.53	0.61
SRF1260-471M	470	± 20	0.83	0.87	1.02	1880	± 20	3.197	0.434	0.51
SRF1260-681M	680	± 20	1.212	0.7	0.85	2720	± 20	4.635	0.35	0.425
SRF1260-821M	820	± 20	1.46	0.6	0.77	3280	± 20	5.363	0.301	0.385
SRF1260-102M	1000	± 20	1.854	0.57	0.7	4000	± 20	6.782	0.283	0.35

General Specifications

Test Voltage.....0.25 V
 Hi-pot.....500 Vrms, 3 mA, 3 sec.
 Reflow Soldering .. 230 °C; 50 sec. max.
 Operating Temperature
 -40 °C to +125 °C
 (Temperature rise included)
 Storage Temperature .. -40 °C to +125 °C
 Resistance to Solder Heat
 +260 °C for 10 sec.

Materials


Core.....Ferrite
 Wire.....Enameled copper
 Base.....LCP
 Adhesive.....Epoxy resin
 Terminal.....Sn
 Rated Current
 Inductance drops 30 % at Isat
 Temperature Rise40 °C at rated I rms
 Packaging..... 400 pcs. per 13-inch reel

How to Order


SRF1260 - 100M

Model _____
 Value Code (see table) _____


Electrical Schematic



Recommended Layout



Product Dimensions



*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.


Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

SRF1260 Series - Dual-Winding Shielded Power Inductors

BOURNS®

Packaging Specifications



BOURNS®

Asia-Pacific: Tel: +886-2 2562-4117 • Fax: +886-2 2562-4116

Europe: Tel: +41-41 768 5555 • Fax: +41-41 768 5510

The Americas: Tel: +1-951 781-5500 • Fax: +1-951 781-5700

www.bourns.com

REV. 06/13

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.