


SAW FILTER FOR UMTS BC9 Rx

Murata part number : SAFEA1G86FL0F00

Package Dimensions





Specification

Item	Specification		
	-30 to 85°C	25±2°C	typ.
Nominal Center Frequency(fc)	1862.45MHz		
Insertion Loss (1844.9 to 1880.5MHz)	2.4 dB max.	2.2 dB max.	2.0 dB
Absolute Attenuation			
1) at 95MHz	60 dB min.	60 dB min.	88 dB
2) 1654.9 to 1690 MHz	35 dB min.	35 dB min.	55 dB
3) 1749.9 to 1785 MHz	35 dB min.	35 dB min.	46 dB
4) 1925 to 1950 MHz	15 dB min.	15 dB min.	24 dB
5) 1950 to 1970 MHz	25 dB min.	25 dB min.	39 dB
6) 3404 to 3475 MHz	30 dB min.	30 dB min.	46 dB
7) 3594 to 3665 MHz	30 dB min.	30 dB min.	46 dB
8) 3689 to 3760 MHz	30 dB min.	30 dB min.	46 dB
9) 5344 to 5450 MHz	30 dB min.	30 dB min.	42 dB
10) 5534 to 5640 MHz	30 dB min.	30 dB min.	41 dB
11) 7094 to 7235 MHz	30 dB min.	30 dB min.	44 dB
12) 7379 to 7520 MHz	30 dB min.	30 dB min.	45 dB
Ripple Deviation (1844.9 to 1880.5MHz)	0.8dB max.	0.8dB max.	0.4 dB
VSWR (1844.9 to 1880.5MHz)	1.8 max.	1.8 max.	1.5
Amplitude Balance (1844.9 to 1880.5MHz)	±1.0dB max.	±1.0dB max.	+0.4dB
Phase Balance (1844.9 to 1880.5MHz)	180±10deg. max.	180±10deg. max.	180+4deg.
Input Impedance (nominal)	50Ω		
Output Impedance (nominal)	200Ω//33nH		
Input Signal Level	20mW (+13dBm), 2000 hours		


SAW FILTER FOR UMTS BC9 Rx

Murata part number : SAFEA1G86FL0F00


Frequency Performance



Amplitude balance




Phase balance




SAW FILTER FOR UMTS BC9 Rx

Murata part number : SAFEA1G86FL0F00

Recommended Land Pattern



Test Circuit



- This PDF Datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- This PDF Datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.