

TM-22 Support Brace Hanging Lid



■ Specification

Model No.	Type	Allowable Load N (kgf)	Net Weight (g)	Code No.
TM-22-L	Left	39.2 (4)	27.5	5001
TM-22-R	Right	39.2 (4)	27.5	5002

■ Parts List


No.	Part Name	Material	Finish	Quantity
1	Bracket (A)	BSP	Ni	1
2	Bracket (B)			1
3	Rivet	BSBM	—	3
4	Washer	PA		3
5	Arm	BSP	Ni	2
6	Stopper			1

■ Characteristic

No wide spaces to install.

■ Application

Measuring instruments /
Telecommunication devices



The figure shows left side fixing type.

TM-30 Support Brace Hanging Lid



■ Specification

Model No.	Type	Allowable Load N (kgf)	Net Weight (g)	Code No.
TM-30-L	Left	128 (13)	31	5015
TM-30-R	Right	128 (13)	31	5016

■ Parts List

No.	Part Name	Material	Finish	Quantity
1	L Plate	SPCC	Cr	1
2	Shaft	C2700	Sn-Co (Cr Color)	3
3	Arm	SPCC	Cr	2
4	Washer	PA	—	3
5	Oval Plate	SPCC	Cr	1

■ Characteristic


No wide spaces to install.

■ Application

Measuring instruments /
Telecommunication devices

■ Note

Beveling must be processed to the attached side
when using countersunk screws or rivets.



This figure shows for left side fixing type.