



Magnetic properties	Conditions	Min	Typ	Max	Unit
Pull-In	at 20°C	30		49	AT
Test equipment				KMS13+PK002+SA002	

Special Product Data	Conditions	Min	Typ	Max	Unit
Contact - No.			75		
Contact - form			A - NO		
Contact rating	Any DC combination of V & A not to exceed their individual max.'s			10	W
Switching voltage	DC or Peak AC			500	V
Carry current	DC or Peak AC			1	A
Switching current	DC or Peak AC			0,5	A
Sensor-resistance	measured with 40% overdrive			450	mOhm
Housing material			PBT glass fibre reinforced		
Case colour			white		
Sealing compound			Polyurethan		

Environmental data	Conditions	Min	Typ	Max	Unit
Shock	1/2 sine wave duration 11ms			50	g
Vibration	from 10 - 2000 Hz			20	g
Operating temperature	cable not moved	-30		70	°C
Operating temperature	cable moved	-5		70	°C
Storage temperature		-30		70	°C
Reach / RoHS conformity			yes		

General data	Conditions	Min	Typ	Max	Unit
Mounting advice		over 5m cable, a resistor is recommended.			