


# MOD6320-T

## WirelessHD® Transmitter Module

The MOD6320-T/MOD6320-4K-T is a WirelessHD module for highly integrated video source devices and transmitter adapters built with SiBEAM® technology. The transmitter module provides a digital audio/video interface compatible with HDMI®, enabling wireless transmission of high quality video to any WirelessHD-compliant receiver. WirelessHD effectively eliminates unsightly cable installation, while maintaining the same visual quality and reliability.



### Applications

- Wireless video transmit adapter
- Medical source and displays
- Industrial source and displays
- Blu-ray player
- Set-top boxes

### Key Features

- WirelessHD v1.1 compliant
- 60 GHz wireless video free from interference
- MOD6320-T supports maximum video resolution 1080p/60Hz
- MOD6320-4K-T supports maximum resolution 1080p/120Hz or 4K30 when used with SiI9396 HDMI bridge device<sup>1</sup>
- Average 5 ms video latency, ideal for real-time video delivery
- Surround sound audio
- CEC or AVC commands
- HDCP content protection

### Benefits Summary

- Quick time-to-market
- Sub-frame latency
- Ease of use and installation

### Industry-Standard Compliance

- WirelessHD Specification v1.1
- HDMI 1.4b / 2.0
- HDCP 1.4 / 2.2

### Digital Input/Output

- HDMI
- USB for debug
- I<sup>2</sup>C for advanced control

### Wireless Range

- Up to 10 m in-room

### Operating Frequency

- 59.40 GHz to 63.72 GHz
- Channels 2 and 3

### Operating Temperature

- 0 to 60 °C ambient temperature

### Modular Regulatory Approval

- IC (Canada)
- SRRC (China)
- ETSI (EU)
- KCC (Korea)
- TELEC (Japan)
- FCC (USA)

### Module Dimensions

- 74 mm x 17 mm x 5.4 mm
- Cable length 30 mm

### Ordering Information

Part Number: MOD6320-T  
Part Number: MOD6320-T-C\*

Part Number: MOD6320-4K-T<sup>1</sup>  
Part Number: MOD6320-4K-T-C\*<sup>1</sup>

All parts include module.

\* Also Includes cable

<sup>1</sup> 4K modules require SiI9396 device. Please order separately.

### Applications Support

[www.latticesemi.com/support](http://www.latticesemi.com/support)

© 2017 Lattice Semiconductor Corporation and/or its affiliates. All rights reserved. SiBEAM, WirelessHD and HDMI are trademarks, registered trademarks or service marks of Lattice Semiconductor Corporation and/or its affiliates in the United States and/or other countries. All other trademarks and registered trademarks are the property of their respective owners in the United States and/or other countries.


May 2017  
Order #: SPB001 Rev.4



# MOD6321-R

## WirelessHD<sup>®</sup> Receiver Module

The MOD6321-R/MOD6321-4K-R is a WirelessHD module for highly integrated display devices and receiver adapters built with SiBEAM<sup>®</sup> technology. The receiver module provides a digital audio/video interface compatible with HDMI<sup>®</sup>, which allows reception of high quality video from any WirelessHD-compliant transmitter. WirelessHD effectively eliminates unsightly cable installation, while maintaining the same visual quality and reliability.



### Applications

- Wireless video receive adapter
- Medical displays
- Industrial displays
- Video projector

### Key Features

- WirelessHD v1.1 compliant
- 60 GHz wireless video free from interference
- MOD6321-R supports maximum resolution 1080p/60Hz
- MOD6321-4K-R supports maximum resolution 1080p/120Hz or 4K30 when used with SiI9396 HDMI bridge device<sup>1</sup>
- Average 5 ms video latency
- Surround sound audio
- CEC or AVC commands
- HDCP content protection

### Benefits Summary

- Quick time-to-market
- Sub-frame latency
- Ease of use and installation

### Industry-Standard Compliance

- WirelessHD Specification v1.1
- HDMI 1.4b / 2.0
- HDCP 1.4 / 2.2

### Digital Input/Output

- HDMI
- USB for debug
- I<sup>2</sup>C for advanced control

### Wireless Range

- Up to 10 m in-room

### Operating Frequency

- 59.40 GHz to 63.72 GHz
- Channels 2 and 3

### Operating Temperature

- 0 to 60 °C ambient temperature

### Antenna Polarization Options

- MOD6321-R/MOD6321-4K-R (Single Polarization)
  - Recommended for stationary applications
- MOD6321-R-12/MOD6321-4K-R-12 (Dual Polarization)
  - Recommended for portable applications

### Modular Regulatory Approval

- IC (Canada)
- SRRC (China)
- ETSI (EU)
- KCC (Korea)
- TELEC (Japan)
- FCC (USA)

### Module Dimensions

- 74 mm x 17 mm x 5.4 mm
- Cable length 30 mm

### Ordering Information

Part Number: MOD6321-R  
Part Number: MOD6321-R-C\*

Part Number: MOD6321-R-12  
Part Number: MOD6321-R-12-C\*

Part Number: MOD6321-4K-R<sup>1</sup>  
Part Number: MOD6321-4K-R-C\*<sup>1</sup>

Part Number: MOD6321-4K-R-12<sup>1</sup>  
Part Number: MOD6321-4K-R-12-C\*<sup>1</sup>

All parts include module.

\* Also Includes cable

<sup>1</sup> 4K modules require SiI9396 device. Please order separately.

### Applications Support

[www.latticesemi.com/support](http://www.latticesemi.com/support)

© 2017 Lattice Semiconductor Corporation and/or its affiliates. All rights reserved. SiBEAM, WirelessHD and HDMI are trademarks, registered trademarks or service marks of Lattice Semiconductor Corporation and/or its affiliates in the United States and/or other countries. All other trademarks and registered trademarks are the property of their respective owners in the United States and/or other countries.

May 2017  
Order #: SPB002 Rev.4

