

Description

Single pole thermal-magnetic circuit breakers with tease-free, trip-free, press-to-reset, snap action mechanism (R-type TM CBE to EN 60934; M-type with manual release (-H)). Available with fast acting and standard magnetic tripping characteristics - types 3300 and 3400 - both with threadneck panel mounting. Options include auxiliary contacts, a separate shunt tap terminal (-A3), and pull-to-trip manual release (-H). Approved to CBE standard EN 60934 (IEC 60934).

Typical applications

Control systems, instrumentation, medical equipment, machine tools, robotics.

Ordering information 3300

Type No.

3300 fast acting

Mounting

IG2 moulded threadneck M12x1, > 5 pcs: hex nut and knurled nut bulk shipped

Terminal design

P10 blade terminals tin-plated DIN 46244-A6.3-0.8

Current ratings

0.05...16 A

3300 -IG2 - P10 -10 A

Ordering information 3400

Type No.

3400 standard delay

Mounting

IG2 moulded threadneck M12x1 (bulk-shipped), not with -H; ... leave blank for metal threadneck, required for -H

Terminal design

P10 blade terminals 6.3-0.8 (QC .250)

K20 screw terminals M3.5x5.5 with clamp (not for -Si and -A3)

Shunt terminal (optional)

A3 same as main terminals, up to $I_N=7$ A max. load 5 A

Manual release (optional)

H manual release facility (pull), without reinforced insulation in operating area, for M12x1 metal threadneck only. Metal threadneck version for -H is not approved.

Auxiliary contacts (optional)

Si with silver-plated solder terminals (N/O and N/C)

Current ratings

0.05...16 A

3400 -IG2 - P10 - ... - Si -10 A ordering example, without manual release and with moulded threadneck

3400 - ... - P10 - ... - H - Si -10 A ordering example, with manual release and metal threadneck

Please be informed that we have minimum ordering quantities to be observed.

Approvals

Authority	Standard	Rated voltage	Current ratings
VDE	IEC/EN 60934	AC 240 V DC 65 V	0.05...16 A 0.05...16 A
UL	UL 1077 C22.2 No 235	AC 250 V DC 80 V	0.05...16 A 0.05...16 A
CSA	C22.2 No 235	AC 250 V DC 80 V	0.05...16 A 0.05...16 A



3300
fast acting

3400
standard delay


Technical data

For further details please see: http://www.e-t-a.de/ti_e


Voltage rating	AC 240 V, 50/60 Hz; DC 65 V	
Current ratings	0.05...16 A	
Auxiliary circuit	AC 240 V / DC 65 V, 1 A	
Typical life		
with -H:	5,000 operations at $1 \times I_N$, inductive 5,000 operations at $2 \times I_N$, resistive	
without -H:	0.05...8 A > 8 A	5,000 operations at $2 \times I_N$, inductive 1,500 operations at $2 \times I_N$, inductive
Ambient temperature	-30...+60 °C (-22...+140 °F)	
Insulation co-ordination (IEC 60664)	2.5 kV/2 reinforced insulation in operating area	
Dielectric strength		
operating area	AC 3,000 V	
main circuit/aux. circuit	AC 1,500 V	
aux. circuit 4-5/6-7	AC 840 V	
Insulation resistance	> 100 MΩ (DC 500 V)	
Interrupting capacity I_{cn}	0.05...0.8 A 1...2 A 2.5...16 A	self-limiting 200 A 400 A
Interrupting capacity (UL 1077)	I_N 0.05...16 A 0.05...16 A	U_N AC 250 V 1,000 A DC 80 V 1,000 A
Degree of protection (IEC 60529)	operating area IP40 terminal area IP00	
Vibration	5 g (57-500 Hz), ± 0.38 mm (10-57 Hz) to IEC 60068-2-6, test Fc 10 frequency cycles/axis	
Shock	25 g (11 ms) to IEC 60068-2-27, test Ea	
Corrosion	96 hours at 5 % salt mist to IEC 60068-2-11, test Ka	
Humidity	240 hours at 95 % RH, to IEC 60068-2-78, test Cab	
Mass	3300: approx. 55 g 3400: approx. 50 g	

Dimensions


-iG2-P10



-H (3400 only)




Installation drawing



Internal connection diagrams


3300/3400

3400




Terminal design 3400


-P10-A3



-P10-Si



-K20





Standard current ratings and typical internal resistance values



Current ratings (A)	Internal resistance (Ω)		Current ratings (A)	Internal resistance (Ω)	
	3300	3400		3300	3400
0.05	447	211	3	0.18	0.19
0.1	131	131	4	0.109	0.090
0.2	41	40	5	0.066	0.061
0.3	19.6	19.3	6	0.046	0.041
0.4	10.4	10.4	7	0.032	0.034
0.5	7.2	7.1	8	0.02	≤ 0.02
0.6	4.8	4.3	10	≤ 0.02	≤ 0.02
0.8	2.5	2.5	12	≤ 0.02	≤ 0.02
1	1.93	1.67	13	≤ 0.02	≤ 0.02
1.5	0.81	0.61	14	≤ 0.02	≤ 0.02
2	0.44	0.38	15	≤ 0.02	≤ 0.02
2.5	0.27	0.24	16	≤ 0.02	≤ 0.02

This is a metric design and millimeter dimensions take precedence (mm/inch)

Typical time/current characteristics



¹⁾ Magnetic tripping currents are increased by 20 % on DC supplies.





¹⁾ Magnetic tripping currents are increased by 20 % on DC supplies.

Accessories

For push buttons with M12 moulded threadneck (-iG2)
 (not with manual release -H)
Hex nut with splash cover, black
X 200 801 03 with O ring
 (IP66 and IP67)
Hex nut with splash cover, transparent
X 200 801 08 with O ring
 (IP66 and IP67)

Water splash cover, transparent with knurled nut
X 210 663 05 (IP64)



The time/current characteristic curve depends on the ambient temperature prevailing. In order to eliminate nuisance tripping, please multiply the circuit breaker current ratings by the derating factor shown below. See also section Technical information.

Ambient temp. °F	-22	-4	+14	+32	+73.4	+104	+122	+140
°C	-30	-20	-10	0	+23	+40	+50	+60
Derating factor	0.76	0.79	0.83	0.88	1	1.08	1.16	1.24

This is a metric design and millimeter dimensions take precedence ($\frac{\text{mm}}{\text{inch}}$)

All dimensions without tolerances are for reference only. In the interest of improved design, performance and cost effectiveness the right to make changes in these specifications without notice is reserved. Product markings may not be exactly as the ordering codes. Errors and omissions excepted.