

File E61760(N)

59065 & 59070 Threaded Barrel Features and Benefits



Features

- 2 part magnetically operated proximity sensor
- Threaded barrel with retaining nuts
- Available as M8 (57070/59070) or 5/16 (57065/59065) size options
- Customer defined sensitivity
- Choice of cable length and connector


Benefits

- Simple installation and adjustment using supplied retaining nuts
- No standby power requirement
- Operates through non-ferrous materials such as wood, plastic or aluminium
- Simple installation and adjustment

Applications

- Position and limit sensing
- Security system switch
- Linear actuators
- Industrial process control

DIMENSIONS (in) mm



CUSTOMER OPTIONS - Switching Specifications

TABLE 1			Normally Open	Normally Open High Voltage	Change Over	Normally Closed
Contact Type			1	2	3	4
Switch Type			1	2	3	4
Power	Power	Watt - max.	10	10	5	5
	Switching	Vdc - max.	200	300	175	175
Voltage	Breakdown	Vdc - min.	250	450	200	200
	Switching	A - max.	0.5	0.5	0.25	0.25
Current	Carry	A - max.	1.2	1.5	1.5	1.5
	Contact, Initial	Ω - max.	0.2	0.2	0.2	0.2
Resistance	Insulation	Ω - min.	10 ¹⁰	10 ¹⁰	10 ⁹	10 ⁹
	Contact	pF - typ.	0.3	0.2	0.3	0.3
Capacitance	Operating	°C	-40 to +105	-20 to +105	-40 to +105	-40 to +105
	Storage	°C	-65 to +105	-65 to +105	-65 to +105	-65 to +105
Temperature	Operate	ms - max.	1.0	1.0	3.0	3.0
	Release	ms - max.	1.0	1.0	3.0	3.0
Shock	11ms 1/2 sine	G - max.	100	100	50	50
Vibration	50-2000 Hz	G - max.	30	30	30	30

CUSTOMER OPTIONS - Sensitivity, Cable Length and Termination Specification

TABLE 2							
Sensitivity Options:- Activate Distances are approximate using Hamlin 57065/57070 actuator as illustrated Switch AT before modification							
Select Option	S		T		U		V
Switch Type	Pull In AT Range	Activate Distance d (in) mm	Pull In AT Range	Activate Distance d (in) mm	Pull In AT Range	Activate Distance d (in) mm	Pull In AT Range
1 Normally Open	12-18	(354)	17-23	(276)	22-28	(236)	27-33
2 High Voltage		9.0		7.0		6.0	4.5
3 Change Over		(295)		(236)		(197)	
4 Normally Closed	15-20	7.5	20-25	6.0	25-30	5.0	

TABLE 3	
Cable Type:- 24 AWG 7/32 PVC 105°C UL1430/UL1569	
Standard Lengths	
SELECT OPTION	CABLE LENGTH (in) mm
01	(3,94) 100
02	(11,81) 300
03	(19,69) 500
04	(29,53) 750
05	(39,37) 1000

TABLE 4		
Termination Options:-		
SELECT OPTION	DESCRIPTION (2 WIRE VERSIONS ILLUSTRATED)	
A or F	Tinned or untinned leads	
C	6.35mm fastons	
D	AMP MTE 2.54mm pitch	
E	JST XHP 2.5mm pitch	

ORDERING INFORMATION

N.B. 57065/57070 actuator sold separately

59065/59070 - X - X - XX - X

Series 59065/59070

Switch Type Table 1

Sensitivity Table 2

Cable Length Table 3

Termination Table 4

Hamlin USA Tel: +1 920 648 3000 • Fax: +1 920 648 3001 • Email: sales.us@hamlin.com
Hamlin UK Tel: +44 (0)1379 649700 • Fax: +44 (0)1379 649702 • Email: sales.uk@hamlin.com
Hamlin Germany Tel: +49 (0) 6181 953660 • Fax: +49 (0) 6181 953666 • Email: sales.de@hamlin.com
Hamletrol France Tel: +33 (0) 1 4687 0202 • Fax: +33 (0) 1 4686 6786 • Email: sales.fr@hamlin.com

ISSUE No: 4 DATE: 1/5/3

DETAILS PROVIDED ON THIS DATA SHEET ARE PROVIDED FOR INFORMATION PURPOSES ONLY AND SHOULD NOT BE RELIED UPON AS BEING ACCURATE FOR ANY PARTICULAR PURPOSE. Product performance may be affected by the application to which the product is put. Upon request, HAMLIN will assist purchasers by providing information specific to any particular application. HAMLIN disclaims any and all liability whatsoever for any purchaser's reliance upon the information contained on this data sheet without further consultation with authorised representatives of HAMLIN.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Hamlin:

[59070-010](#) [59070-030](#) [59065-010](#) [59065-020](#)

Littelfuse:

[59065-030](#) [59065-040](#) [59070-4-U-02-F](#) [59065-4-T-02-A](#) [59065-2-V-02-A](#) [59070-1-U-02-A](#) [59065-1-U-02-F](#) [59070-1-V-02-F](#) [59070-3-U-02-A](#) [59065-3-S-02-F](#) [59065-4-U-02-F](#) [59070-3-T-02-A](#) [59065-1-V-02-A](#) [59070-2-T-02-A](#) [59070-2-T-02-F](#) [59065-3-T-02-A](#) [59070-1-S-02-F](#) [59070-3-U-02-F](#) [59070-2-V-02-A](#) [57070-000](#) [59065-1-V-02-F](#) [59070-2-V-02-F](#) [59065-4-S-02-F](#) [59070-1-S-02-A](#) [59065-3-U-02-A](#) [59070-3-S-02-A](#) [59070-4-U-02-A](#) [59070-4-S-02-A](#) [59065-4-S-02-A](#) [59070-2-U-02-F](#) [59070-040](#) [59065-1-S-02-F](#) [59070-1-V-02-A](#) [59070-1-U-02-F](#) [59065-4-T-02-F](#) [59070-020](#) [59065-2-T-02-F](#) [59065-1-T-02-A](#) [59070-4-T-02-A](#) [59065-3-U-02-F](#) [59065-3-T-02-F](#) [59070-2-U-02-A](#) [59065-2-U-02-A](#) [59065-2-T-02-A](#) [59065-2-U-02-F](#) [59065-1-U-02-A](#) [59070-3-S-02-F](#) [59065-2-V-02-F](#) [59065-1-T-02-F](#) [57065-000](#) [59070-1-T-02-A](#) [59065-1-S-02-A](#) [59070-4-T-02-F](#) [59070-1-T-02-F](#) [59070-4-S-02-F](#) [59065-3-S-02-A](#) [59070-3-T-02-F](#) [59065-4-U-02-A](#) [59065-1-T-04-A](#) [59065-1-V-01-A](#) [59065-1-S-02-D](#) [59065-1-V-01-D](#) [59065-1-S-02-E](#) [59065-1-T-02-E](#) [59065-1-S-04-E](#) [59065-1-S-01-F](#) [59070-4-T-04-A](#) [59070-4-U-04-C](#) [59070-4-U-05-E](#) [59070-4-U-03-A](#) [59070-4-T-03-E](#) [59070-4-T-04-E](#) [59070-4-U-03-E](#) [59070-4-U-04-F](#) [59070-3-U-05-E](#) [59070-4-T-03-D](#) [59070-4-U-01-E](#) [59070-3-U-05-C](#) [59070-4-S-01-D](#) [59070-4-S-03-A](#) [59070-4-U-05-D](#) [59070-4-T-02-E](#) [59070-4-T-01-C](#) [59070-4-T-05-E](#) [59070-4-S-04-D](#) [59070-4-S-04-E](#) [59070-4-T-01-E](#) [59070-4-T-05-A](#) [59070-4-S-05-C](#) [59070-4-U-01-D](#) [59070-4-U-05-F](#) [59070-4-S-05-D](#) [59070-4-S-05-E](#) [59070-4-S-05-F](#) [59070-4-T-04-C](#) [59070-4-U-05-A](#) [59070-4-T-01-A](#) [59070-4-U-01-F](#) [59070-4-U-04-A](#) [59070-4-U-01-A](#)