


# Detailed Specifications & Technical Data

**BELDEN**  
SENDING ALL THE RIGHT SIGNALS

## METRIC MEASUREMENT VERSION

I100455 Fiber - TrayOptic®



For more Information  
please call

1-800-Belden1



### General Description:

FiberExpress Tray Optic Cable, 4-Fiber, OM1 OFNR, Loose Tube, Indoor & Outdoor Rated with UV Resistant Orange PVC Jacket, Industrial Grade, Water-blocked with Gigabit Ethernet Grade fiber.

### Physical Characteristics (Overall)

Product Family - Riser:

Fiber	# Fibers/Count	Type	OM1 MM 62.5/125 1 Gb	OM2 MM 50/125 1 Gb	OM3 MM 50/125 10 Gb 300m	OM4 MM 50/125	OS2 - SM
2	2	PVC	I100255	I1A0255	I1C0255	I1E0255	..
4	4	PVC	I100455	I1A0455	I1C0455	I1E0455	..
6	6	PVC	I100655	I1A0655	I1C0655	I1E0655	..
8	4	PVC	I400855	I4A0855	I4C0855	I4E0855	..
12	6	PVC	I601255	I6A1255	I6C1255	I6E1255	..
18	6	PVC	I601855	I6A1855	I6C1855	I6E1855	..
24	6	PVC	I602455	I6A2455	I6C2455	I6E2455	..
36	6	PVC	I603655	I6A3655	I6C3655	I6E3655	..
48	12	PVC	I604855	I6A4855	I6C4855	I6E4855	..
60	12	PVC	I606055	I6A6055	I6C6055	I6E6055	..
72	12	PVC	I607255	I6A7255	I6C7255	I6E7255	..
2	2	CPE	I100266	I1A0266	I1C0266	I1E0266	..
4	4	CPE	I100466	I1A0466	I1C0466	I1E0466	..
6	6	CPE	I100666	I1A0666	I1C0666	I1E0666	..
8	4	CPE	I400866	I4A0866	I4C0866	I4E0866	..
12	5	CPE	I601266	I6A1266	I6C1266	I6E1266	..
18	6	CPE	I601866	I6A1866	I6C1866	I6E1866	..
24	6	CPE	I602466	I6A2466	I6C2466	I6E2466	..
36	6	CPE	I603666	I6A3666	I6C3666	I6E3666	..
48	12	CPE	I604866	I6A4866	I6C4866	I6E4866	..
60	12	CPE	I606066	I6A6066	I6C6066	I6E6066	..
72	12	CPE	I607266	I6A7266	I6C7266	I6E7266	..

**Fiber Type:** 62.5/125/250 Micron

**Number of Fibers:** 4

**Core Diameter:** 62.5 +/- 2.5

**Core Non-Circularity:** 5%; Maximum

**Clad Diameter:** 125 +/- 2

**Clad Non-Circularity:** 1%; Maximum

**Primary Coating Material:** Acrylate

**Primary Coating Diameter:** 245 +/- 10

**Buffer Tube Diameter:** 1.9

**Buffer Tube Material:** Flame Retardant Thermoplastic

**Buffer Tube Filling Material:** Synthetic Thixotropic Gel

**Buffer Tube Color Code Chart:**

Number	Color
1	Blue

**Core-clad Offset:** 1.5 Microns Maximum

**Inner Jacket**

**Outer Jacket**

**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

# Detailed Specifications & Technical Data



## METRIC MEASUREMENT VERSION

### I100455 Fiber - TrayOptic®

Outer Jacket Color: Orange

#### Overall Cable

Overall Cabling Fillers: PVC

Overall Nominal Diameter: 10.922 mm

#### Mechanical Characteristics (Overall)

Storage Temperature Range: -40°C To +70°C

Installation Temperature Range: -20°C To +60°C

Operating Temperature Range: -40°C To +70°C

Bulk Cable Weight: 136.914 Kg/Km

Min. Bend Radius/Minor Axis: 218.440 mm

Min. Bend Radius for Long Term Application: 165.100 mm

Crush Resistance: Passes TIA/EIA 455-41; 2000 N/cm

Impact Resistance: Passes TIA/EIA 455-25; 2000 Impacts @ 1.6 N-m

Solar Radiation Resistance: High

Water Penetration: Passes TIA/EIA 455-82

Compound Flow: Passes TIA/EIA 455-81

Max. Load for Installation: 2668.920 N

Max. Load for Long Term Application: 800.676 N

Proof Test: 100 kpsi

#### Applicable Specifications and Agency Compliance (Overall)

##### Applicable Standards & Environmental Programs

NEC/(UL) Specification: OFNR

CEC/C(UL) Specification: OFNR

EU Directive 2011/65/EU (ROHS II): Yes

IEEE Specification: 802.3Z

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2006

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Other Specification: Suitable for installation in trays per NFPA 70.

##### Flame Test

C(UL) Flame Test: FT4

IEEE Flame Test: 1202, IEEE 383 Vertical Tray Flame Test (70,000 BTU)

##### Plenum/Non-Plenum

Plenum (Y/N): No

#### Optical Characteristics (Overall)

Maximum Attenuation @ 850nm: 3.5 dB/km

Maximum Attenuation @ 1300nm: 1.2 dB/km

Point Loss @ 850nm & 1300nm: 0.2

Minimum Bandwidth @ 850nm: 200 MHz\*km

Minimum Bandwidth @ 1300nm: 500 MHz\*km

Refractive Index @ 850nm: 1.496

Refractive Index @ 1300nm: 1.491

Numerical Aperture: .275

Maximum Gigabit Ethernet Length @ 850nm: 330 meters

# Detailed Specifications & Technical Data



## METRIC MEASUREMENT VERSION

### I100455 Fiber - TrayOptic®

Maximum Gigabit Ethernet Length @ 1300nm: 550 meters

#### Related Documents:

[Loose Tube Trayoptic Cable.pdf](#) - Loose Tube Trayoptic Cable

#### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
I100455	1 FT	0.104 LB	ORANGE		REPLACED BY FD1T004RF

Revision Number: 4 Revision Date: 08-04-2014

© 2017 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.