


Axial Leaded Inductors

LAN02TA470J



■ Features

- Item Summary
47 μ H($\pm 5\%$), 160mA, 50, Leaded
- Lifecycle Stage
Phaseout
- Standard packaging quantity (minimum)
Taping 2000pcs

■ Products characteristics table

External Dimensions (mm) LxD	3.6(max)×2.4(max)mm
Inductance	47 μ H($\pm 5\%$)
Inductance Measuring Frequency	2.52MHz
DC Resistance (max)	2.8 Ω
Q (min)	50min
Self-resonant Frequency (min)	12MHz
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Wave

■ External Dimensions

L	3.6mm max
D	2.4mm max

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
Before making final selection, please check product specification.

2014.12.01