

Crystal Clock Oscillator

NDK
Crystal Bridge to the Future

2765E Series

EMI Noise-reducing Type

■ Model name

2765E Overall frequency tolerance of $\pm 100 \times 10^{-6}$.

■ Application

- For compact mobile information equipment, such as PDA and notebook PC

■ Features

- With a spread spectrum function installed, this crystal oscillator effectively reduces EMI noise.
- Down-spreading and center-spreading.
- With a standby function installed, power consumption is reduced.

Pb Free

RoHS Compliant
Directive 2011/65/EU




Absolute maximum rating
Supply voltage (V_{cc}) -0.5 to +7.0 V
Storage temperature range -55 to +125 °C

■ Specifications


Item	Model
Output level	CMOS
Nominal frequency range ¹	(MHz)
20 ≤ F ≤ 80	
Operating temperature range ²	(°C)
-20 to +70	
Overall frequency tolerance	($\times 10^{-6}$)
± 100	
Supply voltage [V _{cc}]	(V)
+3.3±0.3	
Current consumption (+3.3 V, 25 °C) max	(mA)
30	
	(μ A)
	30
V _{OL} max/V _{OH} min	(V)
0.2 V _{cc} /0.8 V _{cc}	
T _r max/T _f max	(ns)
5/5 (0.2 V _{cc} to 0.8 V _{cc})	
Symmetry min. to max.	(%)
40 to 60 (at 1/2 V _{cc})	
Load (C _L) max	(pF)
15	
Start-up time max	(ms)
10	
Standby function	Available (Three-state)
Number for specifying an order	NSA3393A

¹: If you require a product with a frequency not given above, please contact us. ²: If you require a product with an operating temperature range not given above, please contact us.

■ Dimensions



■ Output Waveform <CMOS>



■ Spread Spectrum Characteristics

Spreading Type	Spreading Ratio
Center spreading	±1.0 %

■ Standby Function

#1 Input	#3 Output
Level H (0.7 V _{cc} ≤ V _{ih} ≤ V _{cc}) or OPEN is selected.	Oscillation output ON
Level L (V _{il} ≤ 0.3 V _{cc}) is selected.	High impedance

■ How to Specify an Order

When ordering our products, specify them with an "Ordering Code" that consists of the following: Example : When ordering a product with model name: 2765E, frequency: 20 MHz, overall frequency tolerance: $\pm 100 \times 10^{-6}$, and supply voltage: 3.3 V
Model name - Frequency (up to 9 digits) M - Number for specifying an order

If you have any queries concerning our standard frequencies and numbers for specifying orders, please contact our sales representatives or visit our homepage (<http://www.ndk.com/>).