





LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A.PL00LF
15	39.14	33.32	25.18	25.12	19.18	D15P24A.PL00LF
25	53.03	47.04	39.12	38.84	33.12	D25P24A.PL00LF
37	69.32	63.50	55.68	55.30	49.68	D37P24A.PL00LF

Plating: 4 --> flash AU
Plating: 6 --> 0.76 μ AU

PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



Notes:

1) The nut can protrude above the surface of insulator but maintaining the footprint dimension 6.0±0.15 mm.

GENERAL CHARACTERISTICS AND ROHS INFORMATION:

SEE DRAWING C01-8646-0000

mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302	ISO 406 ISO 1101		D-SUB		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title		
H	ELX-I-21256	AB	2015/07/14	angles	linear	MM	MALE CONNECTOR DELTA-D		
				0°±2°	.0±0.1 .00±0.1 .000±0.1	scale 2:1	STRAIGHT - SOLDER TYPE		
				dr	LELEON 1992/09/10		dwg no		sheet 1 of 1
				engr	ALIAS BABU 2015/07/14		C01-8646-0096		A3
				chr	MITHUN PAUL 2015/07/14		type		Product Customer Drawing
				app	BIJU K PAUL 2015/07/14				
sheet index	revision	H							
	sheet	1							