

SPECIFICATIONS


Material: Boot: APM-RUBRGLAS (transparent silicone rubber)
conforms to A-A-59588, Class III Grade 50.
Temperature Range: HEXSEALS: -94°F to +400°F
Pressure Range: Dust tight and splashproof.
Resistant to: Salt spray, weather, sunlight, ozone, corona and
most acids.
Shelf Life: Excess of 25 years.
Operational Life: 10,000 actuations, minimum.

Notes:


1. Mounting screws are supplied in lengths shown unless otherwise specified.

2. New sizes and types of RUBRGLAS-SEELS® are being added regularly. Please request other types and styles as required.

Agency Recognition: Front Panel mounted Circuit Breaker Boots are UL-listed to UL Std. 50, types 1, 2, 3, 12, 12K, and 13. Back-of-Panel mounted Circuit Breaker boots are UL-listed to UL Std. 50, type 1. Also meet CSA standards.



NOTE: ORDER SEPARATELY
6 # 6-32 x 3/8 APM SEELSCREWS®



| REV. | DESCRIPTION | DATE |
|---|---|----------------------|
| B | MAT'L CHANGED and WALL THICKNESS TOL. CHANGED FROM 0.010" to 0.005" | 1-3-03 |
| A | CAD COMPUTER GENERATED | 1-3-03 |
| | | |
| MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON EACH DIMENSION. | | |
| MAT'L: APM RUBRGLOSS® CONFORMS TO A-A-59588, CL III | TITLE: CIRCUIT BREAKER BOOT - BACK-OF-PANEL MOUNTED | ENG. CARBONE 6-13-69 |
| FINISH: GRADE 50 CLEAR | SCALE 3 : 2 | DWG. NO. 1113/43 |

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.
THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE WRITTEN APPROVAL OF AN OFFICER OF THE APM-HEXSEAL CORPORATION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[APM HEXSEAL:](#)

[1113/43](#)