








LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		A	REVISED PER ECO-13-005557	29MAR2013	KH	MB



RECOMMENDED P.C.B LAYOUT (TOP VIEW)
(TOLERANCE:±0.05; THICKNESS IS 1.60mm)



- MATERIAL :
HOUSING: PBT WITH 30% GLASS FILLED, 15% REGRIND MAX, UL 94V-0,COLOR BLACK.
CONTACT: PHOSPHOR BRONZE.
SHIELD: PHOSPHOR BRONZE.
- FINISH :
CONTACT:GOLD FLASH OVER.
0.762um (30u") MIN PALLADIUM-NICKEL PLATING ON CONTACT AREA.
2.54um (100u') MIN MATTE TIN PLATED ON SOLDER TAILS
1.27um (50u') MIN NICKEL UNDERPLATED ALL OVER.
SHIELD: 1.27um(50u') MIN NICKEL PLATED ALL OVER.
- RECOMMENDED PCB THICKNESS :1.60mm.
- WAVE SOLDER CAPABLE TO 265 C PER TE SPEC 109-202,CONDITION B.
- PARTS NOT YET QUALIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KIRAN_HOLAL 22FEB2013	 TE Connectivity				
DIMENSIONS: mm		CHK BRUBAKER MARK 22FEB2013	NAME MINI USB CONN,RCPT,R/A,DIP,B TYPE				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD BRUBAKER MARK 22FEB2013					
	0 PLC ± 0.38 1 PLC ± 0.30 2 PLC ± 0.20 3 PLC ± 0.10 4 PLC ± - ANGLES ± ± 30°	PRODUCT SPEC —					
MATERIAL SEE NOTE	FINISH SEE NOTE	APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		WEIGHT 0.665 GRAMS	A2	00779	C=2172034	—	
CUSTOMER DRAWING					SCALE 1:1	SHEET 1 of 2	REV A

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		—	SEE SHEET 1	—	—	—






FIGURE E
HEIGHT : 8mm



DETAIL A
(SCALE 8:1)

6.2 Kg	3.5 Kg	95	46	4370 PCS
GROSS WEIGHT	NET WEIGHT	PCS/TRAY	TRAYS /CARTON	QUANTITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 22FEB2013 CHK 22FEB2013 APVD 22FEB2013	TE Connectivity		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.38 1 PLC ± 0.30 2 PLC ± 0.20 3 PLC ± 0.10 4 PLC ± - ANGLES ± 30°			
MATERIAL SEE NOTE		FINISH SEE NOTE	NAME MINI USB CONN,RCPT,R/A,DIP,B TYPE		
		WEIGHT 0.665 GRAMS	SIZE A2	CAGE CODE 00779	DRAWING NO C=2172034
		CUSTOMER DRAWING	SCALE 1:1	SHEET 2 OF 2	REV A