





NOTES,
① MATERIAL, HOUSING & EJECTOR LEVER:
L.C.P (HIGH TEMP THERMO PLASTIC)
UL 94V-0, NATURAL. (LEVER: BLACK)
CONTACT: PHOS-BRZ
② FINISH: CONTACT AREA: 0.0003 MIN GOLD ON
0.0013 MIN ALL OVER NICKEL.
SOLDERING AREA: 0.001 MIN TIN-LEAD.
3. MODULE KEY POSITION OF CONNECTOR SEE TABLE.

注記,
① 材料; ハウジング & エジエクターレバー:
L.C.P (耐熱熱可塑性樹脂)
UL94V-0, 自然色. (レバー: 黒色)
コンタクト: 燐青銅
② めっき仕様; 接触部 金めっき 0.0003 MIN 厚
ニッケル下地 0.0013 MIN 厚
半田付け部: 半田めっき 0.001 MIN 厚
3. コネクターのモジュールキーは表参照の事.



3	3	RESERVED 5.0V	CIRCUIT NO. 84,168 SIDE	(D)	(B)	168	2-353476-1
↑	↑	RESERVED 3.3V	↑	(D)	(C)	↑	1- ↑ -2
↑	↑	RESERVED 5.0V	CIRCUIT NO. 84,168 SIDE	(D)	(B)	168	1-353476-1
↑	↑	RESERVED 3.3V	↑	(D)	(C)	↑	↑ -2
2.6	3	RESERVED 5.0V	CIRCUIT NO. 1,85 SIDE	(D)	(B)	168	353476-1
±0.3 "L"	"M"	REMARKS (POWER SUPPLY)	EJECTOR LEVER MOUNT SIDE	KEYING TYPE		POS	PART NO.

Copyright ©1996年 Tyco Electronics AMP K.K.				Copyright ©1996 Tyco Electronics AMP K.K. ALL RIGHTS RESERVED.				AMP Tyco Electronics AMP K.K. Kawasaki, Japan			
組合電線断面積 (WIRE RANGE) mm ² (AWG -)				被覆外径 (INSULATION DIA.) mmφ				名称 (NAME) LOW PROFILE M64 CARD EDGE CONNECTOR, SLANT (25°) TYPE. (FOR 8 BYTE DIMM RESERVED TYPE)			
材料 (MATERIAL) SEE NOTE				仕上 (FINISH) SEE NOTE				一般公差 (GENERAL TOLERANCE) 10以下: ±0.2 10~30: ±0.25 30~100: ±0.3 角 度: ±3°			
A REVISED ECN NO. FJ00-0197-00 K.K. S.S.				DR. 27-AUG-'96 K. KOBAYASHI				10以下: ±0.2 10~30: ±0.25 30~100: ±0.3 角 度: ±3°			
O RELEASED ECN NO. FJ00-5279-96 K.K. I.E.				DE. 27-AUG-'96 K. KOBAYASHI				10以下: ±0.2 10~30: ±0.25 30~100: ±0.3 角 度: ±3°			
LTR 変更 (REVISION RECORD)				CHK. 27-AUG-'96 I. ENOMOTO				10以下: ±0.2 10~30: ±0.25 30~100: ±0.3 角 度: ±3°			
DR				APP. 27-AUG-'96 Y. YOSHIMURA				10以下: ±0.2 10~30: ±0.25 30~100: ±0.3 角 度: ±3°			
DATE				SHEET				1 OF 3			

NUMBER C-353476




三 角 法 (3rd ANGLE PROJECTION)

METRIC

PROJ. NO. 696-105

単位: ㎜ DIMENSIONS IN MM. DO NOT SCALE PRINT


PRINT DIST



推奨取付け穴仕様 (コネクタ—取付け側)
RECOMMENDED P.C. BOARD HOLE LAYOUT
(CONNECTOR MOUNTING SIDE)
推奨基盤厚
P.C. BOARD THK 1.6 ± 0.1

SEE SHEET 1 OF 3			
LTR	変更 (REVISION RECORD)	DR	CHK DATE

Copyright ©1996年 Tyco Electronics AMP K.K.		Copyright ©1996 Tyco Electronics AMP K.K. ALL RIGHTS RESERVED.		AMP		Tyco Electronics AMP K.K. Kawasaki, Japan	
包合電線断面積 (WIRE RANGE) — — mm ² (AWG -)		被覆外径 (INSULATION DIA.) — — mmφ		名称 (NAME) LOW PROFILE M64 CARD EDGE CONNECTOR, SLANT (25°) TYPE. (FOR 8 BYTE DIMM RESERVED TYPE)			
材料 (MATERIAL) — —		仕上 (FINISH) — —		一般公差 (GENERAL TOLERANCE) 10以下 ±0.2 10を超え 30以下 ±0.25 30を超え 100以下 ±0.3 角 度: ±3°		LOC B J	
DR.		DE.		番号 (No.) C-353476		尺度 (SCALE) 2-1	
CHK.				REV. A		SHEET 2 OF 3	



- NOTES;
1. TOLERANCES ON ALL DIMENSIONS ± 0.13 UNLESS OTHERWISE SPECIFIED.
 2. P.C.BOARD THICKNESS APPLIES ACROSS TABS AND INCLUDES PLATING AND/OR MATALIZATION.
 3. FINISH OF PAD : GOLD PLATING 0.00076 MIN OVER NI PLATING 0.002 MIN.

- 注記;
1. 一般公差 ± 0.13
 2. 基板厚寸法は、めっき厚を含む。
 3. パッド部の仕上げ: ニッケル下地めっき 0.002 MIN 厚の上に、金めっき 0.00076 MIN 厚を施す。

推奨基板仕様
RECOMMENDED MATING BOARD CONFIGURATION.

RESERVED 3.3V			DETAIL "C"		1- -2
RESERVED 5.0V	NO.84,168 SIDE		DETAIL "B"		1-353476-1
RESERVED 3.3V			DETAIL "C"		-2
RESERVED 5.0V	NO.1,85 SIDE	DETAIL "D"	DETAIL "B"	168	353476-1
REMARKS (POWER SUPPLY)	EJECTOR LEVER MOUNT SIDE	DRAM KEY	VOLTAGE KEY	POS	CONNECTOR PART NO.
KEYING TYPE					

SEE SHEET 1 OF 3			Copyright ©1995年 Tyco Electronics AMP K.K.		Copyright ©1996 Tyco Electronics AMP K.K. ALL RIGHTS RESERVED.		AMP		Tyco Electronics AMP K.K. Kawasaki, Japan		
			包合電線断面積 (WIRE RANGE) mm ² (AWG)		被覆外径 (INSULATION DIA.) mmφ		名称 (NAME) LOW PROFILE M64 CARD EDGE CONNECTOR, SLANT (25°) TYPE. (FOR 8 BYTE DIMM RESERVED TYPE)				
			材料 (MATERIAL)		仕上 (FINISH) SEE NOTE		一般公差 (GENERAL TOLERANCE) 10mm以下 ±0.2 10mm以上 30mm以下 ±0.25 30mm以上 100mm以下 ±0.3 角 度: ±3°		LOC B J	番号 (No.) C-353476	
			DR.		DE.		尺 寸 (SCALE) 1-1		REV. A		SHEET 3 OF 3
LTR 変更 (REVISION RECORD)			CHK.								

PRINT DIST
単位: 毫米 DIMENSIONS IN MM. DO NOT SCALE PRINT
METRIC
三视图 (3rd ANGLE PROJECTION)
NUMBER
C-353476
AMP-J010-2C
REV. 3/93