






REV.	DATE	ECR NO.	DESCRIPTION
A	03/20/03	—	UPDATE PART DIMENSIONS / DRAWING FORMAT
B	05/08/07	—	REVISE BARREL, FERRULE DIMENSIONS
C	11/12/08	—	REVISE HOUSING, BODY, FERRULE, COVER PLATING TO GOLD



NOTE:
1. CRIMPED FERRULE HEX CRIMP SIZE .128"
2. CONTACT PIN TO SOLDER

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
8					DRAWN	GRS	11/12/08							
7	HEAT SHRINK TUBE		1		CHECKED									
6	COVER	BRASS	GOLD		1	ISSUED				PART DESCRIPTION SMB R/A CRIMP PLUG (FOR RG-174/U, 188A/U, 316/U CABLE)				
5	FERRULE	COPPER	GOLD		1	SHEET	1 OF 1							
4	CONTACT PIN	BER. COPPER	GOLD		1				PART NO. 142194					
3	INSULATOR	PTFE	NATURAL		1									
2	BODY	BRASS	GOLD		1				DWG. NO. 142194.DWG					
1	HOUSING	DIE CAST	GOLD		1									
DESCRIPTION		MATERIAL	FINISH		QTY	CAD FILE C:/142/142194.DWG			REV. NC		SIZE A		SCALE NA	