

Polypropylene (PP) Capacitors for Pulse Applications with Metal Foil Electrodes and Metallized Internal Series Connection in PCM 15 mm to 52.5 mm. Capacitances from 100 pF to 4.7 µF. Rated Voltages from 400 VDC to 6000 VDC.

Special Features

- Extremely high pulse duty
- Self-healing
- Internal series connection
- Very low dissipation factor
- Negative capacitance change versus temperature
- According to RoHS 2011/65/EU

Typical Applications

For high pulse and high frequency applications e.g.

- Switch mode power supplies
- Converters in drives and power electronics
- Deflection systems in monitors and TV-sets
- Electronic ballasts

Construction


Dielectric:

Polypropylene (PPI) film

Capacitor electrodes:

Aluminium foil and double-sided metallized plastic film

Internal construction:



Encapsulation:

Solvent-resistant, flame-retardant plastic case with epoxy resin seal, UL 94 V-0

Terminations:

Tinned wire.

Marking:

Colour: Red. Marking: Black.

Epoxy resin seal: Yellow

Electrical Data

Capacitance range:

100 pF to 4.7 µF (E12-values on request)

Rated voltages:

400 VDC, 630 VDC, 850 VDC, 1000 VDC, 1250 VDC, 1600 VDC, 2000 VDC, 4000 VDC, 6000 VDC

Capacitance tolerances:

±20%, ±10%, ±5% (other tolerances are available subject to special enquiry)

Operating temperature range:

-55° C to +100° C

Climatic test category:

55/100/56 in accordance with IEC

Test voltage:

2 U_r, 2 sec / 6 kV: 1.6 U_r, 2 sec.

Dielectric absorption: 0.05 %

Dissipation factors at +20° C: tan δ

at f	C ≤ 0.1 µF	0.1 µF < C ≤ 1.0 µF	C > 1.0 µF
1 kHz	≤ 6 × 10 ⁻⁴	≤ 6 × 10 ⁻⁴	≤ 6 × 10 ⁻⁴
10 kHz	≤ 6 × 10 ⁻⁴	≤ 6 × 10 ⁻⁴	-
100 kHz	≤ 10 × 10 ⁻⁴	-	-

Insulation resistance at +20° C:

C ≤ 0.1 µF: ≥ 1 × 10⁵ MΩ

(mean value: 5 × 10⁵ MΩ)

C > 0.1 µF: ≥ 30 000 sec (MΩ × µF)

(mean value: 100 000 sec)

Measuring voltage: 100 V/1 min.

Voltage derating:

A voltage derating factor of 1.35 % per K must be applied from +85° C for DC voltages and from +75° C for AC voltages

Reliability:

Operational life > 300 000 hours

Failure rate < 1 fit (0.5 × U_r and 40° C)

Maximum pulse rise time: for pulses equal to the rated voltage

Capacitance pF/µF	max. pulse rise time V/µsec at T _A < 40° C								
	400 VDC	630 VDC	850 VDC	1000 VDC	1250 VDC	1600 VDC	2000 VDC	4000 VDC	6000 VDC
100 ... 220	-	-	-	-	56000	56000	-	-	-
330 ... 680	-	-	-	-	51000	56000	56000	56000	56000
1000 ... 2200	29000	29000	2900	29000	29000	46000	51000	51000	51000
3300 ... 6800	9000	14000	2700	27000	29000	29000	29000	29000	29000
0.01 ... 0.022	9000	11000	1100	11000	11000	11000	13000	13000	13000
0.033 ... 0.068	9000	11000	1100	11000	11000	11000	11000	13000	13000
0.1 ... 0.22	7000	11000	1100	11000	11000	11000	11000	13000	13000
0.33 ... 0.68	6000	10000	1100	11000	11000	11000	11000	-	-
1.0 ... 2.2	5000	6600	8300	8300	9500	11000	-	-	-
3.3 ... 4.7	2500	-	-	-	-	-	-	-	-

Mechanical Tests

Pull test on pins:

d ≤ 0.8 φ: 10 N in direction of pins

d > 0.8 φ: 20 N in direction of pins

according to IEC 60068-2-21

Vibration:

6 hours at 10 ... 2000 Hz and 0.75 mm displacement amplitude or 10 g in accordance with IEC 60068-2-6

Low air density:

1 kPa = 10 mbar in accordance with IEC 60068-2-13

Bump test:

4000 bumps at 390 m/sec² in accordance with IEC 60068-2-29

Packing

Available taped and reeled up to and including case size 15 x 26 x 31.5 / PCM 27.5 mm.

Detailed taping information and graphs at the end of the catalogue.

For further details and graphs please refer to Technical Information.

Continuation

General Data

Capacitance	400 VDC/250 VAC*					630 VDC/400 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
1000 pF	5	11	18	15	FKP1G011004B_____	5	11	18	15	FKP1J011004B_____
1500 "	5	11	18	15	FKP1G011504B_____	5	11	18	15	FKP1J011504B_____
2200 "	5	11	18	15	FKP1G012204B_____	5	11	18	15	FKP1J012204B_____
3300 "	5	11	18	15	FKP1G013304B_____	5	11	18	15	FKP1J013304B_____
4700 "	5	11	18	15	FKP1G014704B_____	5	11	18	15	FKP1J014704B_____
6800 "	5	11	18	15	FKP1G016804B_____	6	12.5	18	15	FKP1J016804C_____
0.01 µF	5	11	18	15	FKP1G021004B_____	7	14	18	15	FKP1J021004D_____
0.015 "	6	12.5	18	15	FKP1G021504C_____	5	14	26.5	22.5	FKP1J021005A_____
0.022 "	7	14	18	15	FKP1G022204D_____	8	15	18	15	FKP1J021504F_____
0.033 "	5	14	26.5	22.5	FKP1G022205A_____	6	15	26.5	22.5	FKP1J021505B_____
0.033 "	8	15	18	15	FKP1G023304F_____	7	16.5	26.5	22.5	FKP1J022205D_____
0.047 "	6	15	26.5	22.5	FKP1G023305B_____	8.5	18.5	26.5	22.5	FKP1J023305F_____
0.047 "	7	16.5	26.5	22.5	FKP1G024705D_____	10.5	20.5	26.5	22.5	FKP1J024705H_____
0.068 "	8.5	18.5	26.5	22.5	FKP1G026805F_____	9	19	31.5	27.5	FKP1J024706A_____
						11	21	31.5	27.5	FKP1J026806B_____
						9	19	41.5	37.5	FKP1J026807A_____
0.1 µF	10.5	20.5	26.5	22.5	FKP1G031005H_____	13	24	31.5	27.5	FKP1J031006D_____
	9	19	31.5	27.5	FKP1G031006A_____	11	22	41.5	37.5	FKP1J031007B_____
0.15 "	11	21	31.5	27.5	FKP1G031506B_____	13	24	41.5	37.5	FKP1J031507C_____
0.22 "	13	24	31.5	27.5	FKP1G032206D_____	15	26	41.5	37.5	FKP1J032207D_____
	11	22	41.5	37.5	FKP1G032207B_____					
0.33 "	13	24	41.5	37.5	FKP1G033307C_____	19	32	41.5	37.5	FKP1J033307F_____
0.47 "	17	29	41.5	37.5	FKP1G034707E_____	20	39.5	41.5	37.5	FKP1J034707G_____
0.68 "	19	32	41.5	37.5	FKP1G036807F_____	24	45.5	41.5	37.5	FKP1J036807H_____
1.0 µF	20	39.5	41.5	37.5	FKP1G041007G_____	35	50	41.5	37.5	FKP1J041007J_____
1.5 "	31	46	41.5	37.5	FKP1G041507I_____	40	55	41.5	37.5	FKP1J041507K_____
						35	50	57	52.5	FKP1J041509F_____
2.2 "	35	50	41.5	37.5	FKP1G042207J_____	45	55	57	52.5	FKP1J042209H_____
3.3 "	35	50	57	52.5	FKP1G043309F_____					
4.7 "	45	65	57	52.5	FKP1G044709J_____					

* AC voltages: $f \leq 1000 \text{ Hz}$; $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_r$

New values

** PCM = Printed circuit module = pin spacing

Dims. in mm.

The values of the WIMA FKP 4 range according to main catalogue 2015 are still available on request.

Ionisation inception level in isolated cases may be lower than admissible rated AC voltage.

Part number completion:	
Version code:	2-pin = 00 4-pin = D4
Tolerance:	20 % = M 10 % = K 5 % = J
Packing:	bulk = S
Pin length:	6-2 = SD
Taped version see page 145.	

Rights reserved to amend design data without prior notification.

Continuation page 75

Continuation

General Data

Capacitance	850 VDC/450 VAC*					1000 VDC/600 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
1000 pF	5	11	18	15	FKP1M011004B_____	5	11	18	15	FKP1O111004B_____
1500 "	5	11	18	15	FKP1M011504B_____	5	11	18	15	FKP1O111504B_____
2200 "	5	11	18	15	FKP1M012204B_____	5	11	18	15	FKP1O112204B_____
3300 "	5	11	18	15	FKP1M013304B_____	5	11	18	15	FKP1O113304B_____
4700 "	6	12.5	18	15	FKP1M014704C_____	6	12.5	18	15	FKP1O114704C_____
6800 "	7	14	18	15	FKP1M016804D_____	7	14	18	15	FKP1O116804D_____
0.01 µF	8	15	18	15	FKP1M021004F_____	8	15	18	15	FKP1O121004F_____
	6	15	26.5	22.5	FKP1M021005B_____	6	15	26.5	22.5	FKP1O121005B_____
0.015 "	6	15	26.5	22.5	FKP1M021505B_____	6	15	26.5	22.5	FKP1O121505B_____
0.022 "	8.5	18.5	26.5	22.5	FKP1M022205F_____	8.5	18.5	26.5	22.5	FKP1O122205F_____
0.033 "	10.5	20.5	26.5	22.5	FKP1M023305H_____	10.5	20.5	26.5	22.5	FKP1O123305H_____
	9	19	31.5	27.5	FKP1M023306A_____	9	19	31.5	27.5	FKP1O123306A_____
0.047 "	11	21	31.5	27.5	FKP1M024706B_____	11	21	31.5	27.5	FKP1O124706B_____
0.068 "	13	24	31.5	27.5	FKP1M026806D_____	13	24	31.5	27.5	FKP1O126806D_____
	11	22	41.5	37.5	FKP1M026807B_____	11	22	41.5	37.5	FKP1O126807B_____
0.1 µF	13	24	41.5	37.5	FKP1M031007C_____	13	24	41.5	37.5	FKP1O131007C_____
0.15 "	15	26	41.5	37.5	FKP1M031507D_____	15	26	41.5	37.5	FKP1O131507D_____
0.22 "	19	32	41.5	37.5	FKP1M032207F_____	19	32	41.5	37.5	FKP1O132207F_____
0.33 "	20	39.5	41.5	37.5	FKP1M033307G_____	20	39.5	41.5	37.5	FKP1O133307G_____
0.47 "	31	46	41.5	37.5	FKP1M034707I_____	31	46	41.5	37.5	FKP1O134707I_____
0.68 "	35	50	41.5	37.5	FKP1M036807J_____	35	50	41.5	37.5	FKP1O136807J_____
1.0 µF	40	55	41.5	37.5	FKP1M041007K_____	40	55	41.5	37.5	FKP1O141007K_____
	35	50	57	52.5	FKP1M041009F_____	35	50	57	52.5	FKP1O141009F_____
1.5 "	45	55	57	52.5	FKP1M041509H_____	45	55	57	52.5	FKP1O141509H_____
2,2 "	45	65	57	52,5	FKP1M042209J_____	45	65	57	52,5	FKP1O142209J_____

* AC voltages: $f \leq 1000 \text{ Hz}$; $1.4 \times U_{\text{rms}} + \text{UDC} \leq U_r$

New range and values


** PCM = Printed circuit module = pin spacing

Dims. in mm.

Ionisation inception level in isolated cases may be lower than admissible rated AC voltage.


Part number completion:	
Version code:	2-pin = 00
	4-pin = D4
Tolerance:	20 % = M
	10 % = K
	5 % = J
Packing:	bulk = S
Pin length:	6-2 = SD
Taped version see page 145.	

2-pin version



∅ d	PCM
0.8	15 - 27.5
1.0	37.5

4-pin version



W	PCM	b	∅ d	c
17	37.5	10	1.0	0.4
19	37.5	10	1.0	0.4
20	37.5	12.5	1.0	0.4
24	37.5	12.5	1.0	0.4
31	37.5	20	1.0	0.4
35	37.5	20	1.0	0.4
40	37.5	20	1.0	0.4
35	52.5	20	1.2	0.8
45	52.5	20	1.2	0.8

Rights reserved to amend design data without prior notification

Continuation page 76

Continuation

General Data

Capacitance	1250 VDC/600 VAC*					1600 VDC/650 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
100 pF						5	11	18	15	FKP1T001004B_____
150 "						5	11	18	15	FKP1T001504B_____
220 "						5	11	18	15	FKP1T002204B_____
330 "						5	11	18	15	FKP1T003304B_____
470 "						5	11	18	15	FKP1T004704B_____
680 "						5	11	18	15	FKP1T006804B_____
1000 pF	5	11	18	15	FKP1R011004B_____	6	12.5	18	15	FKP1T011004C_____
1500 "	5	11	18	15	FKP1R011504B_____	5	14	26.5	22.5	FKP1T011005A_____
2200 "	5	11	18	15	FKP1R012204B_____	7	14	18	15	FKP1T011504D_____
3300 "	6	12.5	18	15	FKP1R013304C_____	5	14	26.5	22.5	FKP1T011505A_____
4700 "	7	14	18	15	FKP1R014704D_____	8	15	18	15	FKP1T012204F_____
6800 "	8	15	18	15	FKP1R016804F_____	5	14	26.5	22.5	FKP1T012205A_____
	5	14	26.5	22.5	FKP1R016805A_____	6	15	26.5	22.5	FKP1T013305B_____
0.01 µF	7	16.5	26.5	22.5	FKP1R021005D_____	7	16.5	26.5	22.5	FKP1T014705D_____
0.015 "	8.5	18.5	26.5	22.5	FKP1R021505F_____	8.5	18.5	26.5	22.5	FKP1T016805F_____
0.022 "	10.5	20.5	26.5	22.5	FKP1R022205H_____					
0.033 "	11	21	31.5	27.5	FKP1R023306B_____					
	9	19	41.5	37.5	FKP1R023307A_____					
0.047 "	13	24	31.5	27.5	FKP1R024706D_____					
	11	22	41.5	37.5	FKP1R024707B_____					
0.068 "	11	22	41.5	37.5	FKP1R026807B_____					
0.1 µF	15	26	41.5	37.5	FKP1R031007D_____					
0.15 "	17	29	41.5	37.5	FKP1R031507E_____					
0.22 "	19	32	41.5	37.5	FKP1R032207F_____					
0.33 "	24	45.5	41.5	37.5	FKP1R033307H_____					
0.47 "	31	46	41.5	37.5	FKP1R034707I_____					
0.68 "	40	55	41.5	37.5	FKP1R036807K_____					
1.0 µF	35	50	57	52.5	FKP1R041009F_____					
1.5 "	45	65	57	52.5	FKP1R041509J_____					

* AC voltages: $f \leq 1000 \text{ Hz}$; $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_r$

New values

** PCM = Printed circuit module = pin spacing

Dims. in mm.

Ionisation inception level in isolated cases may be lower than admissible rated AC voltage.

Part number completion:		
Version code:	2-pin	= 00
	4-pin	= D4
Tolerance:	20 %	= M
	10 %	= K
	5 %	= J
Packing:	bulk	= S
Pin length:	6-2	= SD
Taped version see page 145.		

Rights reserved to amend design data without prior notification

Continuation page 77

Continuation

General Data

Capacitance	2000 VDC/700 VAC~*					4000 VDC/700 VAC~*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
100 pF	5	11	18	15	FKP1U001004B_____					
150 "	5	11	18	15	FKP1U001504B_____					
220 "	5	11	18	15	FKP1U002204B_____					
330 "	6	12.5	18	15	FKP1U003304C_____					
470 "	6	12.5	18	15	FKP1U004704C_____	5	14	26.5	22.5	FKP1X004705A_____
680 "	6	12.5	18	15	FKP1U006804C_____	5	14	26.5	22.5	FKP1X006805A_____
1000 pF	7	14	18	15	FKP1U011004D_____	5	14	26.5	22.5	FKP1X011005A_____
	5	14	26.5	22.5	FKP1U011005A_____					
1500 "	6	15	26.5	22.5	FKP1U011505B_____	7	16.5	26.5	22.5	FKP1X011505D_____
2200 "	7	16.5	26.5	22.5	FKP1U012205D_____	8.5	18.5	26.5	22.5	FKP1X012205F_____
3300 "	7	16.5	26.5	22.5	FKP1U013305D_____	10.5	20.5	26.5	22.5	FKP1X013305H_____
4700 "	8.5	18.5	26.5	22.5	FKP1U014705F_____	11	21	31.5	27.5	FKP1X014706B_____
6800 "	10.5	20.5	26.5	22.5	FKP1U016805H_____	13	24	31.5	27.5	FKP1X016806D_____
0.01 µF	11	21	31.5	27.5	FKP1U021006B_____	15	26	31.5	27.5	FKP1X021006F_____
0.015 "	13	24	31.5	27.5	FKP1U021506D_____	13	24	41.5	37.5	FKP1X021507C_____
0.022 "	15	26	31.5	27.5	FKP1U022206F_____	17	29	41.5	37.5	FKP1X022207E_____
	13	24	41.5	37.5	FKP1U022207C_____					
0.033 "	13	24	41.5	37.5	FKP1U023307C_____	20	39.5	41.5	37.5	FKP1X023307G_____
0.047 "	17	29	41.5	37.5	FKP1U024707E_____	24	45.5	41.5	37.5	FKP1X024707H_____
0.068 "	19	32	41.5	37.5	FKP1U026807F_____	31	46	41.5	37.5	FKP1X026807I_____
0.1 µF	20	39.5	41.5	37.5	FKP1U031007G_____	35	50	41.5	37.5	FKP1X031007J_____
0.15 "	24	45.5	41.5	37.5	FKP1U031507H_____	40	55	41.5	37.5	FKP1X031507K_____
0.22 "	35	50	41.5	37.5	FKP1U032207J_____	45	55	57	52.5	FKP1X032209H_____
0.22 "	40	55	41.5	37.5	FKP1U033307K_____					
0.47 "	45	55	57	52.5	FKP1U034709H_____					
0.68 "	45	65	57	52.5	FKP1U036809J_____					

* AC voltages: $f \leq 1000 \text{ Hz}$; $1.4 \times U_{\text{rms}} + \text{UDC} \leq U_r$

New values

** PCM = Printed circuit module = pin spacing

Dims. in mm.


Ionisation inception level in isolated cases may be lower than admissible rated AC voltage.

Part number completion:

Version code: 2-pin = 00
4-pin = D4
Tolerance: 20 % = M
10 % = K
5 % = J
Packing: bulk = S
Pin length: 6-2 = SD


Taped version see page 145.

2-pin version



Ø d	PCM
0.8	15 - 27.5
1.0	37.5

4-pin version



W	PCM	b	Ø d	c
17	37.5	10	1.0	0.4
19	37.5	10	1.0	0.4
20	37.5	12.5	1.0	0.4
24	37.5	12.5	1.0	0.4
31	37.5	20	1.0	0.4
35	37.5	20	1.0	0.4
40	37.5	20	1.0	0.4
35	52.5	20	1.2	0.8
45	52.5	20	1.2	0.8

Rights reserved to amend design data without prior notification.

Continuation page 78

Continuation

General Data

Capacitance	W	H	L	PCM**	Part number	Dims. in mm.
470 pF	5	14	26.5	22.5	FKP1Y004705A_	Ionisation inception level in isolated cases may be lower than admissible rated AC voltage.
680 "	5	14	26.5	22.5	FKP1Y006805A_	
1000 pF	5	14	26.5	22.5	FKP1Y011005A_	
1500 "	7	16.5	26.5	22.5	FKP1Y011505D_	
2200 "	10.5	20.5	26.5	22.5	FKP1Y012205H_	
3300 "	10.5	20.5	26.5	22.5	FKP1Y013305H_	
4700 "	11	21	31.5	27.5	FKP1Y014706B_	
6800 "	13	24	31.5	27.5	FKP1Y016806D_	
0.01 µF	15	26	31.5	27.5	FKP1Y021006F_	
0.015 "	13	24	41.5	37.5	FKP1Y021507C_	
0.022 "	17	29	41.5	37.5	FKP1Y022207E_	
0.033 "	20	39.5	41.5	37.5	FKP1Y023307G_	
0.047 "	24	45.5	41.5	37.5	FKP1Y024707H_	
0.068 "	31	46	41.5	37.5	FKP1Y026807I_	
0.1 µF	35	50	41.5	37.5	FKP1Y031007J_	
0.15 "	40	55	41.5	37.5	FKP1Y031507K_	
0.22 "	45	55	57	52.5	FKP1Y032209H_	

Part number completion:	
Version code:	2-pin = 00
	4-pin = D4
Tolerance:	20 % = M
	10 % = K
	5 % = J
Packing:	bulk = S
Pin length:	6-2 = SD
Taped version see page 145.	


* AC voltages: $f \leq 1000 \text{ Hz}$; $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_r$

New values

** PCM = Printed circuit module = pin spacing

Rights reserved to amend design data without prior notification.

Permissible AC voltage
in relation to frequency
at 10° C internal temperature rise
(general guide).



Recommendation for Processing and Application of Through-Hole Capacitors

Soldering Process

Internal temperature of the capacitor must be kept as follows:

Polyester: preheating: $T_{\max.} \leq 125^{\circ}\text{C}$
soldering: $T_{\max.} \leq 135^{\circ}\text{C}$

Polypropylene: preheating: $T_{\max.} \leq 100^{\circ}\text{C}$
soldering: $T_{\max.} \leq 110^{\circ}\text{C}$

Single wave soldering

Soldering bath temperature: $T < 260^{\circ}\text{C}$


Dwell time: $t < 5\text{ sec}$

Double wave soldering

Soldering bath temperature: $T < 260^{\circ}\text{C}$

Dwell time: $\Sigma t < 5\text{ sec}$

Due to different soldering processes and heat requirements the graphs are to be regarded as a recommendation only.



WIMA Quality and Environmental Philosophy

ISO 9001:2008 Certification

ISO 9001:2008 is an international basic standard of quality assurance systems for all branches of industry. The approval according to ISO 9001:2008 of our factories by the infaz (Institut für Auditierung und Zertifizierung) certifies that organisation, equipment and monitoring of quality assurance in our factories correspond to internationally recognized standards.

WIMA WPCS

The WIMA Process Control System (WPCS) is a quality surveillance and optimization system developed by WIMA. WPCS is a major part of the quality-oriented WIMA production. Points of application during production process:

- incoming material inspection
- metallization
- film inspection
- schoopage
- pre-healing
- pin attachment
- cast resin preparation/encapsulation
- 100% final inspection
- Testing as per customer requirements

WIMA Environmental Policy

All WIMA capacitors, irrespective of whether through-hole devices or SMD, are made of environmentally friendly materials. Neither during manufacture nor in the product itself any toxic substances are used, e.g.

- | | |
|------------------------|------------|
| – Lead | – PBB/PBDE |
| – PCB | – Arsenic |
| – CFC | – Cadmium |
| – Hydrocarbon chloride | – Mercury |
| – Chromium 6+ | – etc. |

We merely use pure, recyclable materials for packing our components, such as:

- carton
- cardboard
- adhesive tape made of paper
- polystyrene

We almost completely refrain from using packing materials such as:

- foamed polystyrene (Styropor®)
- adhesive tapes made of plastic
- metal clips

RoHS Compliance

According to the RoHS Directive 2011/65/EU certain hazardous substances like e.g. lead, cadmium, mercury must not be used any longer in electronic equipment as of July 1st, 2006. For the sake of the environment WIMA has refrained from using such substances since years already.



WIMA Kondensatoren sind bleifrei
konform RoHS 2011/65/EU

WIMA capacitors are lead free
in accordance with RoHS 2011/65/EU

Tape for lead-free WIMA capacitors

DIN EN ISO 14001:2004

WIMA's environmental management has been established in accordance with the guidelines of DIN EN ISO 14001:2004 to optimize the production processes with regard to energy and resources.

Typical Dimensions for Taping Configuration




Diagram 1:
PCM 2.5/5/7.5mm




Diagram 2: PCM 10/15 mm

Diagram 3: PCM 22.5 and 27.5*mm

*PCM 27.5 taping possible with two feed holes between components

Designation	Symbol	Dimensions for Radial Taping						
		PCM 2.5 taping	PCM 5 taping	PCM 7.5 taping	PCM 10 taping*	PCM 15 taping*	PCM 22.5 taping	PCM 27.5 taping
Carrier tape width	W	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5
Hold-down tape width	W ₀	6.0 for hot-sealing adhesive tape	6.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape
Hole position	W ₁	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5
Hold-down tape position	W ₂	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.
Feed hole diameter	D ₀	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2
Pitch of component	P	12.7 ±1.0	12.7 ±1.0	12.7 ±1.0	25.4 ±1.0	25.4 ±1.0	38.1 ±1.5	38.1 ±1.5 or 50.8 ±1.5
Feed hole pitch	P ₀	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch
Feed hole centre to pin	P ₁	5.1 ±0.5	3.85 ±0.7	2.6 ±0.7	7.7 ±0.7	5.2 ±0.7	7.8 ±0.7	5.3 ±0.7
Hole centre to component centre	P ₂	6.35 ±1.3	6.35 ±1.3	6.35 ±1.3	12.7 ±1.3	12.7 ±1.3	19.05 ±1.3	19.05 ±1.3
Feed hole centre to bottom edge of the component	H	16.5 ±0.3 18.5 ±0.5	16.5 ±0.3 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5
Feed hole centre to top edge of the component	H ₁	H+H _{component} < H ₁ 32.25 max.	H+H _{component} < H ₁ 32.25 max.	H+H _{component} < H ₁ 24.5 to 31.5	H+H _{component} < H ₁ 25.0 to 31.5	H+H _{component} < H ₁ 26.0 to 37.0	H+H _{component} < H ₁ 30.0 to 43.0	H+H _{component} < H ₁ 35.0 to 45.0
Pin spacing at upper edge of carrier tape	F	2.5 ±0.5	5.0 ^{+0.8} _{-0.2}	7.5 ±0.8	10.0 ±0.8	15 ±0.8	22.5 ±0.8	27.5 ±0.8
Pin diameter	d	0.4 ±0.05	0.5 ±0.05	0.5 ±0.05 or 0.6 ^{+0.06} _{-0.05}	0.5 ±0.05 or 0.6 ^{+0.06} _{-0.05}	0.8 ^{+0.08} _{-0.05}	0.8 ^{+0.08} _{-0.05}	0.8 ^{+0.08} _{-0.05}
Component alignment	Δh	± 2.0 max.	± 2.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.
Total tape thickness	t	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2
Package (see also page 146)		ROLL/AMMO			AMMO			
		REEL ø 360 max. ø 30 ±1	B 52 ±2 58 ±2 } depending on comp. dimensions		REEL ø 360 max. ø 30 ±1	B 52 ±2 58 ±2 or 66 ±2	REEL ø 500 max. ø 25 ±1	B 54 ±2 60 ±2 or 68 ±2 } depending on PCM and component dimensions
Unit		see details page 147.						

Dims in mm.

* Diameter of pins see General Data.


Please clarify customer-specific deviations with the manufacturer.

* PCM 10 and PCM 15 can be crimped to PCM 7.5.


Position of components according to PCM 7.5 (sketch 11). P₀ = 12.7 or 15.0 is possible

Types of Tape Packaging of Capacitors for Automatic Radial Insertion


■ ROLL Packaging



■ AMMO Packaging



■ REEL Packaging



BAR CODE (Labelling)

Labelling of package units in plain text and with alphanumerical Bar Code

Scanner decoding of

- WIMA supplier number
- Customer's P/O number
- Customer's part number
- WIMA confirmation number
- WIMA part number
- Lot number
- Date code
- Quantity

In addition part description of

- article
- capacitance value
- rated voltage
- dimensions
- capacitance tolerance
- packing

as well as gross weight and customer's name are indicated in plain text.

WIMA Best Capacitors Made In Germany		Werk Unna	
Supplier-ID: 123456789	RoHS 2011/65/EU	Date Code: 08.10.10	
Purchase Order No. (P/O): Bestellung xyz		Quantity: 5.000	
Customer Part No.: KUNDETEILENUMMER		Customer No.: 0000100002	
		Gross Weight [g]: 1870	
WIMA Confirmation No.: 0001004053000100		WIMA Part No.: MKS2C034701C00K88D	
Handling Unit:	MKS 2	QTY: 5.000	COO: DE
	MKS 2 0.47 μF 63 VDC 3.5x8.5x7.2 RM5		
	Standard 10% Loss - Standard	Drühte 6-2	Week 03/2011
1000067326	Vorlage Debitor Inland		

BARCODE „Code 39“

Packing Quantities for Capacitors with Radial Pins in PCM 2.5 mm to 22.5 mm



PCM	Size				bulk	ROLL		REEL				AMMO			
						H16.5	H18.5	ø 360		ø 500		340 x 340		490 x 370	
	W	H	L	Codes				H16.5	H18.5	H16.5	H18.5	H16.5	H18.5	H16.5	H18.5
					S	N	O	F	I	H	J	A	C	B	D
2.5 mm	2.5	7	4.6	0B	5000		2200	2500		–		2800		–	
	3	7.5	4.6	0C	5000		2000	2300		–		2300		–	
	3.8	8.5	4.6	0D	5000		1500	1800		–		1800		–	
	4.6	9	4.6	0E	5000		1200	1500		–		1500		–	
	5.5	10	4.6	0F	5000		900	1200		–		1200		–	
5 mm	2.5	6.5	7.2	1A	5000		2200	2500		–		2800		–	
	3	7.5	7.2	1B	5000		2000	2300		–		2300		–	
	3.5	8.5	7.2	1C	5000		1600	2000		–		2000		–	
	4.5	6	7.2	1D	6000		1300	1500		–		1500		–	
	4.5	9.5	7.2	1E	4000		1300	1500		–		1500		–	
	5	10	7.2	1F	3500		1100	1400		–		1400		–	
	5.5	7	7.2	1G	4000		1000	1200		–		1200		–	
	5.5	11.5	7.2	1H	2500		1000	1200		–		1200		–	
	6.5	8	7.2	1I	2500		800	1000		–		1000		–	
	7.2	8.5	7.2	1J	2500		700	1000		–		1000		–	
	7.2	13	7.2	1K	2000		700	950		–		1000		–	
	8.5	10	7.2	1L	2000		600	800		–		800		–	
	8.5	14	7.2	1M	1500		600	800		–		800		–	
	11	16	7.2	1N	1000		500	600		–		400		–	
7.5 mm	2.5	7	10	2A	5000		–	2500		4400		2500		–	
	3	8.5	10	2B	5000		–	2200		4300		2300		4150	
	4	9	10	2C	4000		–	1700		3200		1700		3100	
	4.5	9.5	10.3	2D	3500		–	1500		2900		1400		2700	
	5	10.5	10.3	2E	3000		–	1300		2500		1300		–	
	5.7	12.5	10.3	2F	2000		–	1000		2200		1100		–	
	7.2	12.5	10.3	2G	1500		–	900		1800		1000		–	
10 mm	3	9	13	3A	3000		–	1100		2200		–		1900	
	4	8.5	13.5	FA	3000		–	900		1600		–		1450	
	4	9	13	3C	3000		–	900		1600		–		1450	
	4	9.5	13	3D	3000		–	900		1600		–		1400	
	5	10	13.5	FB	2000		–	700		1300		–		1200	
	5	11	13	3F	3000		–	700		1300		–		1200	
	6	12	13	3G	2400		–	550		1100		–		1000	
	6	12.5	13	3H	2400		–	550		1100		–		1000	
15 mm	8	12	13	3I	2000		–	400		800		–		740	
	5	11	18	4B	2400		–	600		1200		–		1150	
	5	13	19	FC	1000		–	600		1200		–		1200	
	6	12.5	18	4C	2000		–	500		1000		–		1000	
	6	14	19	FD	1000		–	500		1000		–		1000	
	7	14	18	4D	1600		–	450		900		–		850	
	7	15	19	FE	1000		–	450		900		–		850	
	8	15	18	4F	1200		–	400		800		–		740	
	8	17	19	FF	500		–	400		800		–		740	
	9	14	18	4H	1200		–	350		700		–		650	
	9	16	18	4J	900		–	350		700		–		650	
22.5 mm	10	18	19	FG	500		–	300		650		–		590	
	11	14	18	4M	1000		–	300		600		–		540	
	5	14	26.5	5A	1200		–	–		800		–		770	
	6	15	26.5	5B	1000		–	–		700		–		640	
	7	16.5	26.5	5D	760		–	–		600		–		550	
	8	20	28	FH	500		–	–		500		–		480	
	8.5	18.5	26.5	5F	500		–	–		480		–		450	
	10	22	28	FI	570*		–	–		420		–		380	
22.5 mm	10.5	19	26.5	5G	594*		–	–		400		–		360	
	10.5	20.5	26.5	5H	594*		–	–		400		–		360	
	11	21	26.5	5I	561*		–	–		380		–		350	
	12	24	28	FJ	480*		–	–		350		–		310	

* TPS (Tray-Packing-System). Plate versions may have different packing units.
Samples and pre-production needs on request.

■ Moulded versions.

Rights reserved to amend design data without prior notification.

Packing Quantities for Capacitors with Radial Pins in PCM 27.5 mm to 52.5 mm

PCM	Size				bulk	ROLL		pcs. per packing unit				AMMO			
								REEL							
	W	H	L	Codes		H16.5	H18.5	ø 360	ø 500	340 x 340	490 x 370				
					S	N	O	F	I	H	J	A	C	B	D
27.5 mm	9	19	31.5	6A	567*	–	–	–	–	460/340*	–	–	–	420	–
	11	21	31.5	6B	459*	–	–	–	–	380/280*	–	–	–	350	–
	13	24	31.5	6D	378*	–	–	–	–	300	–	–	–	290	–
	13	25	33	FK	405*	–	–	–	–	–	–	–	–	–	–
	15	26	31.5	6F	324*	–	–	–	–	270	–	–	–	250	–
	15	26	33	FL	324*	–	–	–	–	–	–	–	–	–	–
	17	29	31.5	6G	198*	–	–	–	–	–	–	–	–	–	–
	17	34.5	31.5	6I	198*	–	–	–	–	–	–	–	–	–	–
	20	32	33	FM	162*	–	–	–	–	–	–	–	–	–	–
	20	39.5	31.5	6J	162*	–	–	–	–	–	–	–	–	–	–
37.5 mm	9	19	41.5	7A	441*	–	–	–	–	–	–	–	–	–	–
	11	22	41.5	7B	357*	–	–	–	–	–	–	–	–	–	–
	13	24	41.5	7C	294*	–	–	–	–	–	–	–	–	–	–
	15	26	41.5	7D	252*	–	–	–	–	–	–	–	–	–	–
	17	29	41.5	7E	154*	–	–	–	–	–	–	–	–	–	–
	19	32	41.5	7F	140*	–	–	–	–	–	–	–	–	–	–
	20	39.5	41.5	7G	126*	–	–	–	–	–	–	–	–	–	–
	24	45.5	41.5	7H	112*	–	–	–	–	–	–	–	–	–	–
	31	46	41.5	7I	84*	–	–	–	–	–	–	–	–	–	–
	35	50	41.5	7J	35*	–	–	–	–	–	–	–	–	–	–
	40	55	41.5	7K	28*	–	–	–	–	–	–	–	–	–	–
48.5 mm	19	31	56	8D	120*	–	–	–	–	–	–	–	–	–	–
	23	34	56	8E	80*	–	–	–	–	–	–	–	–	–	–
	27	37.5	56	8H	84*	–	–	–	–	–	–	–	–	–	–
	33	48	56	8J	25*	–	–	–	–	–	–	–	–	–	–
	37	54	56	8L	25*	–	–	–	–	–	–	–	–	–	–
52.5 mm	25	45	57	9D	70*	–	–	–	–	–	–	–	–	–	–
	30	45	57	9E	60*	–	–	–	–	–	–	–	–	–	–
	35	50	57	9F	25*	–	–	–	–	–	–	–	–	–	–
	45	55	57	9H	20*	–	–	–	–	–	–	–	–	–	–
	45	65	57	9J	20*	–	–	–	–	–	–	–	–	–	–

* for 2-inch transport pitches.

* TPS (Tray-Packing-System). Plate versions may have different packing units.
Samples and pre-production needs on request.

■ Moulded versions.

Rights reserved to amend design data without prior notification.

Updated data on www.wima.com

A WIMA part number consists of 18 digits and is composed as follows:

- Field 1 - 4: Type description
- Field 5 - 6: Rated voltage
- Field 7 - 10: Capacitance
- Field 11 - 12: Size and PCM
- Field 13 - 14: Version code (e.g. Snubber versions)
- Field 15: Capacitance tolerance
- Field 16: Packing
- Field 17 - 18: Pin length (untaped)

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
M	K	S	2	C	0	2	1	0	0	1	A	0	0	M	S	S	D
MKS 2				63 VDC		0.01 μF			2.5x6.5x7.2			-		20%	bulk	6 -2	
Type description: SMD-PET = SMDT SMD-PEN = SMDN SMD-PPS = SMDI FKP 02 = FKPO MKS 02 = MKSO FKS 2 = FKS2 FKP 2 = FKP2 FKS 3 = FKS3 FKP 3 = FKP 3 MKS 2 = MKS2 MKP 2 = MKP2 MKS 4 = MKS4 MKP 4C = MKPC MKP 4 = MKP4 MKP 10 = MKP1 FKP 1 = FKP1 MKP-X2 = MKX2 MKP-X1 R = MKX1 MKP-Y2 = MKY2 MP 3-X2 = MPX2 MP 3-X1 = MPX1 MP 3-Y2 = MPY2 MP 3R-Y2 = MPRY MKP 4F = MKPF Snubber MKP = SNMP Snubber FKP = SNFP GTO MKP = GTOM DC-LINK MKP 3 = DCP3 DC-LINK MKP 4 = DCP4 DC-LINK MKP 4S = DCP5 DC-LINK MKP 5 = DCP5 DC-LINK MKP 6 = DCP6 DC-LINK HC = DCHC DC-LINK HY = DCHY				Rated voltage: 50 VDC = B0 63 VDC = C0 100 VDC = D0 250 VDC = F0 400 VDC = G0 450 VDC = H0 520 VDC = H2 600 VDC = I0 630 VDC = J0 700 VDC = K0 800 VDC = L0 850 VDC = M0 900 VDC = N0 1000 VDC = O1 1100 VDC = P0 1200 VDC = Q0 1250 VDC = R0 1500 VDC = S0 1600 VDC = T0 2000 VDC = U0 2500 VDC = V0 3000 VDC = W0 4000 VDC = X0 6000 VDC = Y0 250 VAC = 0VV 275 VAC = 1VV 300 VAC = 2VV 305 VAC = AVV 350 VAC = BVV 440 VAC = 4VV 500 VAC = 5VV ...		Capacitance: 22 pF = 0022 47 pF = 0047 100 pF = 0100 150 pF = 0150 220 pF = 0220 330 pF = 0330 470 pF = 0470 680 pF = 0680 1000 pF = 1100 1500 pF = 1150 2200 pF = 1220 3300 pF = 1330 4700 pF = 1470 6800 pF = 1680 0.01 μF = 2100 0.022 μF = 2220 0.047 μF = 2470 0.1 μF = 3100 0.22 μF = 3220 0.47 μF = 3470 1 μF = 4100 2.2 μF = 4220 4.7 μF = 4470 10 μF = 5100 22 μF = 5220 47 μF = 5470 100 μF = 6100 220 μF = 6220 1000 μF = 7100 1500 μF = 7150 ...			Size: 4.8x3.3x3 Size 1812 = KA 4.8x3.3x4 Size 1812 = KB 5.7x5.1x3.5 Size 2220 = QA 5.7x5.1x4.5 Size 2220 = QB 7.2x6.1x3 Size 2824 = TA 7.2x6.1x5 Size 2824 = TB 10.2x7.6x5 Size 4030 = VA 12.7x10.2x6 Size 5040 = XA 15.3x13.7x7 Size 6054 = YA 2.5x7x4.6 PCM 2.5 = 0B 3x7.5x4.6 PCM 2.5 = 0C 2.5x6.5x7.2 PCM 5 = 1A 3x7.5x7.2 PCM 5 = 1B 2.5x7x10 PCM 7.5 = 2A 3x8.5x10 PCM 7.5 = 2B 3x9x13 PCM 10 = 3A 4x9x13 PCM 10 = 3C 5x11x18 PCM 15 = 4B 6x12.5x18 PCM 15 = 4C 5x14x26.5 PCM 22.5 = 5A 6x15x26.5 PCM 22.5 = 5B 9x19x31.5 PCM 27.5 = 6A 11x21x31.5 PCM 27.5 = 6B 9x19x41.5 PCM 37.5 = 7A 11x22x41.5 PCM 37.5 = 7B 19x31x56 PCM 48.5 = 8D 25x45x57 PCM 52.5 = 9D ...			Tolerance: ±20% = M ±10% = K ±5% = J ±2.5% = H ±1% = E ... Packing: AMMO H16.5 340x340 = A AMMO H16.5 490x370 = B AMMO H18.5 340x340 = C AMMO H18.5 490x370 = D REEL H16.5 360 = F REEL H16.5 500 = H REEL H18.5 360 = I REEL H18.5 500 = J ROLL H16.5 = N ROLL H18.5 = O BLISTER W12 180 = P BLISTER W12 330 = Q BLISTER W16 330 = R BLISTER W24 330 = T Bulk/TPS Standard = S ... Pin length (untaped) 3.5 ±0.5 = C9 6 -2 = SD 16 ±1 = P1 ... Pin length (taped) none = 00					
Version code: Standard = 00 Version A1 = 1A Version A1.1.1 = 1B Version A2 = 2A ...																	

The data on this page is not complete and serves only to explain the part number system. Part number information is listed on the pages of the respective WIMA range.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

WIMA:

[FKP1-.22/630/5](#) [FKP1-.033/2KV/5](#) [FKP1-2200/2000/10P22](#) [FKP1-1000/1250/5](#) [FKP1-.033/2KV/5P37](#) [FKP1-100/2KV/5T](#) [FKP1-1000/1250/5P15](#) [FKP1O121004F00JSSD](#) [FKP1G022204D00JSSD](#) [FKP1G026805F00JSSD](#) [FKP1G026805F00KSSD](#) [FKP1G031506B00MYSD](#) [FKP1G032206D00KYSD](#) [FKP1J014704B00KSSD](#) [FKP1J016804C00JSSD](#) [FKP1J021504F00KSSD](#) [FKP1J032207D00KYSD](#) [FKP1O114704C00JSSD](#) [FKP1O122205F00KSSD](#) [FKP1O124706B00KYSD](#) [FKP1O124706B00MYSD](#) [FKP1O132207F00MYSD](#) [FKP1R014704D00MSSD](#) [FKP1R031007D00JYSD](#) [FKP1R031507E00JYSD](#) [FKP1R032207F00KYSD](#) [FKP1T001004B00MSSD](#) [FKP1T001504B00KSSD](#) [FKP1T002204B00KSSD](#) [FKP1T004704B00MSSD](#) [FKP1T011504D00KSSD](#) [FKP1T012204F00JSSD](#) [FKP1T013305B00JSSD](#) [FKP1T013305B00KSSD](#) [FKP1T014705D00JSSD](#) [FKP1T016805F00JSSD](#) [FKP1T024707C00KYSD](#) [FKP1T031007E00JYSD](#) [FKP1U002204B00JSSD](#) [FKP1U003304C00JSSD](#) [FKP1U011004D00KSSD](#) [FKP1U011005A00KSSD](#) [FKP1U011505B00JSSD](#) [FKP1U021006B00KYSD](#) [FKP1U024707E00KYSD](#) [FKP1X004705A00JSSD](#) [FKP1X012205F00JSSD](#) [FKP1X021006F00KYSD](#) [FKP1X021507C00MYSD](#) [FKP1Y021006F00KYSD](#) [FKP1Y022207E00MYSD](#) [FKP1T001004B00KSSD](#) [FKP1Y004705A00JSSD](#) [FKP1G032206D00JYSD](#) [FKP1G024705D00JSSD](#) [FKP1U013305D00JSSD](#) [FKP1T006804B00JSSD](#) [FKP1R021005D00JSSD](#) [FKP1T026807D00JYSD](#) [FKP1R026807B00KYSD](#) [FKP1X022207E00JYSD](#) [FKP1J031006D00JYSD](#) [FKP1J032207D00JYSD](#) [FKP1J022205D00KSSD](#) [FKP1U022207C00JYSD](#) [FKP1U016805H00JYSD](#) [FKP1R031007D00KYSD](#) [FKP1G031005H00JYSD](#) [FKP1T002204B00JSSD](#) [FKP1R031507E00KYSD](#) [FKP1U021006B00JYSD](#) [FKP1J014704B00JSSD](#) [FKP1U023307C00JYSD](#) [FKP1R022205H00JYSD](#) [FKP1R012204B00KSSD](#) [FKP1J022205D00JSSD](#) [FKP1R032207F00JYSD](#) [FKP1U001004B00JSSD](#) [FKP1T021506B00JYSD](#) [FKP1R023306B00JYSD](#) [FKP1U014705F00JSSD](#) [FKP1O123305H00KYSD](#) [FKP1T001504B00JSSD](#) [FKP1T031007E00KYSD](#) [FKP1O113304B00JSSD](#) [FKP1R011504B00KSSD](#) [FKP1T022206B00JYSD](#) [FKP1T003304B00JSSD](#) [FKP1R024706D00JYSD](#) [FKP1R021505F00JSSD](#) [FKP1Y022207E00JYSD](#) [FKP1T021005H00JYSD](#) [FKP1T004704B00JSSD](#) [FKP1T023306D00JYSD](#) [FKP1G021004B00JSSD](#) [FKP1O116804D00JSSD](#) [FKP1O124706B00JYSD](#) [FKP1U013305D00KSSD](#) [FKP1R021005D00KSSD](#) [FKP1U022206F00JYSD](#)