

Material Safety Data Sheet



Chemask® WF

1. Product and company identification

Product name	: Chemask® WF
Supplier	: Chemtronics 8125 Cobb Center Drive Kennesaw, GA 30152 Tel. 770-424-4888 or toll free 800-645-5244
Synonym	: Chemask® WF - Water Filterable
Trade name	: Chemask® WF - Water Filterable
Material uses	: Temporary Solder Masking Agent
Manufacturer	: ITW Chemtronics 8125 Cobb Center Drive Kennesaw, GA 30152 Tel. 770-424-4888 or toll free 800-645-5244
Code	: CWF1 , CWF5, CWF8, CWF1C, CWF5C, CWF8C
MSDS #	: 0718
Validation date	: 8/5/2013.
Print date	: 8/5/2013.
<u>In case of emergency</u>	: Chemtrec - 1-800-424-9300 or collect 703-527-3887 24/7
Product type	: Liquid.

2. Hazards identification

Emergency overview

Physical state	: Liquid.
Color	: White.
Hazard statements	: MAY CAUSE EYE AND SKIN IRRITATION. CONTAINS MATERIAL THAT MAY CAUSE TARGET ORGAN DAMAGE, BASED ON ANIMAL DATA. POSSIBLE CANCER HAZARD - CONTAINS MATERIAL WHICH MAY CAUSE CANCER, BASED ON ANIMAL DATA.
Precautionary measures	: Do not handle until all safety precautions have been read and understood. Obtain special instructions before use. Do not breathe vapor or mist. Do not eat, drink or smoke when using this product. Avoid contact with eyes, skin and clothing. Use personal protective equipment as required. Wash thoroughly after handling.
OSHA/HCS status	: This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Potential acute health effects

Inhalation	: Harmful by inhalation.
Ingestion	: Harmful if swallowed.
Skin	: Slightly irritating to the skin.
Eyes	: Slightly irritating to the eyes.

Potential chronic health effects

Chronic effects	: Contains material that may cause target organ damage, based on animal data.
Carcinogenicity	: Contains material which may cause cancer, based on animal data. Risk of cancer depends on duration and level of exposure.
Mutagenicity	: No known significant effects or critical hazards.
Teratogenicity	: No known significant effects or critical hazards.

2. Hazards identification

- Developmental effects** : No known significant effects or critical hazards.
- Fertility effects** : No known significant effects or critical hazards.
- Target organs** : Contains material which may cause damage to the following organs: upper respiratory tract, skin, eyes.

Over-exposure signs/symptoms

- Inhalation** : Adverse symptoms may include the following:
respiratory tract irritation
- Ingestion** : Adverse symptoms may include the following:
Irritating to mouth, throat and stomach.
nausea or vomiting
- Skin** : Adverse symptoms may include the following:
irritation
redness
- Eyes** : Adverse symptoms may include the following:
irritation
watering
redness

- Medical conditions aggravated by over-exposure** : Pre-existing disorders involving any target organs mentioned in this MSDS as being at risk may be aggravated by over-exposure to this product.

See toxicological information (Section 11)

3. Composition/information on ingredients

Name	CAS number	%
Cellulose	9004-34-6	5 - 20
titanium dioxide	13463-67-7	2 - 6

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

4. First aid measures

- Eye contact** : Check for and remove any contact lenses. Immediately flush eyes with plenty of water for at least 15 minutes, occasionally lifting the upper and lower eyelids. Get medical attention immediately.
- Skin contact** : In case of contact, immediately flush skin with plenty of water for at least 15 minutes while removing contaminated clothing and shoes. Wash clothing before reuse. Clean shoes thoroughly before reuse. Get medical attention immediately.
- Inhalation** : Move exposed person to fresh air. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. Loosen tight clothing such as a collar, tie, belt or waistband. Get medical attention immediately.
- Ingestion** : Wash out mouth with water. Do not induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention immediately.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation.
- Notes to physician** : No specific treatment. Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.

5. Fire-fighting measures

Flammability of the product : In a fire or if heated, a pressure increase will occur and the container may burst.

Extinguishing media

Suitable : Use an extinguishing agent suitable for the surrounding fire.

Not suitable : None known.

Special exposure hazards : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.

Hazardous thermal decomposition products : Decomposition products may include the following materials:
carbon dioxide
carbon monoxide
metal oxide/oxides

Special protective equipment for fire-fighters : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

6. Accidental release measures

Personal precautions : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Avoid breathing vapor or mist. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment (see Section 8).

Environmental precautions : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

Methods for cleaning up

Small spill : Stop leak if without risk. Move containers from spill area. Dilute with water and mop up if water-soluble. Alternatively, or if water-insoluble, absorb with an inert dry material and place in an appropriate waste disposal container. Dispose of via a licensed waste disposal contractor.

Large spill : Stop leak if without risk. Move containers from spill area. Approach release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13). Dispose of via a licensed waste disposal contractor. Contaminated absorbent material may pose the same hazard as the spilled product. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

7. Handling and storage

Handling : Put on appropriate personal protective equipment (see Section 8). Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. Do not get in eyes or on skin or clothing. Do not ingest. Avoid breathing vapor or mist. If during normal use the material presents a respiratory hazard, use only with adequate ventilation or wear appropriate respirator. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use. Empty containers retain product residue and can be hazardous. Do not reuse container.

Storage : Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination.

Recommended monitoring procedures : If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Reference should be made to appropriate monitoring standards. Reference to national guidance documents for methods for the determination of hazardous substances will also be required.

Hygiene measures : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

Respiratory

Hands

Eyes

Skin

Environmental exposure controls

- Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

9. Physical and chemical properties

Physical state	: Liquid.
Flash point	: [Product does not sustain combustion.]
Color	: White.
Boiling/condensation point	: 93°C (199.4°F)
Melting/freezing point	: 0°C (32°F)
Relative density	: 1.05
Vapor pressure	: 1.6 kPa (12 mm Hg) [room temperature]
Evaporation rate	: >1 (butyl acetate = 1)

10. Stability and reactivity

Chemical stability	: The product is stable.
Conditions to avoid	: Avoid all possible sources of ignition (spark or flame). open flames, sparks and static discharge
Incompatible materials	: Reactive or incompatible with the following materials: Strong oxidizing materials Alkaline.
Hazardous decomposition products	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.
Possibility of hazardous reactions	: Under normal conditions of storage and use, hazardous reactions will not occur.

11. Toxicological information

Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
Cellulose	LD50 Oral	Rat	>5 g/kg	-

Conclusion/Summary : Not available.

Chronic toxicity

Conclusion/Summary : Not available.

Irritation/Corrosion

Product/ingredient name	Result	Species	Score	Exposure	Observation
titanium dioxide	Skin - Mild irritant	Human	-	72 hours 300 Micrograms Intermittent	-

Conclusion/Summary : Not available.

Sensitizer

Conclusion/Summary : Not available.

Carcinogenicity

Conclusion/Summary : Not available.

Classification

Product/ingredient name	OSHA	IARC	NTP	ACGIH	EPA	NIOSH
titanium dioxide	-	2B	-	A4	-	+

Mutagenicity

Conclusion/Summary : Not available.

Teratogenicity

Conclusion/Summary : Not available.

Reproductive toxicity

Conclusion/Summary : Not available.

12. Ecological information

Ecotoxicity : No known significant effects or critical hazards.

Aquatic ecotoxicity

Product/ingredient name	Result	Species	Exposure
titanium dioxide	Acute EC50 5.83 mg/l Fresh water	Algae - Pseudokirchneriella subcapitata - Exponential growth phase	72 hours
	Acute LC50 3 mg/l Fresh water	Crustaceans - Ceriodaphnia dubia - Neonate	48 hours
	Acute LC50 5.5 ppm Fresh water	Daphnia - Daphnia magna - Juvenile (Fledgling, Hatchling, Weanling)	48 hours
	Acute LC50 1000 mg/l Fresh water	Fish - Pimephales promelas	96 hours
	Chronic NOEC 0.984 mg/l Fresh water	Algae - Pseudokirchneriella subcapitata - Exponential growth phase	72 hours

Conclusion/Summary : Not available.

Persistence/degradability

Conclusion/Summary : Not available.

Other adverse effects : No known significant effects or critical hazards.

13. Disposal considerations

Waste disposal : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Care should be taken when handling emptied containers that have not been cleaned or rinsed out. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Refer to Section 7: HANDLING AND STORAGE and Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION for additional handling information and protection of employees.

14. Transport information

Regulatory information	UN number	Proper shipping name	Classes	PG*	Label	Additional information
DOT Classification	Not regulated.	Coating Compound	-	-		-
TDG Classification	Not regulated.	Coating Compound	-	-		-
Mexico Classification	Not regulated.	Coating Compound	-	-		-
ADR/RID Class	Not regulated.	Coating Compound	-	-		-
IMDG Class	Not regulated.	Coating Compound	-	-		-

14. Transport information

IATA-DGR Class	Not regulated.	Coating Compound	-	-	-
-----------------------	----------------	------------------	---	---	---

PG* : Packing group

15. Regulatory information

HCS Classification : Carcinogen
Target organ effects

U.S. Federal regulations : **TSCA 8(a) CDR Exempt/Partial exemption**: Not determined
United States inventory (TSCA 8b): All components are listed or exempted.

Clean Air Act Section 112 (b) Hazardous Air Pollutants (HAPs) : Not listed

Clean Air Act Section 602 Class I Substances : Not listed

Clean Air Act Section 602 Class II Substances : Not listed

DEA List I Chemicals (Precursor Chemicals) : Not listed

DEA List II Chemicals (Essential Chemicals) : Not listed

SARA 302/304

Composition/information on ingredients

No products were found.

SARA 304 RQ : Not applicable.

SARA 311/312

Classification : Delayed (chronic) health hazard

Composition/information on ingredients

Name	%	Fire hazard	Sudden release of pressure	Reactive	Immediate (acute) health hazard	Delayed (chronic) health hazard
Cellulose titanium dioxide	5 - 20 2 - 6	No. No.	No. No.	No. No.	No. No.	Yes. Yes.

State regulations

Massachusetts : The following components are listed: CELLULOSE; TITANIUM DIOXIDE

New York : None of the components are listed.

New Jersey : The following components are listed: CELLULOSE; TITANIUM DIOXIDE; TITANIUM OXIDE (TiO₂)

Pennsylvania : The following components are listed: CELLULOSE; TITANIUM OXIDE (TiO₂)

California Prop. 65

WARNING: This product contains a chemical known to the State of California to cause cancer.

Ingredient name	Cancer	Reproductive	No significant risk level	Maximum acceptable dosage level
titanium dioxide	Yes.	No.	No.	No.

Canada inventory : All components are listed or exempted.

15. Regulatory information

International regulations

International lists

- : **Australia inventory (AICS)**: All components are listed or exempted.
- China inventory (IECSC)**: All components are listed or exempted.
- Japan inventory**: All components are listed or exempted.
- Korea inventory**: All components are listed or exempted.
- Malaysia Inventory (EHS Register)**: Not determined.
- New Zealand Inventory of Chemicals (NZIoC)**: All components are listed or exempted.
- Philippines inventory (PICCS)**: All components are listed or exempted.
- Taiwan inventory (CSNN)**: Not determined.

Chemical Weapons Convention List Schedule I Chemicals

- : Not listed

Chemical Weapons Convention List Schedule II Chemicals

- : Not listed

Chemical Weapons Convention List Schedule III Chemicals

- : Not listed

16. Other information

Label requirements

- : MAY CAUSE EYE AND SKIN IRRITATION. CONTAINS MATERIAL THAT MAY CAUSE TARGET ORGAN DAMAGE, BASED ON ANIMAL DATA. POSSIBLE CANCER HAZARD - CONTAINS MATERIAL WHICH MAY CAUSE CANCER, BASED ON ANIMAL DATA.

Hazardous Material Information System (U.S.A.)

:

Health	1
Flammability	0
Physical hazards	0

Caution: HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings are not required on MSDSs under 29 CFR 1910.1200, the preparer may choose to provide them. HMIS® ratings are to be used with a fully implemented HMIS® program. HMIS® is a registered mark of the National Paint & Coatings Association (NPCA). HMIS® materials may be purchased exclusively from J. J. Keller (800) 327-6868.

The customer is responsible for determining the PPE code for this material.

National Fire Protection Association (U.S.A.)

:



Reprinted with permission from NFPA 704-2001, Identification of the Hazards of Materials for Emergency Response Copyright ©1997, National Fire Protection Association, Quincy, MA 02269. This reprinted material is not the complete and official position of the National Fire Protection Association, on the referenced subject which is represented only by the standard in its entirety.

Copyright ©2001, National Fire Protection Association, Quincy, MA 02269. This warning system is intended to be interpreted and applied only by properly trained individuals to identify fire, health and reactivity hazards of chemicals. The user is referred to certain limited number of chemicals with recommended classifications in NFPA 49 and NFPA 325, which would be used as a guideline only. Whether the chemicals are classified by NFPA or not, anyone using the 704 systems to classify chemicals does so at their own risk.

16. Other information

Date of printing : 8/5/2013.
Date of issue : 8/5/2013.
Date of previous issue : No previous validation.
Version : 1
Prepared by : Not available.

▣ Indicates information that has changed from previously issued version.

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.