

## Current Mode PWM Controller

### FEATURES

- Automatic Feed Forward Compensation
- Programmable Pulse-by-Pulse Current Limiting
- Automatic Symmetry Correction in Push-pull Configuration
- Enhanced Load Response Characteristics
- Parallel Operation Capability for Modular Power Systems
- Differential Current Sense Amplifier with Wide Common Mode Range
- Double Pulse Suppression
- 500mA (Peak) Totem-pole Outputs
- $\pm 1\%$  Bandgap Reference
- Under-voltage Lockout
- Soft Start Capability
- Shutdown Terminal
- 500kHz Operation

### DESCRIPTION


The UC1846/7 family of control ICs provides all of the necessary features to implement fixed frequency, current mode control schemes while maintaining a minimum external parts count. The superior performance of this technique can be measured in improved line regulation, enhanced load response characteristics, and a simpler, easier-to-design control loop. Topological advantages include inherent pulse-by-pulse current limiting capability, automatic symmetry correction for push-pull converters, and the ability to parallel "power modules" while maintaining equal current sharing.

Protection circuitry includes built-in under-voltage lockout and programmable current limit in addition to soft start capability. A shutdown function is also available which can initiate either a complete shutdown with automatic restart or latch the supply off.

Other features include fully latched operation, double pulse suppression, deadline adjust capability, and a  $\pm 1\%$  trimmed bandgap reference.

The UC1846 features low outputs in the OFF state, while the UC1847 features high outputs in the OFF state.

### BLOCK DIAGRAM



## ABSOLUTE MAXIMUM RATINGS (Note 1)


|                                               |                                                 |
|-----------------------------------------------|-------------------------------------------------|
| Supply Voltage (Pin 15)                       | +40V                                            |
| Collector Supply Voltage (Pin 13)             | +40V                                            |
| Output Current, Source or Sink (Pins 11, 14)  | 500mA                                           |
| Analog Inputs (Pins 3, 4, 5, 6, 16)           | -0.3V to $V_{IN}$                               |
| Reference Output Current (Pin 2)              | -30mA                                           |
| Sync Output Current (Pin 10)                  | -5mA                                            |
| Error Amplifier Output Current (Pin 7)        | -5mA                                            |
| Soft Start Sink Current (Pin 1)               | 50mA                                            |
| Oscillator Charging Current (Pin 9)           | 5mA                                             |
| Power Dissipation at $T_A=25^{\circ}\text{C}$ | 1000mW                                          |
| Power Dissipation at $T_c=25^{\circ}\text{C}$ | 2000mW                                          |
| Storage Temperature Range                     | $-65^{\circ}\text{C}$ to $+150^{\circ}\text{C}$ |
| Lead Temperature (soldering, 10 seconds)      | $+300^{\circ}\text{C}$                          |

Note 1. All voltages are with respect to Ground, Pin 13. Currents are positive into, negative out of the specified terminal. Consult Packaging Section of Databook for thermal limitations and considerations of packages. Pin numbers refer to DIL and SOIC packages only.

## CONNECTION DIAGRAMS


### DIL-16, SOIC-16 (TOP VIEW)

J or N Package, DW Package



### PLCC-20, LCC-20 (TOP VIEW)

Q, L Packages



| PACKAGE PIN FUNCTION |     |
|----------------------|-----|
| FUNCTION             | PIN |
| N/C                  | 1   |
| C/L SS               | 2   |
| $V_{REF}$            | 3   |
| C/S-                 | 4   |
| C/S+                 | 5   |
| N/C                  | 6   |
| E/A+                 | 7   |
| E/A-                 | 8   |
| Comp                 | 9   |
| $C_T$                | 10  |
| N/C                  | 11  |
| $R_T$                | 12  |
| Sync                 | 13  |
| A Out                | 14  |
| Gnd                  | 15  |
| N/C                  | 16  |
| $V_c$                | 17  |
| B Out                | 18  |
| $V_{IN}$             | 19  |
| Shutdown             | 20  |

**ELECTRICAL CHARACTERISTICS** (Unless otherwise stated, these specifications apply for  $T_A=-55^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$  for UC1846/7;  $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$  for the UC2846/7; and  $0^{\circ}\text{C}$  to  $+70^{\circ}\text{C}$  for the UC3846/7;  $V_{IN}=15\text{V}$ ,  $R_T=10\text{k}$ ,  $C_T=4.7\text{nF}$ ,  $T_A=T_J$ .)

| PARAMETER                    | TEST CONDITIONS                                 | UC1846/UC1847<br>UC2846/UC2847 |      |      | UC3846/UC3847 |      |      | UNITS |
|------------------------------|-------------------------------------------------|--------------------------------|------|------|---------------|------|------|-------|
|                              |                                                 | MIN.                           | TYP. | MAX. | MIN.          | TYP. | MAX. |       |
| Reference Section            |                                                 |                                |      |      |               |      |      |       |
| Output Voltage               | T <sub>J</sub> =25°C, I <sub>O</sub> =1mA       | 5.05                           | 5.10 | 5.15 | 5.00          | 5.10 | 5.20 | V     |
| Line Regulation              | V <sub>IN</sub> =8V to 40V                      |                                | 5    | 20   |               | 5    | 20   | mV    |
| Load Regulation              | I <sub>L</sub> =1mA to 10mA                     |                                | 3    | 15   |               | 3    | 15   | mV    |
| Temperature Stability        | Over Operating Range, (Note 2)                  |                                | 0.4  |      |               | 0.4  |      | mV/°C |
| Total Output Variation       | Line, Load, and Temperature (Note 2)            | 5.00                           |      | 5.20 | 4.95          |      | 5.25 | V     |
| Output Noise Voltage         | 10Hz ≤ f ≤ 10kHz, T <sub>J</sub> =25°C (Note 2) |                                | 100  |      |               | 100  |      | μV    |
| Long Term Stability          | T <sub>J</sub> =125°C, 1000 Hrs. (Note 2)       |                                | 5    |      |               | 5    |      | mV    |
| Short Circuit Output Current | V <sub>REF</sub> =0V                            | -10                            | -45  |      | -10           | -45  |      | mA    |

**ELECTRICAL CHARACTERISTICS (cont.)** (Unless otherwise stated, these specifications apply for  $T_A = -55^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$  for UC1846/7;  $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$  for the UC2846/7; and  $0^{\circ}\text{C}$  to  $+70^{\circ}\text{C}$  for the UC3846/7;  $V_{IN} = 15\text{V}$ ,  $R_T = 10\text{k}$ ,  $C_T = 4.7\text{nF}$ ,  $T_A = T_J$ .)

| PARAMETER                                                                   | TEST CONDITIONS                                                     | UC1846/UC1847<br>UC2846/UC2847 |      |                     | UC3846/UC3847 |      |                     | UNITS |
|-----------------------------------------------------------------------------|---------------------------------------------------------------------|--------------------------------|------|---------------------|---------------|------|---------------------|-------|
|                                                                             |                                                                     | MIN.                           | TYP. | MAX.                | MIN.          | TYP. | MAX.                |       |
| Oscillator Section                                                          |                                                                     |                                |      |                     |               |      |                     |       |
| Initial Accuracy                                                            | T <sub>J</sub> =25°C                                                | 39                             | 43   | 47                  | 39            | 43   | 47                  | kHz   |
| Voltage Stability                                                           | V <sub>IN</sub> =8V to 40V                                          |                                | -1   | 2                   |               | -1   | 2                   | %     |
| Temperature Stability                                                       | Over Operating Range (Note 2)                                       |                                | -1   |                     |               | -1   |                     | %     |
| Sync Output High Level                                                      |                                                                     | 3.9                            | 4.35 |                     | 3.9           | 4.35 |                     | V     |
| Sync Output Low Level                                                       |                                                                     |                                | 2.3  | 2.5                 |               | 2.3  | 2.5                 | V     |
| Sync Input High Level                                                       | Pin 8=0V                                                            | 3.9                            |      |                     | 3.9           |      |                     | V     |
| Sync Input Low Level                                                        | Pin 8=0V                                                            |                                |      | 2.5                 |               |      | 2.5                 | V     |
| Sync Input Current                                                          | Sync Voltage=3.9V, Pin 8=0V                                         |                                | 1.3  | 1.5                 |               | 1.3  | 1.5                 | mA    |
| Error Amp Section                                                           |                                                                     |                                |      |                     |               |      |                     |       |
| Input Offset Voltage                                                        |                                                                     |                                | 0.5  | 5                   |               | 0.5  | 10                  | mV    |
| Input Bias Current                                                          |                                                                     |                                | -0.6 | -1                  |               | -0.6 | -2                  | μA    |
| Input Offset Current                                                        |                                                                     |                                | 40   | 250                 |               | 40   | 250                 | nA    |
| Common Mode Range                                                           | V <sub>IN</sub> =8V to 40V                                          | 0                              |      | V <sub>IN</sub> -2V | 0             |      | V <sub>IN</sub> -2V | V     |
| Open Loop Voltage Gain                                                      | ΔV <sub>O</sub> =1.2 to 3V, V <sub>CM</sub> =2V                     | 80                             | 105  |                     | 80            | 105  |                     | dB    |
| Unity Gain Bandwidth                                                        | T <sub>J</sub> =25°C (Note 2)                                       | 0.7                            | 1.0  |                     | 0.7           | 1.0  |                     | MHz   |
| CMRR                                                                        | V <sub>CM</sub> =0V to 38V, V <sub>IN</sub> =40V                    | 75                             | 100  |                     | 75            | 100  |                     | dB    |
| PSRR                                                                        | V <sub>IN</sub> =8V to 40V                                          | 80                             | 105  |                     | 80            | 105  |                     | dB    |
| Output Sink Current                                                         | V <sub>ID</sub> =-15mV to -5V, V <sub>PIN 7</sub> =1.2V             | 2                              | 6    |                     | 2             | 6    |                     | mA    |
| Output Source Current                                                       | V <sub>ID</sub> =15mV to 5V, V <sub>PIN 7</sub> =2.5V               | -0.4                           | -0.5 |                     | -0.4          | -0.5 |                     | mA    |
| High Level Output Voltage                                                   | R <sub>L</sub> =(Pin 7) 15kΩ                                        | 4.3                            | 4.6  |                     | 4.3           | 4.6  |                     | V     |
| Low Level Output Voltage                                                    |                                                                     |                                | 0.7  | 1                   |               | 0.7  | 1                   | V     |
| Current Sense Amplifier Section                                             |                                                                     |                                |      |                     |               |      |                     |       |
| Amplifier Gain                                                              | V <sub>PIN 3</sub> =0V, Pin 1 Open (Notes 3 & 4)                    | 2.5                            | 2.75 | 3.0                 | 2.5           | 2.75 | 3.0                 | V     |
| Maximum Differential Input Signal (V <sub>PIN 4</sub> -V <sub>PIN 3</sub> ) | Pin 1 Open (Note 3)<br>R <sub>L</sub> (Pin 7)=15kW                  | 1.1                            | 1.2  |                     | 1.1           | 1.2  |                     | V     |
| Input Offset Voltage                                                        | V <sub>PIN 1</sub> =0.5V, Pin 7 Open (Note 3)                       |                                | 5    | 25                  |               | 5    | 25                  | mV    |
| CMRR                                                                        | V <sub>CM</sub> =1V to 12V                                          | 60                             | 83   |                     | 60            | 83   |                     | dB    |
| PSRR                                                                        | V <sub>IN</sub> =8V to 40V                                          | 60                             | 84   |                     | 60            | 84   |                     | dB    |
| Input Bias Current                                                          | V <sub>PIN 1</sub> =0.5V, Pin 7 Open (Note 3)                       |                                | -2.5 | -10                 |               | -2.5 | -10                 | μA    |
| Input Offset Current                                                        | V <sub>PIN 1</sub> =0.5V, Pin 7 Open (Note 3)                       |                                | 0.08 | 1                   |               | 0.08 | 1                   | μA    |
| Input Common Mode Range                                                     |                                                                     | 0                              |      | V <sub>IN</sub> -3  | 0             |      | V <sub>IN</sub> -3  | V     |
| Delay to Outputs                                                            | T <sub>J</sub> =25°C, (Note 2)                                      |                                | 200  | 500                 |               | 200  | 500                 | ns    |
| Current Limit Adjust Section                                                |                                                                     |                                |      |                     |               |      |                     |       |
| Current Limit Offset                                                        | V <sub>PIN 3</sub> =0V, V <sub>PIN 4</sub> =0V, Pin 7 Open (Note 3) | 0.45                           | 0.5  | 0.55                | 0.45          | 0.5  | 0.55                | V     |
| Input Bias Current                                                          | V <sub>PIN 5</sub> =V <sub>REF</sub> , V <sub>PIN 6</sub> =0V       |                                | -10  | -30                 |               | -10  | -30                 | μA    |
| Shutdown Terminal Section                                                   |                                                                     |                                |      |                     |               |      |                     |       |
| Threshold Voltage                                                           |                                                                     | 250                            | 350  | 400                 | 250           | 350  | 400                 | mV    |
| Input Voltage Range                                                         |                                                                     | 0                              |      | V <sub>IN</sub>     | 0             |      | V <sub>IN</sub>     | V     |
| Minimum Latching Current (I <sub>PIN 1</sub> )                              | (Note 6)                                                            | 3.0                            | 1.5  |                     | 3.0           | 1.5  |                     | mA    |



# **ELECTRICAL CHARACTERISTICS (cont.)**

(Unless otherwise stated, these specifications apply for  $T_A = -55^\circ\text{C}$  to  $+125^\circ\text{C}$  for UC1846/7;  $-40^\circ\text{C}$  to  $+85^\circ\text{C}$  for the UC2846/7; and  $0^\circ\text{C}$  to  $+70^\circ\text{C}$  for the UC3846/7;  $V_{IN} = 15\text{V}$ ,  $R_T = 10\text{k}$ ,  $C_T = 4.7\text{nF}$ ,  $T_A = T_J$ .)

| PARAMETER                             | TEST CONDITIONS          | UC1846/UC1847<br>UC2846/UC2847 |      |      | UC3846/UC3847 |      |      | UNITS |
|---------------------------------------|--------------------------|--------------------------------|------|------|---------------|------|------|-------|
|                                       |                          | MIN.                           | TYP. | MAX. | MIN.          | TYP. | MAX. |       |
| Shutdown Terminal Section (cont.)     |                          |                                |      |      |               |      |      |       |
| Maximum Non-Latching Current (IPIN 1) | (Note 7)                 |                                | 1.5  | 0.8  |               | 1.5  | 0.8  | mA    |
| Delay to Outputs                      | TJ=25°C (Note 2)         |                                | 300  | 600  |               | 300  | 600  | ns    |
| Output Section                        |                          |                                |      |      |               |      |      |       |
| Collector-Emitter Voltage             |                          | 40                             |      |      | 40            |      |      | V     |
| Collector Leakage Current             | VC=40V (Note 5)          |                                |      | 200  |               |      | 200  | µA    |
| Output Low Level                      | ISINK=20mA               |                                | 0.1  | 0.4  |               | 0.1  | 0.4  | V     |
|                                       | ISINK=100mA              |                                | 0.4  | 2.1  |               | 0.4  | 2.1  | V     |
| Output High Level                     | ISOURCE=20mA             | 13                             | 13.5 |      | 13            | 13.5 |      | V     |
|                                       | ISOURCE=100mA            | 12                             | 13.5 |      | 12            | 13.5 |      | V     |
| Rise Time                             | CL=1nF, TJ=25°C (Note 2) |                                | 50   | 300  |               | 50   | 300  | ns    |
| Fall Time                             | CL=1nF, TJ=25°C (Note 2) |                                | 50   | 300  |               | 50   | 300  | ns    |
| Under-Voltage Lockout Section         |                          |                                |      |      |               |      |      |       |
| Start-Up Threshold                    |                          |                                | 7.7  | 8.0  |               | 7.7  | 8.0  | V     |
| Threshold Hysteresis                  |                          |                                | 0.75 |      |               | 0.75 |      | V     |
| Total Standby Current                 |                          |                                |      |      |               |      |      |       |
| Supply Current                        |                          |                                | 17   | 21   |               | 17   | 21   | mA    |

Note 2. These parameters, although ensured over the recommended operating conditions, are not 100% tested in production.

Note 3. Parameter measured at trip point of latch with  $V_{PIN\ 5} = V_{REF}$ ,  $V_{PIN\ 6} = 0\text{V}$ .

Note 4. Amplifier gain defined as:  $G = \frac{\Delta V_{PIN7}}{\Delta V_{PIN4}}$ ;  $V_{PIN4} = 0$  to  $1.0\text{V}$


Note 5. Applies to UC1846/UC2846/UC3846 only due to polarity of outputs.

Note 6. Current into Pin 1 ensured to latch circuit in shutdown state.

Note 7. Current into Pin 1 ensured not to latch circuit in shutdown state.


## **APPLICATIONS DATA**

### **Oscillator Circuit**




## APPLICATIONS DATA (cont.)


Error Amp Output Configuration




Error Amp Gain and Phase vs Frequency



Error Amp Open-Logic D.C. Gain vs Load Resistance




Parallel Operation





# APPLICATIONS DATA (cont.)

## Pulse by Pulse Current Limiting



## Soft Start and Shutdown /Restart Functions




If  $\frac{V_{REF}}{R_1} < 0.8\text{mA}$ , the shutdown latch will commute when  $I_{SS} = 0.8\text{mA}$  and a restart cycle will be initiated.

If  $\frac{V_{REF}}{R_1} > 3\text{mA}$ , the device will latch off until power is recycled.


## APPLICATIONS DATA (cont.)

### Current Sense Amp Connection



A small RC filter may be required in some applications to reduce switch transients.  
Differential input allows remote, noise free sensing.

### UC1846 Open Loop Test Circuit



## REVISION HISTORY

SLUS352A to SLUS352B July 2010:

- 1) Updated block diagram, page 1.
- 2) Added peak and vally voltages to the Oscillator Circuit, page 4.



**PACKAGING INFORMATION**

| Orderable Device   | Status<br>(1) | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan<br>(2)            | Lead/Ball Finish<br>(6) | MSL Peak Temp<br>(3) | Op Temp (°C) | Device Marking<br>(4/5)            | Samples                 |
|--------------------|---------------|--------------|--------------------|------|----------------|----------------------------|-------------------------|----------------------|--------------|------------------------------------|-------------------------|
| 5962-86806012A     | ACTIVE        | LCCC         | FK                 | 20   | 1              | TBD                        | POST-PLATE              | N / A for Pkg Type   | -55 to 125   | 5962-86806012A<br>UC1846L/<br>883B | <a href="#">Samples</a> |
| 5962-8680601EA     | ACTIVE        | CDIP         | J                  | 16   | 1              | TBD                        | A42                     | N / A for Pkg Type   | -55 to 125   | 5962-8680601EA<br>UC1846J/883B     | <a href="#">Samples</a> |
| UC1846J            | ACTIVE        | CDIP         | J                  | 16   | 1              | TBD                        | A42                     | N / A for Pkg Type   | -55 to 125   | UC1846J                            | <a href="#">Samples</a> |
| UC1846J/80257      | OBSOLETE      | CDIP         | J                  | 16   |                | TBD                        | Call TI                 | Call TI              | -55 to 125   |                                    |                         |
| UC1846J/80364      | OBSOLETE      | CDIP         | J                  | 16   |                | TBD                        | Call TI                 | Call TI              | -55 to 125   |                                    |                         |
| UC1846J/80619      | OBSOLETE      | CDIP         | J                  | 16   |                | TBD                        | Call TI                 | Call TI              | -55 to 125   |                                    |                         |
| UC1846J883B        | ACTIVE        | CDIP         | J                  | 16   | 1              | TBD                        | A42                     | N / A for Pkg Type   | -55 to 125   | 5962-8680601EA<br>UC1846J/883B     | <a href="#">Samples</a> |
| UC1846L883B        | ACTIVE        | LCCC         | FK                 | 20   | 1              | TBD                        | POST-PLATE              | N / A for Pkg Type   | -55 to 125   | 5962-86806012A<br>UC1846L/<br>883B | <a href="#">Samples</a> |
| UC1847J            | OBSOLETE      | CDIP         | J                  | 16   |                | TBD                        | Call TI                 | Call TI              | -55 to 125   |                                    |                         |
| UC1847J883B        | OBSOLETE      | CDIP         | J                  | 16   |                | TBD                        | Call TI                 | Call TI              | -55 to 125   |                                    |                         |
| UC1847L            | OBSOLETE      | LCCC         | FK                 | 20   |                | TBD                        | Call TI                 | Call TI              | -55 to 125   |                                    |                         |
| UC1847L883B        | OBSOLETE      | LCCC         | FK                 | 20   |                | TBD                        | Call TI                 | Call TI              | -55 to 125   |                                    |                         |
| UC2846DW           | ACTIVE        | SOIC         | DW                 | 16   | 40             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-2-260C-1 YEAR  | -40 to 85    | UC2846DW                           | <a href="#">Samples</a> |
| UC2846DWG4         | ACTIVE        | SOIC         | DW                 | 16   | 40             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-2-260C-1 YEAR  | -40 to 85    | UC2846DW                           | <a href="#">Samples</a> |
| UC2846DWTR         | ACTIVE        | SOIC         | DW                 | 16   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-2-260C-1 YEAR  | -40 to 85    | UC2846DW                           | <a href="#">Samples</a> |
| UC2846DWTR/81265   | OBSOLETE      | SOIC         | DW                 | 16   |                | TBD                        | Call TI                 | Call TI              |              |                                    |                         |
| UC2846DWTR/81265G4 | OBSOLETE      | SOIC         | DW                 | 16   |                | TBD                        | Call TI                 | Call TI              |              |                                    |                         |
| UC2846DWTRG4       | ACTIVE        | SOIC         | DW                 | 16   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-2-260C-1 YEAR  | -40 to 85    | UC2846DW                           | <a href="#">Samples</a> |
| UC2846J            | ACTIVE        | CDIP         | J                  | 16   | 1              | TBD                        | A42                     | N / A for Pkg Type   | -40 to 85    | UC2846J                            | <a href="#">Samples</a> |

| Orderable Device | Status<br>(1) | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan<br>(2)            | Lead/Ball Finish<br>(6) | MSL Peak Temp<br>(3) | Op Temp (°C) | Device Marking<br>(4/5) | Samples                 |
|------------------|---------------|--------------|--------------------|------|----------------|----------------------------|-------------------------|----------------------|--------------|-------------------------|-------------------------|
| UC2846N          | ACTIVE        | PDIP         | N                  | 16   | 25             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | N / A for Pkg Type   | -40 to 85    | UC2846N                 | <a href="#">Samples</a> |
| UC2846NG4        | ACTIVE        | PDIP         | N                  | 16   | 25             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | N / A for Pkg Type   | -40 to 85    | UC2846N                 | <a href="#">Samples</a> |
| UC2846QTR        | ACTIVE        | PLCC         | FN                 | 20   | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | -40 to 85    | UC2846Q                 | <a href="#">Samples</a> |
| UC2846QTRG3      | ACTIVE        | PLCC         | FN                 | 20   |                | TBD                        | Call TI                 | Call TI              | -40 to 85    |                         | <a href="#">Samples</a> |
| UC2847DW         | ACTIVE        | SOIC         | DW                 | 16   | 40             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-2-260C-1 YEAR  | -40 to 85    | UC2847DW                | <a href="#">Samples</a> |
| UC2847DWG4       | ACTIVE        | SOIC         | DW                 | 16   | 40             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-2-260C-1 YEAR  | -40 to 85    | UC2847DW                | <a href="#">Samples</a> |
| UC2847N          | ACTIVE        | PDIP         | N                  | 16   | 25             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | N / A for Pkg Type   | -40 to 85    | UC2847N                 | <a href="#">Samples</a> |
| UC2847NG4        | ACTIVE        | PDIP         | N                  | 16   |                | TBD                        | Call TI                 | Call TI              | -40 to 85    |                         | <a href="#">Samples</a> |
| UC3846DW         | ACTIVE        | SOIC         | DW                 | 16   | 40             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-2-260C-1 YEAR  | 0 to 70      | UC3846DW                | <a href="#">Samples</a> |
| UC3846DWG4       | ACTIVE        | SOIC         | DW                 | 16   | 40             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-2-260C-1 YEAR  | 0 to 70      | UC3846DW                | <a href="#">Samples</a> |
| UC3846DWTR       | ACTIVE        | SOIC         | DW                 | 16   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-2-260C-1 YEAR  | 0 to 70      | UC3846DW                | <a href="#">Samples</a> |
| UC3846DWTRG4     | ACTIVE        | SOIC         | DW                 | 16   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-2-260C-1 YEAR  | 0 to 70      | UC3846DW                | <a href="#">Samples</a> |
| UC3846J          | ACTIVE        | CDIP         | J                  | 16   | 1              | TBD                        | A42                     | N / A for Pkg Type   | 0 to 70      | UC3846J                 | <a href="#">Samples</a> |
| UC3846N          | ACTIVE        | PDIP         | N                  | 16   | 25             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | N / A for Pkg Type   | 0 to 70      | UC3846N                 | <a href="#">Samples</a> |
| UC3846NG4        | ACTIVE        | PDIP         | N                  | 16   | 25             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | N / A for Pkg Type   | 0 to 70      | UC3846N                 | <a href="#">Samples</a> |
| UC3846Q          | ACTIVE        | PLCC         | FN                 | 20   | 46             | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 70      | UC3846Q                 | <a href="#">Samples</a> |
| UC3846QG3        | ACTIVE        | PLCC         | FN                 | 20   |                | TBD                        | Call TI                 | Call TI              | 0 to 70      |                         | <a href="#">Samples</a> |
| UC3846QTR        | ACTIVE        | PLCC         | FN                 | 20   | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 70      | UC3846Q                 | <a href="#">Samples</a> |
| UC3846QTRG3      | ACTIVE        | PLCC         | FN                 | 20   |                | TBD                        | Call TI                 | Call TI              | 0 to 70      |                         | <a href="#">Samples</a> |

| Orderable Device | Status<br>(1) | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan<br>(2)            | Lead/Ball Finish<br>(6) | MSL Peak Temp<br>(3) | Op Temp (°C) | Device Marking<br>(4/5) | Samples                 |
|------------------|---------------|--------------|--------------------|------|----------------|----------------------------|-------------------------|----------------------|--------------|-------------------------|-------------------------|
| UC3847DW         | ACTIVE        | SOIC         | DW                 | 16   | 40             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-2-260C-1 YEAR  | 0 to 70      | UC3847DW                | <a href="#">Samples</a> |
| UC3847DWG4       | ACTIVE        | SOIC         | DW                 | 16   |                | TBD                        | Call TI                 | Call TI              | 0 to 70      |                         | <a href="#">Samples</a> |
| UC3847J          | OBSOLETE      | CDIP         | J                  | 16   |                | TBD                        | Call TI                 | Call TI              | 0 to 70      |                         |                         |
| UC3847N          | ACTIVE        | PDIP         | N                  | 16   | 25             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | N / A for Pkg Type   | 0 to 70      | UC3847N                 | <a href="#">Samples</a> |
| UC3847NG4        | ACTIVE        | PDIP         | N                  | 16   |                | TBD                        | Call TI                 | Call TI              | 0 to 70      |                         | <a href="#">Samples</a> |

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

**Green (RoHS & no Sb/Br):** TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF UC1846, UC1847, UC2846, UC2846M, UC3846, UC3846M, UC3847 :**

- Catalog: [UC3846](#), [UC3847](#), [UC2846](#), [UC3846M](#), [UC3846](#)
- Enhanced Product: [UC1846-EP](#), [UC1846-EP](#)
- Military: [UC2846M](#), [UC1846](#), [UC1847](#)
- Space: [UC1846-SP](#), [UC1846-SP](#)

**NOTE: Qualified Version Definitions:**

- Catalog - TI's standard catalog product
- Enhanced Product - Supports Defense, Aerospace and Medical Applications
- Military - QML certified for Military and Defense Applications
- Space - Radiation tolerant, ceramic packaging and qualified for use in Space-based application


**TAPE AND REEL INFORMATION**


\*All dimensions are nominal

| Device     | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| UC2846DWTR | SOIC         | DW              | 16   | 2000 | 330.0              | 16.4               | 10.75   | 10.7    | 2.7     | 12.0    | 16.0   | Q1            |



## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device     | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|------------|--------------|-----------------|------|------|-------------|------------|-------------|
| UC2846DWTR | SOIC         | DW              | 16   | 2000 | 367.0       | 367.0      | 38.0        |

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

### Products

|                              |                                                                                      |
|------------------------------|--------------------------------------------------------------------------------------|
| Audio                        | <a href="http://www.ti.com/audio">www.ti.com/audio</a>                               |
| Amplifiers                   | <a href="http://amplifier.ti.com">amplifier.ti.com</a>                               |
| Data Converters              | <a href="http://dataconverter.ti.com">dataconverter.ti.com</a>                       |
| DLP® Products                | <a href="http://www.dlp.com">www.dlp.com</a>                                         |
| DSP                          | <a href="http://dsp.ti.com">dsp.ti.com</a>                                           |
| Clocks and Timers            | <a href="http://www.ti.com/clocks">www.ti.com/clocks</a>                             |
| Interface                    | <a href="http://interface.ti.com">interface.ti.com</a>                               |
| Logic                        | <a href="http://logic.ti.com">logic.ti.com</a>                                       |
| Power Mgmt                   | <a href="http://power.ti.com">power.ti.com</a>                                       |
| Microcontrollers             | <a href="http://microcontroller.ti.com">microcontroller.ti.com</a>                   |
| RFID                         | <a href="http://www.ti-rfid.com">www.ti-rfid.com</a>                                 |
| OMAP Applications Processors | <a href="http://www.ti.com/omap">www.ti.com/omap</a>                                 |
| Wireless Connectivity        | <a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a> |

### Applications

|                               |                                                                                          |
|-------------------------------|------------------------------------------------------------------------------------------|
| Automotive and Transportation | <a href="http://www.ti.com/automotive">www.ti.com/automotive</a>                         |
| Communications and Telecom    | <a href="http://www.ti.com/communications">www.ti.com/communications</a>                 |
| Computers and Peripherals     | <a href="http://www.ti.com/computers">www.ti.com/computers</a>                           |
| Consumer Electronics          | <a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>                   |
| Energy and Lighting           | <a href="http://www.ti.com/energy">www.ti.com/energy</a>                                 |
| Industrial                    | <a href="http://www.ti.com/industrial">www.ti.com/industrial</a>                         |
| Medical                       | <a href="http://www.ti.com/medical">www.ti.com/medical</a>                               |
| Security                      | <a href="http://www.ti.com/security">www.ti.com/security</a>                             |
| Space, Avionics and Defense   | <a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a> |
| Video and Imaging             | <a href="http://www.ti.com/video">www.ti.com/video</a>                                   |

### TI E2E Community

[e2e.ti.com](http://e2e.ti.com)