


TAPING DIMENSIONS



unit: mm

symbol	A_o	B_o	K_o	P_o	P_1	P_2	T
Spec	7.30 ± 0.10	12.50 ± 0.10	9.45 ± 0.10	4.0 ± 0.10	16.0 ± 0.10	2.0 ± 0.10	0.50 ± 0.10
symbol	E	F	D_o	D_1	W	$10P_o$	K_o
Spec	1.75 ± 0.10	11.5 ± 0.10	1.55 ± 0.05		24.0 ± 0.30	40.0 ± 0.20	7.15 ± 0.10



LITE-ON TECHNOLOGY CORPORATION

Property of Lite-On Only

ABSOLUTE MAXIMUM RATINGS AT TA=25°C

PARAMETER	MAXIMUM RATING	UNIT
Diode Power Dissipation	100	mW
Phototransistor Collector-Emitter Voltage	30	V
Phototransistor Emitter - Collector Voltage	5	V
Operating Temperature Range	-40°C to + 100°C	
Storage Temperature Range	-40°C to + 100°C	
Lead Soldering Temperature [1.6mm(.063") From Body]	260°C for 5 Seconds	

ELECTRICAL OPTICAL CHARACTERISTICS AT TA=25°C

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
INPUT LED						
Forward Voltage	VF		1.2	1.6	V	IF = 20mA
Reverse Current	IR			100	μ A	VR=5V
OUTPUT PHOTOTRANSISTOR						
Collector-Emitter Breakdown Voltage	V(BR)CEO	30			V	IC=1mA
Emitter-Collector Breakdown Voltage	V(BR)ECO	5			V	IE=0.1mA
Collector-Emitter Dark Current	ICEO		0.1	100	nA	VCE=10V
COUPLER						
Collector-Emitter Saturation Voltage	VCE(SAT)			0.4	V	IC=0.5mA IF=20mA
On State Collector Current	CTR	5		15	%	VCE=5V IF=7 mA

TYPICAL ELECTRICAL / OPTICAL CHARACTERISTICS CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




FIG.1 SPECTRAL DISTRIBUTION




FIG.2 FORWARD CURRENT VS. AMBIENT TEMPERATURE




FIG.3 FORWARD CURRENT VS. FORWARD VOLTAGE




FIG.4 RELATIVE RADIANT INTENSITY VS. AMBIENT TEMPERATURE




FIG.5 RELATIVE RADIANT INTENSITY VS. FORWARD CURRENT




FIG.6 RADIATION DIAGRAM

TYPICAL ELECTRICAL / OPTICAL CHARACTERISTICS CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




FIG.1 COLLECTOR DARK CURRENT VS AMBIENT TEMPERATURE




FIG.2 COLLECTOR POWER DISSIPATION VS AMBIENT TEMPERATURE




FIG.3 RISE AND FALL TIME VS LOAD RESISTANCE




FIG.4 RELATIVE COLLECTOR CURRENT VS IRRADIANCE