



MODULAR CONNECTORS

CL 222 TM


Right Angle Dip Type

●TM5RC-**(50)

CL No.	Part No.	RoHS
222-0270-9-50	TM5RC-44 (50)	YES
222-0338-0-50	TM5RC-64 (50)	
222-0337-8-50	TM5RC-66 (50)	



PCB mounting hole layout
(Connector mounting side)





Note 1: Standard finish color is gray.


Note 2: The drawing is shown sample of TM5RC-66(50).

●TM5RC-88(50)

CL No.	Part No.	RoHS
222-0339-3-50	TM5RC-88 (50)	YES



PCB mounting hole layout
(Connector mounting side)




Note : Standard finish color is warm gray.

MODULAR CONNECTORS

CL 222 TM

●TM5RE1- ** (20)

CL No.	Part No.	A	B	C	RoHS
222-0538-0-20	TM5RE1-44 (20)	13	10.4	8	YES
222-0539-2-20	TM5RE1-62 (20)	15	12.4	10	
222-0540-1-20	TM5RE1-64 (20)	15	12.4	10	
222-0541-4-20	TM5RE1-66 (20)	15	12.4	10	




Note 1: Standard finish color is dark gray.

Note 2: The drawing is shown sample of TM5RE1-66 (20).

●TM5RE2- ** (20)

CL No.	Part No.	A	B	C	RoHS
222-1222-1-20	TM5RE2-44 (20)	13	10.4	10.8	YES
222-1224-7-20	TM5RE2-62 (20)	15	12.4	12.8	
222-1223-4-20	TM5RE2-64 (20)	15	12.4	12.8	
222-1225-0-20	TM5RE2-66 (20)	15	12.4	12.8	



Note 1: Standard finish color is dark gray.


Note 3: The drawing is shown sample of TM5RE2-66 (20).

MODULAR CONNECTORS


CL 222 TM

●TM5RE3-*(20)


CL No.	Part No.	A	B	C	RoHS
222-1406-4-20	TM5RE3-44 (20)	13	10.4	10.8	YES
222-1407-7-20	TM5RE3-62 (20)	15	12.4	12.8	
222-1427-4-20	TM5RE3-64 (20)	15	12.4	12.8	
222-1428-7-20	TM5RE3-66 (20)	15	12.4	12.8	
222-1702-7-20	TM5RE3-88 (20)	18.6	16	16.4	




TM5RE3-66 (20)



TM5RE3-88 (20)





PCB mounting hole layout
(Connector mounting side)



Note 1: Standard finish color is dark gray.

Note 2: The drawing is shown sample of TM5RE3-88 (20).


●TM5RF-44 (50)



CL No.	Part No.	RoHS
222-0391-3-50	TM5RF-44 (50)	YES

PCB mounting hole layout
(Connector mounting side)



C.L. : Center Line




Note 1: Standard finish color is gray.

Note 2: Backboard size is shown the connector mounting side of PCB.



CL 222 TM




CL No.	Part No.	RoHS
222-1452-1-50	TM5RF-64 (50)	YES
222-1411-4-50	TM5RF-66 (50)	





Note 2: The drawing is shown sample of TM5RF-66(50).




CL No.	Part No.	RoHS
222-1242-9-50	TM5RF1-44 (50)	YES



Note 1: Standard finish color is dark gray.



CL No.	Part No.	RoHS
222-1533-1-50	TM5RF1-64 (50)	YES
222-1534-4-50	TM5RF1-66 (50)	




Note 2: The drawing is shown sample of TM5RF1-66(50).


MODULAR CONNECTORS

CL 222 TM

●TM5RJ2- *(50)




TM5RJ2-66(50)




TM5RJ2-88(50)


CL No.	Part No.	A	B	C	RoHS
222-1459-0-50	TM5RJ2-44 (50)	12.8	10.2	10	YES
222-1486-3-50	TM5RJ2-62 (50)	14.8	12.2	12	
222-1460-0-50	TM5RJ2-64 (50)	14.8	12.2	12	
222-1461-2-50	TM5RJ2-66 (50)	14.8	12.2	12	
222-1462-5-50	TM5RJ2-88 (50)	18.6	16	15	



PCB mounting hole layout
(Connector mounting side)



TM5RJ2-44,6*




TM5RJ2-88(50)


Note 1: Standard finish color is gray.

Note 2: The drawing is shown sample of TM5RJ2-88(50).

●TM5RJ3- *(50)




TM5RJ3-66(50)




TM5RJ3-88(50)


CL No.	Part No.	A	B	C	RoHS
222-1363-3-50	TM5RJ3-44 (50)	12.8	10.2	10.76	YES
222-1487-6-50	TM5RJ3-62 (50)	14.8	12.2	12.8	
222-1463-8-50	TM5RJ3-64 (50)	14.8	12.2	12.8	
222-1464-0-50	TM5RJ3-66 (50)	14.8	12.2	12.8	
222-1465-3-50	TM5RJ3-88 (50)	18.6	16	16.6	



PCB mounting hole layout
(Connector mounting side)



TM5RJ3-44, 6*



TM5RJ3-88(50)

Note 1: Standard finish color is gray.



Note 2: The drawing is shown sample of TM5RJ3-88(50).

MODULAR CONNECTORS


CL 222 TM

●TM5RU-6 *(50)

CL No.	Part No.	RoHS
222-2639-8-50	TM5RU-62 (50)	YES
222-2638-5-50	TM5RU-64 (50)	
222-2630-3-50	TM5RU-66 (50)	



PCB mounting hole layout
(Connector mounting side)



Note 1: Standard finish color is black.

Note 2: The drawing is shown sample of TM5RU-66(50).





MODULAR CONNECTORS

CL 222 TM


Gang-Jacks Right Angle Dip Type

●TM2REA-06 ** (50)


CL No.	Part No.	RoHS
222-1277-3-50	TM2REA-0602 (50)	YES
222-1466-6-50	TM2REA-0604 (50)	
222-1467-9-50	TM2REA-0606 (50)	




PCB mounting hole layout
(Connector mounting side)



TM2REA-0602 (50)



TM2REA-0604 (50)







TM2REA-0606 (50)

Note 1: Standard finish color is gray.


Note 2: The drawing is shown sample of TM2REA-0602 (50).

●TM2REA-12 ** (50)


CL No.	Part No.	RoHS
222-0802-6-50	TM2REA-1204 (50)	YES
222-0799-3-50	TM2REA-1208 (50)	
222-0681-3-50	TM2REA-1212 (50)	




PCB mounting hole layout
(Connector mounting side)



TM2REA-1204 (50)



TM2REA-1208 (50)



TM2REA-1212 (50)

Note 1: Standard finish color is gray.

Note 2: The drawing is shown sample of TM2REA-1204 (50).




All non-RoHS products have been discontinued, or will be discontinued soon. Please check the products status on the Hirose website RoHS search at www.hirose-connectors.com, or contact your Hirose sales representative.

CL 222 TM


CL No.	Part No.	RoHS
222-0801-3-50	TM2REA-1806 (50)	YES
222-0798-0-50	TM2REA-1812 (50)	
222-0737-6-50	TM2REA-1818 (50)	

Technical drawing of a shaft with dimensions and labels. The shaft has a total length of 36. It features a central section with two 11-unit segments and a 6-unit segment in the middle. The shaft has a diameter of 2.8 at the left end and 2.54 at the right end. There are two keyways, each 11 units wide and 0.5 units deep. The shaft is supported by bearings, with a 6-unit distance from the left end to the first bearing and a 6-unit distance from the last bearing to the right end. The shaft has a fillet radius of R0.35 at the left end and a fillet radius of R0.8 at the right end. The shaft is labeled with '3' and '4' near the keyways.

TM2REA-1806(50)



TM2REA-1812(50)






TM2REA-1818(50)


Note 2: The drawing is shown sample of TM2REA-1806 (50) .

CL No.	Part No.	RoHS
222-0800-0-50	TM2REA-2408 (50)	YES
222-0749-5-50	TM2REA-2416 (50)	
222-0750-4-50	TM2REA-2424 (50)	

TM2REA-2408(50)



TM2REA-2416(50)





TM2REA-2424(50)

Note 2: The drawing is shown sample of TM2REA-2416 (50).

MODULAR CONNECTORS


CL 222 TM

●TM5RQ-1414 (50)





CL No.	Part No.	RoHS
222-1504-3-50	TM5RQ-1414 (50)	YES

PCB mounting hole layout
(Connector mounting side)




Note : Standard finish color is gray.

●TM5RQ-2020 (50)





CL No.	Part No.	RoHS
222-1645-5-50	TM5RQ-2020 (50)	YES

PCB mounting hole layout
(Connector mounting side)




Note : Standard finish color is gray.

●TM5RSA-2424 (50)



CL No.	Part No.	RoHS
222-3264-2-50	TM5RSA-2424 (50)	YES

PCB mounting hole layout (Connector mounting side)







Note : Standard finish color is gray.


MODULAR CONNECTORS

CL 222 TM

●TM5RSB-1616 (50)







PCB mounting hole layout
(Connector mounting side)




CL No.	Part No.	RoHS
222-3712-1-50	TM5RSB-1616 (50)	YES

Note : Standard finish color is gray.

●TM5RSB-2424 (50)



PCB mounting hole layout
(Connector mounting side)



CL No.	Part No.	RoHS
222-3423-4-50	TM5RSB-2424 (50)	YES

Note : Standard finish color is gray.

EIGHT-CONDUCTOR LOW PROFILE JACKS

●GENERAL

The TM5RL Series are small 8-contact modular connectors designed to be 11.7 mm in height and 23% smaller in volume than our former models to meet the demand for smaller and thinner electronic equipment.

●FEATURES

- (1) 11.7 mm in height above PCB surface (shielded jacks: 11.9 mm)
- (2) 23% smaller in volume than our former models
- (3) Space-saving: 14 mm (14.6 mm) in width and 17 mm (7.6 mm) in depth. (): shielded jacks
- (4) EMI-protected ferrite and shielded jacks available.
- (5) Ferrite and shielded jacks use the same connector body as standard jacks, requiring no change in the PCB for redesigning.
(When you plan to redesign a standard PCB to a shielded PCB, select the shielding pattern in advance).
- (6) A quadruple jack is equal to or smaller in size than four TM5RL-88 jacks combined.
- (7) Plugs and jack connectors comply with the ISO 8877 Standard (ISDN interface connector).



●APPLICATIONS

LAN boards, HUB, ISDN terminals, and personal computers.


●RIGHT-ANGLE DIP TYPE

●TM5RL *-88(50)


CL No.	Part No.	Type	RoHS
222-2665-8-50	TM5RL-88 (50)	Standard	YES
222-2666-0-50	TM5RL-88 (50)	With ferrite core	



View of mating plug
A-A



Reference mounting dimensions
(PCB component side)



Note : When preparing frames or PCBs, follow the above $\square$ dimensions.




MODULAR CONNECTORS

CL 222 TM


Quadruplet right-angle dip

●TM5RL *-3232(50)

CL No.	Part No.	Type	RoHS
222-2671-0-50	TM5RL-3232 (50)	Standard	YES
222-2711-3-50	TM5RLF-3232 (50)	With ferrite core	





Mounting dimensions for reference (PCB mounting side)



Note : When preparing frames or PCBs, provide the above  for the connector.

Eight-conductor extension adapter

●TM5RL *-88-JJ(50)



CL No.	Part No.	Type	RoHS
222-3798-7-50	TM5RL-88-JJ (50)	Standard	YES
222-3805-0-50	TM5RLF-88-JJ (50)	With ferrite core	

Terminal numbers

Connector(a) terminal No. TM5RL-88	1	2	3	4	5	6	7	8
Connector(b) terminal No. TM5RL-88	1	2	3	4	5	6	7	8