


13	12	11	10	9	8	7	6	5	4	3	2	1
CIRCUIT SIZE	HOUSING STYLE	ASSEMBLY PART NUMBER	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"	DIM. "E"					
2	FLANGES	30069-0211	_____	<u>.213</u> (5.40)	<u>.354</u> (9.00)	<u>.606</u> (15.40)	<u>.370</u> (9.40)					
	PEGS	30069-0231										
4	FLANGES	30069-0411	<u>.165</u> (4.20)	<u>.378</u> (9.60)	<u>.520</u> (13.20)	<u>.772</u> (19.60)	<u>.535</u> (13.60)					
	PEGS	30069-0431										
6	FLANGES	30069-0611	<u>.331</u> (8.40)	<u>.543</u> (13.80)	<u>.685</u> (17.40)	<u>.937</u> (23.80)	<u>.701</u> (17.80)					
	PEGS	30069-0631										
8	FLANGES	30069-0811	<u>.496</u> (12.60)	<u>.709</u> (18.00)	<u>.850</u> (21.60)	<u>1.102</u> (28.00)	<u>.866</u> (22.00)					
	PEGS	30069-0831										
10	FLANGES	30069-1011	<u>.661</u> (16.80)	<u>.874</u> (22.20)	<u>1.016</u> (25.80)	<u>1.268</u> (32.20)	<u>1.031</u> (26.20)					
	PEGS	30069-1031										
12	FLANGES	30069-1211	<u>.827</u> (21.00)	<u>1.039</u> (26.40)	<u>1.181</u> (30.00)	<u>1.433</u> (36.40)	<u>1.197</u> (30.40)					
	PEGS	30069-1231										
16	FLANGES	30069-1611	<u>1.157</u> (29.40)	<u>1.370</u> (34.80)	<u>1.512</u> (38.40)	<u>1.764</u> (44.80)	<u>1.527</u> (38.80)					
	PEGS	30069-1631										

FINISHED PART LEGEND



SEE SHEET 1 EC NO: UCP2014-0298 DRAWN: NGUYEN CHKD: J.BELL APPR: F.S.MITH	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
				mm	INCH	DRAWN BY TGREGORI	DATE 2005/12/27	TITLE MINI-FIT T.P.A. VERTICAL HEADER ASSY (100U" TIN OVER 50U" NI)		
			4 PLACES	± ---	± ---	CHECKED BY JCOMERC I				
			3 PLACES	± ---	± .010					
			2 PLACES	± 0.25	± .014	APPROVED BY JCOMERC I		DATE 2010/07/27		
			1 PLACE	± 0.36	± ---					
			0 PLACE	±	±	MATERIAL NO.		DOCUMENT NO. SD-30069-001	SHEET NO. 2 OF 2	
			ANGULAR ±1/2°							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		