







THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating	16A 125V AC 1/3 HP	
	10A 250V AC 1/2 HP	
	16A 12VDC 6A 28VDC	
	16(4)A 125/250V AC	
	20A 12V DC	
Contact Resistance	50m ohm Max.	
Insulation Resistance	DC 500V 100M ohm Min.	
Dielectric Strength	AC 1500V 1 minute	
Operation Temp.	- 25°C ~ 85°C	
Switch Function	2P SPST ON-OFF	

Mounting Hole			Circuit Diagram	
			OFF	
			ON	
	Thickness	X	Y	
	0.75...1.5	19.4-0.1	13+0.1	
	1.5...2.5	19.8-0.1	13+0.1	



Material:
 Frame: Black, Nylon 66(94-V2)
 Actuator: Black, PC(94-V2)
 Waterproof Rubber: Black, Silicone
 Terminals: Silver plated, Copper alloy
 Hot stamping: None
 Waterproof: IP65



Tolerances ±0.3 Unless Otherwise Specified

RoHS Compliant

3 Updated ratings and views. 2-21-13.

CW INDUSTRIES
 Southampton, Pa. 18966
 Tel 215.355.7080/www.cwind.com

Date Drawn: 10/02/09

Rev. 3

Unit: mm

Checked By: *G. Gold*

Title: **ROCKER SWITCH**

CW P/N: **GRB066A802BB1**