





FOR 60 Circuits



FOR 64 Circuits




2.540
.100

A = 2.54 * No. of Spaces

B = A + 10.16

C = A + 7.86

* Available circuits: 06, 08, 10, 14, 16, 20, 24, 26, 30, 34, 40, 44, 50, 60, 64



Recommended P.C. Board Layout

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

SIGN	DATE	DESCRIPTION	APPROVER
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	

Material

- Insulator: Glass Filled Polyester
- Flammability: UL94V-0
- Color: Black
- Contacts: Brass
- Plating termination: 1.2u" Au min, 50u" Ni

Ratings

- Current: 3A
- Voltage: 250V AC(r.m.s.)
- Contact Resistance: <20mΩ
- Insulation Resistance: >1,000MΩ
- Dielectric Withstanding Voltage: 1500V AC for one minute
- Operating Temperature: -40°C ±105°C
- Solderability: 245°C ± 5°C for 3±0.5 seconds

RoHS Compliant

PLATING

1= Full Gold Flash/50u" Nickel (STD)
5 = 120u" Tin/50u" Nickel
7 = Selective 15u" Gold/50u" Nickel
8 = Selective 30u" Gold/50u" Nickel
NON-STD may require MOQ

PART NUMBER:

302-SXXX

Number of circuits

Dim. D

3.10 - leave blank (standard)

2.80 - add 2.8 to end of p/n
may require MOQ



TITLE	302 Series - Dual Row Vertical Box Header						
PART NO.	302-SXXX			DWG NO.	302-SXXX.DWG		
APPROVED	CHECKED	DESIGNED	DRAWN		4050		Tolerance
	Marvin 2003.06.16	Marvin 2003.06.16	Marvin 2003.06.16		UNIT: mm/inches	X.	±0.30/.012
					SCALE: NONE	X.X	±0.20/.008
					SHEET: 01/01	REV: B	X.XX
						X°	±1°