



SMAJ530 THRU SMAJ550

Surface Mount TransZorbTM Transient Voltage Suppressors



Voltage Range
530 to 550 Volts
300 Watts Peak Power



Features

- ◊ Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- ◊ Protects power IC controllers such as TOPSwitch®
- ◊ Excellent clamping capability
- ◊ Glass passivated junction
- ◊ High temperature soldering guaranteed: 260°C / 10 seconds at terminals
- ◊ Available in unidirectional only

Mechanical Data

- ◊ Case: JEDEC DO-201AC molded plastic body over passivated junction
- ◊ Terminals: Solder plated, solderable per MIL-STD-750, Method 2026
- ◊ Polarity: The band denotes the cathode, which is positive with respect to the anode under normal TVS operation
- ◊ Mounting position: Any
- ◊ Weight: 0.002 ounce, 0.064 gram

SMA/DO-214AC



Dimensions in inches and (millimeters)

Maximum Ratings and Thermal Characteristics TA= 25°C Unless Otherwise Noted.

Type Number	Symbol	SMAJ530	SMAJ550	Units
Device Marking Code		HD	SB	
Peak Pulse Power Dissipation (Note 1, 2 Fig. 1)	P _{PPM}	Minimum 300		Watts
Steady State Power Dissipation at T _L =75°C	P _{M(AV)}	1.0		Watts
Stand-off Voltage	V _{WM}	477	495	V
Typical Thermal resistance Junction-to-lead	R _{θ JL}	27		°C/W
Typical Thermal Resistance Junction-to-ambient	R _{θ JA}	75		°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to + 150		°C

Electrical Characteristics

Type Number	Symbol	SMAJ530	SMAJ550	Units
Minimum Breakdown Voltage at 100uA	V _(BR)	530	550	V
Max. Clamping Voltage at 400mA, 10/1000uS-Waveform	V _C	760		V
Maximum DC Reverse Leakage Current at V _{WM}	I _D	5.0		uA
Typical Temperature Coefficient of V _{BR}		650		mV/°C
Typical Capacitance (Note 3) at 0V 200V	C _J	90	7.5	pF

Notes: 1. Non Repetitive Current Pulse per Fig. 3 and Derated above 25°C per Fig. 2.
 2. Peak Pulse Power Waveform is 10 / 1000uS.
 3. Measured at 1MHz.

RATINGS AND CHARACTERISTIC CURVES (SMAJ530 THRU SMAJ550)

FIG.1- PEAK PULSE POWER RATING CURVE




FIG.2- PULSE DERATING CURVE




FIG.3- PULSE WAVEFORM

