

Hall Effect Current Sensors S22P Series



Features:

- Closed Loop type
- Voltage output
- Unipolar power supply
- Configurable integrated primary
- Printed circuit board mounting
- UL recognised - plastic case material UL94V0
- UL Recognition

Advantages:

- Excellent accuracy and linearity
- Low temperature drift
- Wide frequency bandwidth
- No insertion loss
- High Immunity to external interferences
- Optimised response time
- Current overload capability



$T_A=25^\circ\text{C}$, $V_{CC}=+5\text{V}$, $R_L=10\text{k}\Omega$

Specifications

Parameters	Symbol	S22P006S05	S22P015S05	S22P025S05
Primary nominal current	I_f	6A	15A	25A
Saturation current	I_{fmax}	$\geq \pm 18\text{A}$	$\geq \pm 45\text{A}$	$\geq \pm 75\text{A}$
Rated output voltage	V_o	$V_{of}\pm 0.625\text{V}$ (at I_f)		
Offset voltage ¹ (at $I_f=0\text{A}$)	V_{of}	$2.5\text{V}\pm 0.050\text{V}$	$2.5\text{V}\pm 0.020\text{V}$	$2.5\text{V}\pm 0.015\text{V}$
Output voltage accuracy(at I_f)	X	$0.625\text{V}\pm 0.010\text{V}$ (at I_f)		
Output linearity ² (0A~ I_f)	ϵ_L	$\leq \pm 0.2\%$ (at I_f)		
Power supply voltage	V_{CC}	$+5\text{V}\pm 5\%$		
Consumption current ³	I_{CC}	Typ. 12.5mA (at $I_f=0\text{A}$) + 37.5mA / 22.5mA / 9mA (at $I_f = 75\text{A} / 45\text{A} / 18\text{A}$)		
Response time ⁴	t_r	$\leq 1.0\mu\text{s}$ (at $dI/dt = 100\text{A}/\mu\text{s}$)		
Thermal drift of gain ⁵	T_{CVo}	$\leq \pm 0.05\text{mV}/^\circ\text{C}$		
Thermal drift of offset	T_{CVof}	$-10^\circ\text{C}\sim 25^\circ\text{C} : \leq \pm 1.6\text{mV}/^\circ\text{C}$ $25^\circ\text{C}\sim 85^\circ\text{C} : \leq \pm 0.8\text{mV}/^\circ\text{C}$	$-10^\circ\text{C}\sim 25^\circ\text{C} : \leq \pm 0.6\text{mV}/^\circ\text{C}$ $25^\circ\text{C}\sim 85^\circ\text{C} : \leq \pm 0.3\text{mV}/^\circ\text{C}$	$-10^\circ\text{C}\sim 25^\circ\text{C} : \leq \pm 0.4\text{mV}/^\circ\text{C}$ $25^\circ\text{C}\sim 85^\circ\text{C} : \leq \pm 0.2\text{mV}/^\circ\text{C}$
Hysteresis error	V_{OH}	$\leq 0.5\text{mV}$ (at $I_f=0\text{A}\rightarrow I_f\rightarrow 0\text{A}$)		
Insulation voltage	V_d	AC 3kV for 1minute (Sensing current 0.5mA) Primary \Leftrightarrow Secondary		
Insulation resistance	R_{IS}	$\geq 500\text{M}\Omega$ (at DC500V) , primary \Leftrightarrow secondary		
Ambient operation temperature	T_A	$-10^\circ\text{C}\sim +85^\circ\text{C}$		
Ambient storage temperature	T_s	$-25^\circ\text{C}\sim +100^\circ\text{C}$		

¹ After removal of core hysteresis — ² Without offset — ³ Conversion ratio 1:2000 — ⁴ Time between 90% input current full scale and 90% of sensor output full scale — ⁵ Without Thermal drift of offset


Electrical Performances




Tamura reserve the right to modify its products in order to improve them without prior notice

Hall Effect Current Sensors S22P Series

Mechanical dimensions



Electrical connection diagram



UL Standard

UL 508, CSA C22.2 No.14
(UL FILE No.E243511)

- For use in Pollution Degree 2 Environment.
- Maximum Surrounding air temperature rating, 85°C.

Package & Weight Information

Weight	Pcs/box	Pcs/carton	Pcs/pallet
8g	100	400	12000



Tamura reserve the right to modify its products in order to improve them without prior notice