

NOTES:

① MAT'L: COPPER (STOCK TKN $\frac{.040}{1.02}$)

PLATING: WATTS BATH NICKLE (.0002 MIN)

② BRAZED SEAM

③ 650°F MAX. OPERATING TEMP.

STUD SIZES: ($\pm .005$)

02 = .094 209 = .209

04 = .119 413 = .413

06 = .146

08 = .173

10 = .198


14 = .265

56 = .328

38 = .390

FILE NO.

C-T-CD-301-01



ALL DIMENSIONS = $\frac{\text{INCHES}}{\text{MM}}$

WIRE SIZE: 12-10 AWG
40-6.0 MM²

PART NUMBER	"W"	"C"	"L"	AVAILABLE STUD SIZES	
C-T-301-	$\frac{.750}{19.05}$	$\frac{.611}{15.52}$	$\frac{1.280}{32.51}$	14, 56, 38, 76, 12	
C-T-328-	$\frac{.375}{9.53}$	$\frac{.303}{7.70}$	$\frac{.785}{19.94}$	04, 06, 08, 10, 209	
C-T-330-	$\frac{.530}{13.46}$	$\frac{.393}{9.98}$	$\frac{.952}{24.18}$	10, 14, 56, 38	
C-T-336-	$\frac{.282}{7.16}$	$\frac{.306}{7.77}$	$\frac{.741}{18.82}$	04, 06, 08	
C-T-340-	$\frac{.592}{15.04}$	$\frac{.468}{11.89}$	$\frac{1.056}{26.82}$	10, 14, 56, 38, 209, 413	
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED		REFERENCE	SCALE: NTS	DATE	TITLE:
FRAC.	DEC.	ANG.	DRWN. BY: JJ	11-28-84	RING TONGUE TEMP-TERM.
±	±	±	CHKD. BY: GZ	11-30-84	650°F MAX.
			APPRD. BY:		VERSAKRIMP
					DWG. NO. A CUSTOMER DWG.

ETC mox INCORPORATED