




	13	12	11	10	9	8	7	6		2145	4	3	2	1		
J	ENG. NO.		HOUSING NO.		TERMINAL NO.		DIM. C		EDP ON SHT/COL							J
	A-2145-AANA(I02)-*		2145-N-AN		2144-AA-A IAA-I02B		(3.68) / .145		7 / 1							
	A-2145-AANA(I22)-*		2145-N-AN		2144-AA-A IAA-I22B		(3.68) / .145		7 / 2							
	A-2145-AANA(505)-*		2145-N-AN		2144-AA-A IAA-505B		(3.68) / .145		7 / 3							
	A-2145-AANA(507)-*		2145-N-AN		2144-AA-A IAA-507B		(3.68) / .145		7 / 4							
I	A-2145-AANB(558)-*		2145-N-AN		2144-BA-A IAA-558B		(3.68) / .145		8 / 1							I
	A-2145-AANA(P913)-*		2145-N-AN		2144-AA-A IAA-P913B		(3.68) / .145		8 / 2							
	A-2145-ABNA(I22)-*		2145-NBK-AN		2144-AA-A IAA-I22B		(3.68) / .145		8 / 3							
	A-2145-ABNA(P913)-*		2145-NBK-AN		2144-AA-A IAA-P913B		(3.68) / .145		8 / 4							
	A-2145-AANA(587)-*		2145-N-AN		2144-AA-A IAA-587B		(3.68) / .145		9 / 1							
	A-2145-AGNA(P913)-*		2145-N-CN		2144-AA-A IAA-587B		(3.68) / .145		9 / 2							
H	A-2145-BANH(I02)-*		2145-N-AN		2188-(I02)		(4.06) / .160		9 / 3							H
	A-2145-BANH(I22)-*		2145-N-AN		2188-(I22)		(4.06) / .160		9 / 4							
	A-2145-BANL(P913)-*		2145-N-AN		6298-(P913)		(4.06) / .160		10 / 1							
	A-2145-BANL(565)-*		2145-N-AN		6298-(565)		(4.06) / .160		10 / 2							
	A-2145-BBNH(I22)-*		2145-NBK-AN		2188-(I22)		(4.06) / .160		10 / 3							
G	A-2145-CANA(I02)-*		2145-N-AN		2144-AA-A IAA-I02B		(3.05) / .120		10 / 4							G
	A-2145-CANA(I22)-*		2145-N-AN		2144-AA-A IAA-I22B		(3.05) / .120		11 / 1							
	A-2145-CANB(565)-*		2145-N-AN		2144-BA-A IAA-565B		(3.05) / .120		11 / 2							
	A-2145-CANC(P913)-*		2145-N-AN		2144-AA-A2AA-P913B		(4.80) / .189		11 / 3							
	A-2145-FGNA(587)-*		2145-N-CN		2144-AA-A IAA-587B		(3.05) / .120		11 / 4							
	A-2145-FANA(P913)-*		2145-N-AN		2144-AA-A IAA-P913B		(3.05) / .120		12 / 1							
F	A-2145-DANC(P913)-*		2145-N-AN		2144-AA-A2AA-P913B		(4.80) / .189		12 / 2							F
	A-2145-BBNH(P913)-*		2145-NBK-AN		2188-(P913)		(4.06) / .160		12 / 3							
	A-2145-CBNA(P913)-*		2145-NBK-AN		2144-AA-A IAA-P913B		(3.05) / .120		12 / 4							
	A-2145-FGNA(550)-*		2145-N-CN		2144-AA-A IAA-550B		(3.05) / .120		13 / 1							
	A-2145-BANH(P913)-*		2145-N-AN		2188-(P913)		(4.06) / .160		13 / 2							
E	A-2145-BANH(587)-*		2145-N-AN		2188-(587)		(4.06) / .160		13 / 3							E
	A-2145-FANA(503)-*		2145-N-AN		2144-AA-A IAA-503B		(3.05) / .120		13 / 4							
	A-2145-EANH(P913)-*		2145-N-AN		2188-(P913)		(4.06) / .160		14 / 1							
	A-2145-AANK(P913)-*		2145-N-AN		4244-(P913)		(3.68) / .145		14 / 2							
	A-2145-ABNK(P913)-*		2145-NBK-AN		4244-(P913)		(3.68) / .145		14 / 3							
D	A-2145-ABNA(587)-*		2145-NBK-AN		2144-AA-A IAA-587B		(3.68) / .145		14 / 4							D
	A-2145-AANA-(I09)-*		2145-N-AN		2144-AA-A IAA-I09B		(3.68) / .145		15 / 1							
	A-2145-CANA(P913)-*		2145-N-AN		2144-AA-A IAA-P913B		(3.05) / .120		15 / 2							
	A-2145-AANB(I22)-*		2145-N-AN		2144-BA-A IAA(I22)B		(3.68) / .145		15 / 3							
	A-2145-BANL(I22)-*		2145-N-AN		6298-(I22)		(4.06) / .160		15 / 4							
	A-2145-CANB(I22)-*		2145-N-AN		2144-BA-A IAA(I22)B		(3.05) / .120		16 / 1							
C	A-2145-EGNH(P913)-*		2145-N-CN		2188-(P913)		(4.06) / .160		16 / 2							C
	A-2145-FGNA(P913)-*		2145-N-CN		2144-AA-A IAA-P913B		(3.05) / .120		16 / 3							
	A-2145-CANA(587)-*		2145-N-AN		2144-AA-A IAA-587B		(3.05) / .120		16 / 4							
	A-2145-BHNH(I22)-*		2145-NGN-AN		2188-(I22)		(4.06) / .160		17 / 1							
	A-2145-BJNH(I22)-*		2145-NYW-AN		2188-(I22)		(4.06) / .160		17 / 2							
B	A-2145-BKNH(I22)-*		2145-NRD-AN		2188-(I22)		(4.06) / .160		17 / 3							B
							/		/							

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

09-62-6043