









TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - SEALING CODE 3 - DESIGN WILL PASS SALT FOG AND IMMERSION TEST AFTER CONDITIONING AS SPECIFIED IN ESA-644 (WEATHER-PACK), ESA-710 (METRI-PACK), ESA-650 (UNDERHOOD MICRO-PACK), C-4006 (WORLD CONNECTOR), ETC WHEN MATED TO MATING PART OR EQUIVALENT
 - THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
 - REFERENCE MATING COMPONENTS OR EQUIVALENT: SEE PE119328 MATING CONFIGURATION REQUIREMENTS DRAWING MATING HEADER ASSEMBLY - 15463914
 - THIS PART ACCEPTS THE FOLLOWING HARNESS COMPONENTS OR EQUIVALENT: WIRE DRESS COVER - SEE CHART SECONDARY TERMINAL LOCK MIC/P 100W - 15404650 (2 REQ'D) 100W CAVITY PLUG - 12129557
 - CAVITIES ACCEPT THE FOLLOWING TERMINALS OR EQUIVALENT: CAVITIES 1-64 MIC/P 100W TO ACCEPT 20,22 GAUGE 15359002 OR EQUIVALENT 20,22 GAUGE 15359001 OR EQUIVALENT
 - USE M7 (7MM) HEX-HEAD DRIVE SOCKET
MAX BOLT TORQUE 6 N-m.
MIN BOLT TORQUE 4 N-m.
 - CONNECTOR SEAL MUST SIT FLUSH WITH INSIDE FACE OF CONNECTOR. CONNECTOR SEAL MUST NOT BE ROLLED OR TWISTED.
 - FOR OPEN SEAL CAVITIES, SEE CHART.
 - ALL CAVITIES ACCEPT A MAX. INSULATION CRIMP OF 2.3 HIGH AND 2.3 WIDE (2.42 MAX CABLE O.D.) REFER TO ES-A-605 FOR CRIMP DIMENSIONS.



DRAWING NUMBER			
15488666			
SIZE	SCALE	FRAME NO	SHEET NO
A1x3	2:1	2 OF 2	1 OF 1
REV N/P			
R 03			

15488668	R	03	-		102	64W CONN ASM	1 THRU 64	15488662	DARK BLUE	15489396	LT BLUE	2.26-2.42	15488665	15488663	GRAY	D OR C	15488664 (DRESS D)/TBD (DRESS C)
15488667	R	03	-		101	64W CONN ASM	1 THRU 64	15488661	GRAY	15489396	LT BLUE	2.26-2.42	15488665	15488663	GRAY	D OR C	15488664 (DRESS D)/TBD (DRESS C)
PART NO	STG	REV	N/P	STATUS	TYPE	DESCRIPTION	OPEN CABLE SEAL CAVITIES	CONN HSG PART NUMBER	CONN HSG COLOR	CABLE SEAL PART NUMBER	CABLE SEAL COLOR	CABLE O.D. RANGE	BOLT P/N	STRAIN RELIEF PART NUMBER	STRAIN RELIEF COLOR	TYP CABLE DRESS TYPE	MATING WIRE DRESS COVER (DRESS TYPE) OR EQUIVALENT

UNLESS OTHERWISE SPECIFIED			
FROM	TO	SCALE	THIRD ANGLE PROJECTION
10.151-10.21	10.151-10.21	1:1	DO NOT SCALE
USE MATH DATA			

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
OR	DATE
APPRO: ROBERT HURO	18MY04
APPRO: ROBERT HURO	18MY04
APPRO: KARL SZENNA	20MY04
APPRO:	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI (DPP0001)	
DRAWING NAME	
TAXI ASM CONN 64 MIC/P 100W	
DRAWING NUMBER	
15488666	
SIZE	SCALE
A1x3	2:1
FRAME NO	SHEET NO
2 OF 2	1 OF 1
REV	N/P
R 03	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[15488667](#)