

# CNY171, CNY172, CNY173, CNY174, CNY17F1, CNY17F2, CNY17F3, CNY17F4, MOC8101, MOC8102, MOC8103, MOC8104, MOC8105, MOC8106, MOC8107, MOC8108 Phototransistor Optocouplers

## Features

- CNY171/2/3/4 and CNY17F1/2/3/4 are also available in white package by specifying M suffix (eg. CNY17F2M)
- UL recognized (File # E90700)
- VDE recognized
  - Add option V for white package (e.g., CNY17F2VM)
  - File #102497
  - Add option '300' for black package (e.g., CNY17F2300)
  - File #94766
- Current transfer ratio in select groups
- High  $BV_{CEO}$ —70V minimum (CNY17X/M, CNY17FX/M, MOC8106/7/8)
- Closely matched current transfer ratio (CTR) minimizes unit-to-unit variation.
- Very low coupled capacitance along with no chip to pin 6 base connection for minimum noise susceptibility (CNY17FX/M, MOC810X)


## Applications

- Power supply regulators
- Digital logic inputs
- Microprocessor inputs
- Appliance sensor systems
- Industrial controls


## Description

The CNY17, CNY17F and MOC810X devices consist of a Gallium Arsenide IRED coupled with an NPN phototransistor in a dual in-line package.



## White Package (-M Suffix)



## Black Package (No -M Suffix)



## Schematic



**Absolute Maximum Ratings**

| Parameters                                                | Symbol              | Device                              | Value          | Units |
|-----------------------------------------------------------|---------------------|-------------------------------------|----------------|-------|
| TOTAL DEVICE                                              |                     |                                     |                |       |
| Storage Temperature                                       | T <sub>STG</sub>    | M                                   | -40 to +150    | °C    |
|                                                           |                     | non M                               | -55 to +150    |       |
| Operating Temperature                                     | T <sub>OPR</sub>    | M                                   | -40 to +100    | °C    |
|                                                           |                     | non M                               | -55 to +100    |       |
| Lead Solder Temperature                                   | T <sub>SOL</sub>    | All                                 | 260 for 10 sec | °C    |
| Total Device Power Dissipation @ 25°C (LED plus detector) | P <sub>D</sub>      | M                                   | 250            | mW    |
| Derate Linearly From 25°C                                 |                     | non M                               | 250            |       |
|                                                           |                     | M                                   | 2.94           | mW/°C |
|                                                           |                     | non M                               | 3.30           |       |
| EMITTER                                                   |                     |                                     |                |       |
| Continuous Forward Current                                | I <sub>F</sub>      | M                                   | 60             | mA    |
|                                                           |                     | non M                               | 100            |       |
| Reverse Voltage                                           | V <sub>R</sub>      | All                                 | 6              | V     |
| Forward Current - Peak (1 μs pulse, 300 pps)              | I <sub>F</sub> (pk) | M                                   | 1.5            | A     |
|                                                           |                     | non M                               | 1.0            |       |
| LED Power Dissipation 25°C Ambient                        | P <sub>D</sub>      | M                                   | 120            | mW    |
|                                                           |                     | non M                               | 150            |       |
|                                                           |                     | M                                   | 1.41           | mW/°C |
|                                                           |                     | non M                               | 1.8            |       |
| DETECTOR                                                  |                     |                                     |                |       |
| Continuous Collector Current                              | I <sub>C</sub>      | All                                 | 50             | mA    |
| Collector-Emitter Voltage                                 | V <sub>CEO</sub>    | CNY17X/M, CNY17FX/M,<br>MOC8106/7/8 | 70             | V     |
|                                                           |                     | MOC8101/2/3/4/5                     | 30             | V     |
| Emitter Collector Voltage                                 | V <sub>ECO</sub>    | All                                 | 7              | V     |
| Detector Power Dissipation @ 25°C                         | P <sub>D</sub>      | M                                   | 150            | mW    |
| Derate Linearly from 25°C                                 |                     | non M                               | 150            |       |
|                                                           |                     | M                                   | 1.76           | mW/°C |
|                                                           |                     | non M                               | 2.0            |       |

**Electrical Characteristics** ( $T_A = 25^\circ\text{C}$  Unless otherwise specified.)<sup>(1)</sup>**Individual Component Characteristics**

| Parameters              | Test Conditions                           | Symbol | Device                | Min | Typ   | Max  | Units         |
|-------------------------|-------------------------------------------|--------|-----------------------|-----|-------|------|---------------|
| <b>EMITTER</b>          |                                           |        |                       |     |       |      |               |
| Input Forward Voltage   | $I_F = 60\text{ mA}$                      | $V_F$  | CNY17FX/M<br>CNY17X/M | 1.0 | 1.35  | 1.65 | V             |
|                         | $I_F = 10\text{ mA}$                      |        | MOC810X               | 1.0 | 1.15  | 1.50 |               |
| Capacitance             | $V_F = 0\text{ V}$ , $f = 1.0\text{ MHz}$ | $C_J$  | All                   |     | 18    |      | pF            |
| Reverse Leakage Current | $V_R = 6\text{ V}$                        | $I_R$  | All                   |     | 0.001 | 10   | $\mu\text{A}$ |

**Individual Component Characteristics (Continued)**

| Parameters                                | Test Conditions                  | Symbol     | Device                                           | Min | Typ | Max | Units |
|-------------------------------------------|----------------------------------|------------|--------------------------------------------------|-----|-----|-----|-------|
| <b>DETECTOR</b>                           |                                  |            |                                                  |     |     |     |       |
| Breakdown Voltage<br>Collector to Emitter | $I_C = 1.0 \text{ mA}, I_F = 0$  | $BV_{CEO}$ | MOC8101/2/3/4/5                                  | 30  | 100 |     | V     |
|                                           |                                  |            | MOC8106/7/8<br>CNY17F1/2/3/4/M<br>CNY171/2/3/4/M | 70  | 100 |     |       |
| Collector to Base                         | $I_C = 10 \mu\text{A}, I_F = 0$  | $BV_{CBO}$ | CNY171/2/3/4/M                                   | 70  | 120 |     |       |
| Emitter to Collector                      | $I_E = 100 \mu\text{A}, I_F = 0$ | $BV_{ECO}$ | All                                              | 7   | 10  |     |       |
| Leakage Current<br>Collector to Emitter   | $V_{CE} = 10 \text{ V}, I_F = 0$ | $I_{CEO}$  | All                                              |     | 1   | 50  | nA    |
| Collector to Base                         | $V_{CB} = 10 \text{ V}, I_F = 0$ | $I_{CBO}$  | CNY171/2/3/4/M                                   |     |     | 20  | nA    |
| Capacitance<br>Collector to Emitter       | $V_{CE} = 0, f = 1 \text{ MHz}$  | $C_{CE}$   | All                                              |     | 8   |     | pF    |
| Collector to Base                         | $V_{CB} = 0, f = 1 \text{ MHz}$  | $C_{CB}$   | CNY171/2/3/4/M                                   |     | 20  |     | pF    |
| Emitter to Base                           | $V_{EB} = 0, f = 1 \text{ MHz}$  | $C_{EB}$   | CNY171/2/3/4/M                                   |     | 10  |     | pF    |

**Isolation Characteristics**

| Characteristic                 | Test Conditions                              | Symbol    | Device            | Min       | Typ** | Max | Units     |
|--------------------------------|----------------------------------------------|-----------|-------------------|-----------|-------|-----|-----------|
| Input-Output Isolation Voltage | $f = 60 \text{ Hz}, t = 1 \text{ min. (4)}$  | $V_{ISO}$ | Black Package     | 5300      |       |     | Vac(rms)* |
|                                | $f = 60 \text{ Hz}, t = 1 \text{ sec. (4)}$  |           | 'M' White Package | 7500      |       |     | Vac(pk)   |
| Isolation Resistance           | $V_{I-O} = 500 \text{ VDC (4)}$              | $R_{ISO}$ | All               | $10^{11}$ |       |     | $\Omega$  |
| Isolation Capacitance          | $V_{I-O} = \emptyset, f = 1 \text{ MHz (4)}$ | $C_{ISO}$ | Black Package     |           | 0.5   |     | pF        |
|                                |                                              |           | 'M' White Package |           | 0.2   |     |           |

Note

\* 5300 Vac(rms) for 1 minute equates to approximately 9000 Vac (pk) for 1 second

\*\* Typical values at  $T_A = 25^\circ\text{C}$

**Transfer Characteristics** ( $T_A = 25^\circ\text{C}$  Unless otherwise specified.)<sup>(1)</sup>

| DC Characteristics                   |                       | Test Conditions                                    | Symbol               | Min | Typ | Max | Units |
|--------------------------------------|-----------------------|----------------------------------------------------|----------------------|-----|-----|-----|-------|
| Coupled                              |                       |                                                    |                      |     |     |     |       |
| Output Collector Current             | MOC8101               | (I <sub>F</sub> = 10 mA, V <sub>CE</sub> = 10 V)   | (CTR) <sup>(2)</sup> | 50  | —   | 80  | %     |
|                                      | MOC8102               |                                                    |                      | 73  | —   | 117 |       |
|                                      | MOC8103               |                                                    |                      | 108 | —   | 173 |       |
|                                      | MOC8104               |                                                    |                      | 160 | —   | 256 |       |
|                                      | MOC8105               |                                                    |                      | 65  | —   | 133 |       |
|                                      | MOC8106               |                                                    |                      | 50  | —   | 150 |       |
|                                      | MOC8107               |                                                    |                      | 100 | —   | 300 |       |
|                                      | MOC8108               |                                                    |                      | 250 | —   | 600 |       |
|                                      | CNY17F1/1M            | (I <sub>F</sub> = 10 mA, V <sub>CE</sub> = 5 V)    |                      | 40  | —   | 80  |       |
|                                      | CNY17F2/2M            |                                                    |                      | 63  | —   | 125 |       |
|                                      | CNY17F3/3M            |                                                    |                      | 100 | —   | 200 |       |
|                                      | CNY17F4/4M            |                                                    |                      | 160 | —   | 320 |       |
|                                      | CNY171/1M             |                                                    |                      | 40  | —   | 80  |       |
|                                      | CNY172/2M             |                                                    |                      | 63  | —   | 125 |       |
|                                      | CNY173/3M             |                                                    |                      | 100 | —   | 200 |       |
|                                      | CNY174/4M             |                                                    |                      | 160 | —   | 320 |       |
| Collector-Emitter Saturation Voltage | CNY17XM/FXM           | (I <sub>C</sub> = 2.5 mA, I <sub>F</sub> = 10 mA)  | V <sub>CE(sat)</sub> | —   | —   | 0.4 | V     |
|                                      | MOC8101/2/3/4/5/6/7/8 | (I <sub>C</sub> = 500 μA, I <sub>F</sub> = 5.0 mA) |                      |     |     |     |       |
|                                      | CNY17X/FX             | (I <sub>F</sub> = 10 mA, I <sub>C</sub> = 2.5 mA)  |                      | —   | —   | 0.3 | V     |

| AC Characteristics <sup>(3)</sup>   |                 | Test Conditions                                                        | Symbol    | Min | Typ* | Max | Units         |
|-------------------------------------|-----------------|------------------------------------------------------------------------|-----------|-----|------|-----|---------------|
| <b>Non-Saturated Switching Time</b> |                 |                                                                        |           |     |      |     |               |
| Turn-On Time                        | MOC8101/2/3/4/5 | $(I_C = 2.0\text{ mA}, V_{CC} = 10\text{ V}, R_L = 100\text{ }\Omega)$ | $t_{on}$  | —   | 2    | 20  | $\mu\text{s}$ |
|                                     | MOC8106/7/8     |                                                                        |           |     |      | —   |               |
|                                     | CNY17X/FX       |                                                                        |           |     |      | 10  |               |
| Turn-Off Time                       | MOC8101/2/3/4/5 | $(I_C = 2.0\text{ mA}, V_{CC} = 10\text{ V}, R_L = 100\text{ }\Omega)$ | $t_{off}$ | —   | 3    | 20  | $\mu\text{s}$ |
|                                     | MOC8106/7/8     |                                                                        |           |     |      | —   |               |
|                                     | CNY17X/FX       |                                                                        |           |     |      | 10  |               |
| Delay Time                          | CNY17XM/FXM     | $(I_F = 10\text{ mA}, V_{CC} = 5\text{ V}, R_L = 75\text{ }\Omega)$    | $t_d$     | —   | —    | 5.6 | $\mu\text{s}$ |
| Rise Time                           | All Devices     | $(I_C = 2.0\text{ mA}, V_{CC} = 10\text{ V}, R_L = 100\text{ }\Omega)$ | $t_r$     | —   | 1    | —   | $\mu\text{s}$ |
|                                     | CNY17XM/FXM     | $(I_F = 10\text{ mA}, V_{CC} = 5\text{ V}, R_L = 75\text{ }\Omega)$    |           |     |      | 4.0 |               |
| Storage Time                        | CNY17XM/FXM     | $(I_F = 10\text{ mA}, V_{CC} = 5\text{ V}, R_L = 75\text{ }\Omega)$    | $t_s$     | —   | —    | 4.1 | $\mu\text{s}$ |
| Fall Time                           | All Devices     | $(I_C = 2.0\text{ mA}, V_{CC} = 10\text{ V}, R_L = 100\text{ }\Omega)$ | $t_f$     | —   | 2    | —   | $\mu\text{s}$ |
|                                     | CNY17XM/FXM     | $(I_F = 10\text{ mA}, V_{CC} = 5\text{ V}, R_L = 75\text{ }\Omega)$    |           |     |      | 3.5 |               |

**Transfer Characteristics (continued)** ( $T_A = 25^\circ\text{C}$  Unless otherwise specified.)<sup>(1)</sup>

| AC Characteristics <sup>(3)</sup> |                                   | Test Conditions                                                        | Symbol           | Min | Typ | Max  | Units |
|-----------------------------------|-----------------------------------|------------------------------------------------------------------------|------------------|-----|-----|------|-------|
| Saturated Switching Times         |                                   |                                                                        |                  |     |     |      |       |
| Turn-on Time                      | CNY171/F1                         | (I <sub>F</sub> = 20 mA, V <sub>CE</sub> = 0.4 V)                      | t <sub>on</sub>  | —   | —   | 5.5  | μs    |
|                                   | CNY172/F2                         | (I <sub>F</sub> = 10 mA, V <sub>CE</sub> = 0.4 V)                      |                  | —   | —   | 8.0  |       |
|                                   | CNY173/F3                         |                                                                        |                  |     |     |      |       |
|                                   | CNY174/F4                         |                                                                        |                  |     |     |      |       |
| Rise Time                         | CNY171/F1                         | (I <sub>F</sub> = 20 mA, V <sub>CE</sub> = 0.4 V)                      | t <sub>r</sub>   | —   | —   | 4.0  | μs    |
|                                   | CNY172/F1                         | (I <sub>F</sub> = 10 mA, V <sub>CE</sub> = 0.4 V)                      |                  | —   | —   | 6.0  |       |
|                                   | CNY173/F3                         |                                                                        |                  |     |     |      |       |
|                                   | CNY174/F4                         |                                                                        |                  |     |     |      |       |
|                                   | CNY171M/F1M                       | (I <sub>F</sub> = 20 mA, V <sub>CC</sub> = 5 V, R <sub>L</sub> = 1 KΩ) |                  | —   | —   | 4.0  |       |
|                                   | CNY172M/3M/4M<br>CNY17F2M/F3M/F4M | (I <sub>F</sub> = 10 mA, V <sub>CC</sub> = 5 V, R <sub>L</sub> = 1 KΩ) |                  | —   | —   | 6.0  |       |
| Delay Time                        | CNY171M/F1M                       | (I <sub>F</sub> = 20 mA, V <sub>CC</sub> = 5 V, R <sub>L</sub> = 1 KΩ) | t <sub>d</sub>   | —   | —   | 5.5  | μs    |
|                                   | CNY172M/3M/4M<br>CNY17F2M/F3M/F4M | (I <sub>F</sub> = 10 mA, V <sub>CC</sub> = 5 V, R <sub>L</sub> = 1 KΩ) |                  | —   | —   | 8.0  |       |
| Turn-off Time                     | CNY171/F1                         | (I <sub>F</sub> = 20 mA, V <sub>CE</sub> = 0.4 V)                      | t <sub>off</sub> | —   | —   | 34   | μs    |
|                                   | CNY172/F2                         | (I <sub>F</sub> = 10 mA, V <sub>CE</sub> = 0.4 V)                      |                  | —   | —   | 39   |       |
|                                   | CNY173/F3                         |                                                                        |                  |     |     |      |       |
|                                   | CNY174/F4                         |                                                                        |                  |     |     |      |       |
| Fall Time                         | CNY171/F1                         | (I <sub>F</sub> = 20 mA, V <sub>CE</sub> = 0.4 V)                      | t <sub>f</sub>   | —   | —   | 20   | μs    |
|                                   | CNY172/F2                         | (I <sub>F</sub> = 10 mA, V <sub>CE</sub> = 0.4 V)                      |                  | —   | —   | 24   |       |
|                                   | CNY173/F3                         |                                                                        |                  |     |     |      |       |
|                                   | CNY174/F4                         |                                                                        |                  |     |     |      | μs    |
|                                   | CNY171M/F1M                       | (I <sub>F</sub> = 20 mA, V <sub>CC</sub> = 5V, R <sub>L</sub> = 1KΩ)   |                  | —   | —   | 20.0 |       |
|                                   | CNY172M/3M/4M<br>CNY17F2M/F3M/F4M | (I <sub>F</sub> = 10 mA, V <sub>CC</sub> = 5V, R <sub>L</sub> = 1KΩ)   |                  | —   | —   | 24.0 |       |
|                                   |                                   |                                                                        |                  |     |     |      |       |
| Storage Time                      | CNY171M/F1M                       | (I <sub>F</sub> = 20 mA, V <sub>CC</sub> = 5V, R <sub>L</sub> = 1KΩ)   | t <sub>s</sub>   | —   | —   | 34.0 | μs    |
|                                   | CNY172M/3M/4M<br>CNY17F2M/F3M/F4M | (I <sub>F</sub> = 10 mA, V <sub>CC</sub> = 5V, R <sub>L</sub> = 1KΩ)   |                  | —   | —   | 39.0 |       |

\*\* All typicals at  $T_A = 25^\circ\text{C}$

**Notes:**

1. Always design to the specified minimum/maximum electrical limits (where applicable).
2. Current Transfer Ratio (CTR) =  $I_C/I_F \times 100\%$ .
3. For test circuit setup and waveforms, refer to Figures 20.
4. For this test, Pins 1 and 2 are common, and Pins 4 and 5 are common.

**Fig.1 Normalized CTR vs. Forward Current  
(Black Package)**




**Fig.2 Normalized CTR vs. Forward Current  
(White Package)**




**Fig. 3 Normalized CTR vs. Ambient Temperature  
(Black Package)**




**Fig. 4 Normalized CTR vs. Ambient Temperature  
(White Package)**




**Fig. 5 CTR vs. RBE (Unsaturated)  
(Black Package)**




**Fig. 6 CTR vs. RBE (Unsaturated)  
(White Package)**




**Fig. 7 CTR vs. R<sub>BE</sub> (Saturated)  
(Black Package)**




**Fig. 8 CTR vs. R<sub>BE</sub> (Saturated)  
(White Package)**




**Fig. 9 Switching Speed vs. Load Resistor  
(Black Package)**




**Fig. 10 Switching Speed vs. Load Resistor  
(White Package)**




**Fig. 11 Normalized t<sub>on</sub> vs. R<sub>BE</sub>  
(Black Package)**




**Fig. 12 Normalized t<sub>on</sub> vs. R<sub>BE</sub>  
(White Package)**




Fig. 13 Normalized  $t_{off}$  vs.  $R_{BE}$   
(Black Package)




Fig. 14 Normalized  $t_{off}$  vs.  $R_{BE}$   
(White Package)




Fig. 15 LED Forward Voltage vs. Forward Current  
(Black Package)




Fig. 16 LED Forward Voltage vs. Forward Current  
(White Package)




Fig. 17 Collector-Emitter Saturation Voltage vs Collector Current  
(Black Package)




Fig. 18 Collector-Emitter Saturation Voltage vs Collector Current  
(White Package)




Fig. 19 Dark Current vs. Ambient Temperature  
(Black Package)





Figure 20. Switching Time Test Circuit






Figure 21. Switching Time Test Circuit

## Black Package (No -M Suffix)


### Package Dimensions (Through Hole)




### Package Dimensions (Surface Mount)



### Package Dimensions (0.4" Lead Spacing)



### Recommended Pad Layout for Surface Mount Leadform (Black Package Only)




#### NOTE


All dimensions are in inches (millimeters)

## White Package (-M Suffix)


### Package Dimensions (Through Hole)




### Package Dimensions (Surface Mount)



### Package Dimensions (0.4" Lead Spacing)



### Recommended Pad Layout for Surface Mount Leadform (White Package Only)




#### NOTE

All dimensions are in inches (millimeters)




## Marking Information (Black package non 'M' suffix)




| Definitions |                                                                                        |
|-------------|----------------------------------------------------------------------------------------|
| 1           | Fairchild logo                                                                         |
| 2           | Device number                                                                          |
| 3           | VDE mark (Note: Only appears on parts ordered with VDE option – See order entry table) |
| 4           | Two digits year code, e.g., '03'; One digit year code for 'M' version, e.g. '5'        |
| 5           | Two digit work week ranging from '01' to '53'                                          |
| 6           | Assembly package code                                                                  |

## Reflow Profile (Black Package, No Suffix)




- Peak reflow temperature: 225°C (package surface temperature)
- Time of temperature higher than 183°C for 60–150 seconds
- One time soldering reflow is recommended

## Marking Information (White package M suffix)



| Definitions |                                                                                        |
|-------------|----------------------------------------------------------------------------------------|
| 1           | Fairchild logo                                                                         |
| 2           | Device number                                                                          |
| 3           | VDE mark (Note: Only appears on parts ordered with VDE option – See order entry table) |
| 4           | Single digit year code, e.g. '5'                                                       |
| 5           | Two digit work week ranging from '01' to '53'                                          |
| 6           | Assembly package code                                                                  |

## Reflow Profile (White Package, M Suffix)



## TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

|                                                  |                                 |                           |                                 |                             |
|--------------------------------------------------|---------------------------------|---------------------------|---------------------------------|-----------------------------|
| ACE <sup>™</sup>                                 | FAST <sup>®</sup>               | ISOPLANAR <sup>™</sup>    | PowerSaver <sup>™</sup>         | SuperSOT <sup>™</sup> -8    |
| ActiveArray <sup>™</sup>                         | FAST <sup>™</sup>               | LittleFET <sup>™</sup>    | PowerTrench <sup>®</sup>        | SyncFET <sup>™</sup>        |
| Bottomless <sup>™</sup>                          | FPS <sup>™</sup>                | MICROCOUPLER <sup>™</sup> | QFET <sup>®</sup>               | TinyLogic <sup>®</sup>      |
| Build it Now <sup>™</sup>                        | FRFET <sup>™</sup>              | MicroFET <sup>™</sup>     | QS <sup>™</sup>                 | TINYOPTO <sup>™</sup>       |
| CoolFET <sup>™</sup>                             | GlobalOptoisolator <sup>™</sup> | MicroPak <sup>™</sup>     | QT Optoelectronics <sup>™</sup> | TruTranslation <sup>™</sup> |
| CROSSVOLT <sup>™</sup>                           | GTO <sup>™</sup>                | MICROWIRE <sup>™</sup>    | Quiet Series <sup>™</sup>       | UHC <sup>™</sup>            |
| DOMET <sup>™</sup>                               | HiSeC <sup>™</sup>              | MSX <sup>™</sup>          | RapidConfigure <sup>™</sup>     | UltraFET <sup>®</sup>       |
| EcoSPARK <sup>™</sup>                            | I <sup>2</sup> C <sup>™</sup>   | MSXPro <sup>™</sup>       | RapidConnect <sup>™</sup>       | UniFET <sup>™</sup>         |
| E <sup>2</sup> CMOS <sup>™</sup>                 | i-Lo <sup>™</sup>               | OCX <sup>™</sup>          | μSerDes <sup>™</sup>            | VCX <sup>™</sup>            |
| EnSigna <sup>™</sup>                             | ImpliedDisconnect <sup>™</sup>  | OCXPro <sup>™</sup>       | SILENT SWITCHER <sup>®</sup>    | Wire <sup>™</sup>           |
| FACT <sup>™</sup>                                | IntelliMAX <sup>™</sup>         | OPTOLOGIC <sup>®</sup>    | SMART START <sup>™</sup>        |                             |
| FACT Quiet Series <sup>™</sup>                   |                                 | OPTOPLANAR <sup>™</sup>   | SPM <sup>™</sup>                |                             |
| Across the board. Around the world. <sup>™</sup> |                                 | PACMAN <sup>™</sup>       | Stealth <sup>™</sup>            |                             |
| The Power Franchise <sup>®</sup>                 |                                 | POP <sup>™</sup>          | SuperFET <sup>™</sup>           |                             |
| Programmable Active Droop <sup>™</sup>           |                                 | Power247 <sup>™</sup>     | SuperSOT <sup>™</sup> -3        |                             |
|                                                  |                                 | PowerEdge <sup>™</sup>    | SuperSOT <sup>™</sup> -6        |                             |

## DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

## PRODUCT STATUS DEFINITIONS

### Definition of Terms

| Datasheet Identification | Product Status         | Definition                                                                                                                                                                                                            |
|--------------------------|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Advance Information      | Formative or In Design | This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.                                                                                    |
| Preliminary              | First Production       | This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design. |
| No Identification Needed | Full Production        | This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.                                                       |
| Obsolete                 | Not In Production      | This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.                                                   |

Rev. 116